


Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Printed circuit board terminal, nominal current: 32 A, rated voltage (III/2): 400 V, nominal cross section: 4 mm<sup>2</sup>, number of potentials: 10, number of rows: 1, number of positions per row: 10, product range: SPT 2,5/...-H-THR, pitch: 5 mm, connection method: Push-in spring connection, mounting: THR soldering / wave soldering, conductor/PCB connection direction: 0 °, color: black, Pin layout: Linear pinning, Solder pin [P]: 2 mm, number of solder pins per potential: 2, type of packaging: 72 mm wide tape

Your advantages

- Time saving push-in connection, tools not required
- Defined contact force ensures that contact remains stable over the long term
- Intuitive operation due to color-coded actuating push button
- Operation and conductor connection from one direction enable integration into front of device
- Designed for integration into the SMT soldering process

Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 1135289                        |
| Packing unit                         | 125 pc                         |
| Minimum order quantity               | 125 pc                         |
| Note                                 | Made to order (non-returnable) |
| Sales key                            | AA13                           |
| Product key                          | AAMCAA                         |
| GTIN                                 | 4063151068783                  |
| Weight per piece (including packing) | 21.08 g                        |
| Weight per piece (excluding packing) | 15.47 g                        |
| Customs tariff number                | 85369010                       |
| Country of origin                    | PL                             |

# SPT-THR 2,5/10-H-5,0 P20 R72 - PCB terminal block



1135289

<https://www.phoenixcontact.com/us/products/1135289>

## Technical data

### Product properties

|                           |                                |
|---------------------------|--------------------------------|
| Product type              | Printed circuit board terminal |
| Product family            | SPT 2,5/..-H-THR               |
| Product line              | COMBICON Terminals M           |
| Number of positions       | 10                             |
| Pitch                     | 5 mm                           |
| Number of connections     | 10                             |
| Number of rows            | 1                              |
| Number of potentials      | 10                             |
| Pin layout                | Linear pinning                 |
| Solder pins per potential | 2                              |

### Electrical properties

#### Properties

|                             |       |
|-----------------------------|-------|
| Nominal current $I_N$       | 32 A  |
| Nominal voltage $U_N$       | 400 V |
| Rated voltage (III/3)       | 320 V |
| Rated surge voltage (III/3) | 4 kV  |
| Rated voltage (III/2)       | 400 V |
| Rated surge voltage (III/2) | 4 kV  |
| Rated voltage (II/2)        | 500 V |
| Rated surge voltage (II/2)  | 4 kV  |

### Connection data

#### Connection technology

|                       |                   |
|-----------------------|-------------------|
| Nominal cross section | 4 mm <sup>2</sup> |
|-----------------------|-------------------|

#### Conductor connection

|                                                                                           |                                                                                           |
|-------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------|
| Connection method                                                                         | Push-in spring connection                                                                 |
| Conductor cross-section rigid                                                             | 0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup> (Conductor connection with open terminal point) |
|                                                                                           | 0.5 mm <sup>2</sup> ... 4 mm <sup>2</sup> (Push-in connection)                            |
| Conductor cross-section flexible                                                          | 0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>                                                 |
| Conductor cross-section AWG                                                               | 24 ... 12                                                                                 |
| Conductor cross-section flexible, with ferrule without plastic sleeve                     | 0.25 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>                                              |
| Conductor cross-section, flexible, with ferrule, with plastic sleeve                      | 0.25 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>                                              |
| 2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve | 0.5 mm <sup>2</sup> ... 0.5 mm <sup>2</sup>                                               |
| Stripping length                                                                          | 10 mm                                                                                     |

### Mounting

# SPT-THR 2,5/10-H-5,0 P20 R72 - PCB terminal block



1135289

<https://www.phoenixcontact.com/us/products/1135289>

|               |                                |
|---------------|--------------------------------|
| Mounting type | THR soldering / wave soldering |
| Pin layout    | Linear pinning                 |

## Processing notes

|                                           |                       |
|-------------------------------------------|-----------------------|
| Process                                   | Reflow/wave soldering |
| Moisture Sensitive Level                  | MSL 1                 |
| Classification temperature T <sub>c</sub> | 260 °C                |
| Solder cycles in the reflow               | 3                     |

## Material specifications

### Material data - contact

|                                          |                                                                                  |
|------------------------------------------|----------------------------------------------------------------------------------|
| Note                                     | WEEE/RoHS-compliant, free of whiskers according to IEC 60068-2-82/JEDEC JESD 201 |
| Contact material                         | Cu alloy                                                                         |
| Surface characteristics                  | hot-dip tin-plated                                                               |
| Metal surface terminal point (top layer) | Tin (4 - 8 µm Sn)                                                                |
| Metal surface soldering area (top layer) | Tin (4 - 8 µm Sn)                                                                |

### Material data - housing

|                                                                   |              |
|-------------------------------------------------------------------|--------------|
| Color (Housing)                                                   | black (9005) |
| Insulating material                                               | LCP          |
| Insulating material group                                         | IIIa         |
| CTI according to IEC 60112                                        | 175          |
| Flammability rating according to UL 94                            | V0           |
| Glow wire flammability index GWFI according to EN 60695-2-12      | 850          |
| Glow wire ignition temperature GWIT according to EN 60695-2-13    | 775          |
| Temperature for the ball pressure test according to EN 60695-10-2 | 200 °C       |

### Material data – actuating element

|                                        |              |
|----------------------------------------|--------------|
| Color (Actuating element)              | white (9010) |
| Insulating material                    | PA GF        |
| Insulating material group              | I            |
| CTI according to IEC 60112             | 600          |
| Flammability rating according to UL 94 | V0           |

## Notes

|               |                                                          |
|---------------|----------------------------------------------------------|
| Assembly note | This item is not suitable for PCB cleaning with liquids. |
|---------------|----------------------------------------------------------|

## Dimensions

# SPT-THR 2,5/10-H-5,0 P20 R72 - PCB terminal block



1135289

<https://www.phoenixcontact.com/us/products/1135289>

|                       |                                                                                    |
|-----------------------|------------------------------------------------------------------------------------|
| Dimensional drawing   |  |
| Pitch                 | 5 mm                                                                               |
| Width [w]             | 50.8 mm                                                                            |
| Height [h]            | 14.8 mm                                                                            |
| Length [l]            | 19.15 mm                                                                           |
| Installed height      | 12.8 mm                                                                            |
| Solder pin length [P] | 2 mm                                                                               |

## PCB design

|               |        |
|---------------|--------|
| Hole diameter | 1.2 mm |
|---------------|--------|

## Mechanical tests

### Test for conductor damage and slackening

|               |                     |
|---------------|---------------------|
| Specification | IEC 60999-1:1999-11 |
| Result        | Test passed         |

### Pull-out test

|                                                                             |                                         |
|-----------------------------------------------------------------------------|-----------------------------------------|
| Specification                                                               | IEC 60999-1:1999-11                     |
| Conductor cross-section/conductor type/tractive force setpoint/actual value | 0.2 mm <sup>2</sup> / solid / > 10 N    |
|                                                                             | 0.2 mm <sup>2</sup> / flexible / > 10 N |
|                                                                             | 4 mm <sup>2</sup> / solid / > 60 N      |
|                                                                             | 4 mm <sup>2</sup> / flexible / > 60 N   |
|                                                                             | 0.5 mm <sup>2</sup> / solid / > 20 N    |

## Electrical tests

### Temperature-rise test

|                                   |                                                                                                                                |
|-----------------------------------|--------------------------------------------------------------------------------------------------------------------------------|
| Specification                     | IEC 60947-7-4:2019-01                                                                                                          |
| Requirement temperature-rise test | The sum of ambient temperature and temperature rise of the PCB terminal block shall not exceed the upper limiting temperature. |

### Short-time withstand current

|               |                       |
|---------------|-----------------------|
| Specification | IEC 60947-7-4:2019-01 |
|---------------|-----------------------|

### Insulation resistance

|                                              |                       |
|----------------------------------------------|-----------------------|
| Specification                                | IEC 60512-3-1:2002-02 |
| Insulation resistance, neighboring positions | > 5 MΩ                |

### Air clearances and creepage distances |

|                           |                       |
|---------------------------|-----------------------|
| Specification             | IEC 60947-7-4:2019-01 |
| Insulating material group | IIIa                  |

# SPT-THR 2,5/10-H-5,0 P20 R72 - PCB terminal block



1135289

<https://www.phoenixcontact.com/us/products/1135289>

|                                                        |         |
|--------------------------------------------------------|---------|
| Comparative tracking index (IEC 60112)                 | CTI 175 |
| Rated insulation voltage (III/3)                       | 320 V   |
| Rated surge voltage (III/3)                            | 4 kV    |
| minimum clearance value - non-homogenous field (III/3) | 3 mm    |
| minimum creepage distance (III/3)                      | 5 mm    |
| Rated insulation voltage (III/2)                       | 400 V   |
| Rated surge voltage (III/2)                            | 4 kV    |
| minimum clearance value - non-homogenous field (III/2) | 3 mm    |
| minimum creepage distance (III/2)                      | 4 mm    |
| Rated insulation voltage (II/2)                        | 500 V   |
| Rated surge voltage (II/2)                             | 4 kV    |
| minimum clearance value - non-homogenous field (II/2)  | 3 mm    |
| minimum creepage distance (II/2)                       | 5 mm    |

## Environmental and real-life conditions

### Vibration test

|                        |                                          |
|------------------------|------------------------------------------|
| Specification          | IEC 60068-2-6:2007-12                    |
| Frequency              | 10 - 150 - 10 Hz                         |
| Sweep speed            | 1 octave/min                             |
| Amplitude              | 0.35 mm (10 Hz ... 60.1 Hz)              |
| Acceleration           | 50 m/s <sup>2</sup> (60.1 Hz ... 150 Hz) |
| Test duration per axis | 2.5 h                                    |
| Test directions        | X-, Y- and Z-axis                        |

### Glow-wire test

|                  |                        |
|------------------|------------------------|
| Specification    | IEC 60695-2-10:2013-04 |
| Temperature      | 850 °C                 |
| Time of exposure | 5 s                    |

### Aging

|               |                       |
|---------------|-----------------------|
| Specification | IEC 60947-7-4:2019-01 |
|---------------|-----------------------|

### Ambient conditions

|                                         |                                                                               |
|-----------------------------------------|-------------------------------------------------------------------------------|
| Ambient temperature (operation)         | -40 °C ... 105 °C (Depending on the current carrying capacity/derating curve) |
| Ambient temperature (storage/transport) | -40 °C ... 70 °C                                                              |
| Relative humidity (storage/transport)   | 30 % ... 70 %                                                                 |
| Ambient temperature (assembly)          | -5 °C ... 100 °C                                                              |

## Packaging specifications

|                     |  |
|---------------------|--|
| Dimensional drawing |  |
|---------------------|--|

# SPT-THR 2,5/10-H-5,0 P20 R72 - PCB terminal block




1135289

<https://www.phoenixcontact.com/us/products/1135289>

|                             |                 |
|-----------------------------|-----------------|
| Type of packaging           | 72 mm wide tape |
| [W] tape width              | 72 mm           |
| [W2] coil overall dimension | ≤ 78.4 mm       |
| [A] coil diameter           | ≤ 330 mm        |
| Outer packaging type        | Transparent-Bag |

## Drawings

Diagram



Type: SPT-THR 2,5/...-H-5,0 P...

# SPT-THR 2,5/10-H-5,0 P20 R72 - PCB terminal block



1135289

<https://www.phoenixcontact.com/us/products/1135289>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1135289>

|  <b>VDE approval of drawings</b><br>Approval ID: 40046113 |                       |                       |                   |                             |
|--------------------------------------------------------------------------------------------------------------------------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
|                                                                                                                                            | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| keine                                                                                                                                      |                       |                       |                   |                             |
|                                                                                                                                            | 400 V                 | 32 A                  | -                 | 0.2 - 4                     |

|  <b>cULus Recognized</b><br>Approval ID: E60425-20061129 |                       |                       |                   |                             |
|-------------------------------------------------------------------------------------------------------------------------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
|                                                                                                                                           | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| B                                                                                                                                         |                       |                       |                   |                             |
| Standard                                                                                                                                  | 300 V                 | 20 A                  | 24 - 12           | -                           |
| F                                                                                                                                         |                       |                       |                   |                             |
| USR application only                                                                                                                      | 300 V                 | 20 A                  | 24 - 12           | -                           |
| D                                                                                                                                         |                       |                       |                   |                             |
| Alternative 1                                                                                                                             | 300 V                 | 10 A                  | 24 - 12           | -                           |

# SPT-THR 2,5/10-H-5,0 P20 R72 - PCB terminal block



1135289

<https://www.phoenixcontact.com/us/products/1135289>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27460101 |
| ECLASS-15.0 | 27460101 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC002643 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# SPT-THR 2,5/10-H-5,0 P20 R72 - PCB terminal block



1135289

<https://www.phoenixcontact.com/us/products/1135289>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)