

# TMC 2 M1 120 0,6A - Thermal-magnetic device circuit breaker



0914950

<https://www.phoenixcontact.com/us/products/0914950>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Thermal-magnetic circuit breaker, 2-pos., normal blow, 1 N/O contact and 1 N/C contact, with universal foot for mounting on NS 32 or NS 35

## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 0914950                        |
| Packing unit                         | 1 pc                           |
| Minimum order quantity               | 1 pc                           |
| Note                                 | Made to order (non-returnable) |
| Sales key                            | CL04                           |
| Product key                          | CLA121                         |
| GTIN                                 | 4017918009632                  |
| Weight per piece (including packing) | 137.07 g                       |
| Weight per piece (excluding packing) | 137.07 g                       |
| Customs tariff number                | 85362010                       |
| Country of origin                    | DE                             |

# TMC 2 M1 120 0,6A - Thermal-magnetic device circuit breaker



0914950

<https://www.phoenixcontact.com/us/products/0914950>

## Technical data

### Product properties

|                       |                                        |
|-----------------------|----------------------------------------|
| Product type          | Thermomagnetic device circuit breakers |
| Product family        | TMC                                    |
| Type                  | DIN rail module, one-piece             |
| Number of positions   | 2                                      |
| Number of connections | 4                                      |
| Number of rows        | 2                                      |
| No. of channels       | 1                                      |

### Insulation characteristics

|                      |    |
|----------------------|----|
| Overvoltage category | II |
| Degree of pollution  | 2  |

### Electrical properties

|           |                  |
|-----------|------------------|
| Fuse type | Automatic device |
|-----------|------------------|

### General

|                                                 |                                       |
|-------------------------------------------------|---------------------------------------|
| Rated voltage                                   | 250 V AC (3 AC 433 V)                 |
|                                                 | 65 V DC                               |
| Rated current $I_N$                             | 0.6 A                                 |
| Rated surge voltage                             | 2.5 kV                                |
| Insulation resistance $R_{iso}$                 | > 100 M $\Omega$ (500 V DC)           |
| Auxiliary circuit                               | 240 V AC / 1 A (Low-induction)        |
|                                                 | 65 V AC / 1 A (Low-induction)         |
| Tripping method                                 | TM (thermal-magnetic)                 |
| Device resistance                               | 3 $\Omega$                            |
| Rated short-circuit switching capacity $I_{cn}$ | 400 A                                 |
|                                                 | 2500 A (32 V DC)                      |
| Short-circuit switching capacity                | 5000 A ()                             |
|                                                 | 2000 A (UL 1077: 65 V DC)             |
|                                                 | 3000 V AC (Actuation area)            |
| Dielectric strength                             | 3000 V AC (Main to auxiliary circuit) |
|                                                 | 1500 V AC (Position to position)      |
|                                                 | 10000 (At 1 x $I_N$ , inductive)      |
| Switching cycles, max.                          | 10000 (At 1 x $I_N$ , inductive)      |
| Fuse                                            | M1 (normal blow)                      |
| Contact switching type                          | 1 N/O contact                         |
|                                                 | 1 N/C contact                         |

### Indicator/remote signaling

|                   |                          |
|-------------------|--------------------------|
| Connection name   | Auxiliary contact        |
| Operating voltage | 240 V AC                 |
|                   | 65 V DC                  |
| Operating current | 0.6 A AC (Low-induction) |

# TMC 2 M1 120 0,6A - Thermal-magnetic device circuit breaker



0914950

<https://www.phoenixcontact.com/us/products/0914950>

## Connection data

### Main contact

|                                                                                           |                                              |
|-------------------------------------------------------------------------------------------|----------------------------------------------|
| Connection method                                                                         | Screw connection                             |
| Screw thread                                                                              | M3                                           |
| Tightening torque                                                                         | 0.6 ... 0.8 Nm                               |
| Stripping length                                                                          | 12 mm                                        |
| Internal cylindrical gage                                                                 | A3                                           |
| Conductor cross-section rigid                                                             | 0.2 mm <sup>2</sup> ... 6 mm <sup>2</sup>    |
| Cross section AWG                                                                         | 24 ... 10 (converted acc. to IEC)            |
| Conductor cross-section flexible                                                          | 0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>    |
| Conductor cross-section flexible (ferrule without plastic sleeve)                         | 0.25 mm <sup>2</sup> ... 4 mm <sup>2</sup>   |
| Flexible conductor cross-section (ferrule with plastic sleeve)                            | 0.25 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |
| 2 conductors with same cross section, solid                                               | 0.2 mm <sup>2</sup> ... 0.75 mm <sup>2</sup> |
| 2 conductors with same cross section, flexible                                            | 0.2 mm <sup>2</sup> ... 0.75 mm <sup>2</sup> |
| 2 conductors with same cross section, flexible, with ferrule without plastic sleeve       | 0.25 mm <sup>2</sup> ... 1 mm <sup>2</sup>   |
| 2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve | 0.5 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>  |
| Nominal current                                                                           | 0.6 A                                        |
| Nominal voltage                                                                           | 250 V AC                                     |
|                                                                                           | 65 V DC                                      |

### Auxiliary contact

|                                                                                           |                                              |
|-------------------------------------------------------------------------------------------|----------------------------------------------|
| Connection method                                                                         | Screw connection                             |
| Screw thread                                                                              | M3                                           |
| Tightening torque                                                                         | 0.6 ... 0.8 Nm                               |
| Stripping length                                                                          | 12 mm                                        |
| Internal cylindrical gage                                                                 | A1                                           |
| Conductor cross-section rigid                                                             | 0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>  |
| Cross section AWG                                                                         | 24 ... 14 (converted acc. to IEC)            |
| Conductor cross-section flexible                                                          | 0.2 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>  |
| Conductor cross-section flexible (ferrule without plastic sleeve)                         | 0.25 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |
| Flexible conductor cross-section (ferrule with plastic sleeve)                            | 0.25 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> |
| 2 conductors with same cross section, solid                                               | 0.2 mm <sup>2</sup> ... 0.75 mm <sup>2</sup> |
| 2 conductors with same cross section, flexible                                            | 0.2 mm <sup>2</sup> ... 0.75 mm <sup>2</sup> |
| 2 conductors with same cross section, flexible, with ferrule without plastic sleeve       | 0.25 mm <sup>2</sup> ... 0.5 mm <sup>2</sup> |
| 2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve | 0.5 mm <sup>2</sup> ... 0.75 mm <sup>2</sup> |
| Nominal current                                                                           | 0.6 A                                        |
| Nominal voltage                                                                           | 250 V AC                                     |
|                                                                                           | 65 V DC                                      |

### Main contact

|                   |                  |
|-------------------|------------------|
| Connection method | Screw connection |
|-------------------|------------------|

# TMC 2 M1 120 0,6A - Thermal-magnetic device circuit breaker



0914950

<https://www.phoenixcontact.com/us/products/0914950>

|                                                                                           |                                             |
|-------------------------------------------------------------------------------------------|---------------------------------------------|
| Screw thread                                                                              | M3                                          |
| Tightening torque                                                                         | 0.6 Nm ... 0.8 Nm                           |
| Stripping length                                                                          | 12 mm                                       |
| Conductor cross-section flexible                                                          | 0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>   |
| Conductor cross-section rigid                                                             | 0.2 mm <sup>2</sup> ... 6 mm <sup>2</sup>   |
| Conductor cross-section AWG                                                               | 24 ... 10                                   |
| 2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve | 0.5 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |
| Conductor cross-section, flexible, with ferrule, with plastic sleeve                      | 0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |
| Conductor cross-section flexible, with ferrule without plastic sleeve                     | 0.25 mm <sup>2</sup> ... 4 mm <sup>2</sup>  |

## Auxiliary contact

|                                                                       |                                              |
|-----------------------------------------------------------------------|----------------------------------------------|
| Connection method                                                     | Screw connection                             |
| Screw thread                                                          | M3                                           |
| Tightening torque                                                     | 0.6 Nm ... 0.8 Nm                            |
| Stripping length                                                      | 12 mm                                        |
| Conductor cross-section flexible                                      | 0.2 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>  |
| Conductor cross-section rigid                                         | 0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>  |
| Conductor cross-section AWG                                           | 24 ... 14                                    |
| Conductor cross-section, flexible, with ferrule, with plastic sleeve  | 0.25 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> |
| Conductor cross-section flexible, with ferrule without plastic sleeve | 0.25 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |

## Dimensions

|        |         |
|--------|---------|
| Width  | 25 mm   |
| Height | 82.5 mm |
| Depth  | 96 mm   |

## Material specifications

|                                        |                  |
|----------------------------------------|------------------|
| Color                                  | black (RAL 9005) |
| Flammability rating according to UL 94 | V-2              |
| Insulating material group              | II               |
| Insulating material                    | PA66             |

## Mechanical properties

### Mechanical data

|                 |    |
|-----------------|----|
| Open side panel | No |
|-----------------|----|

## Environmental and real-life conditions

### Ambient conditions

|                                 |                        |
|---------------------------------|------------------------|
| Degree of protection            | IP30 (Actuation area)  |
|                                 | IP20 (Connection area) |
| Ambient temperature (operation) | -30 °C ... 60 °C       |
| Humidity test                   | 240 h, 95 % RH, 40 °C  |

# TMC 2 M1 120 0,6A - Thermal-magnetic device circuit breaker



0914950

<https://www.phoenixcontact.com/us/products/0914950>

## Standards and regulations

|                          |          |
|--------------------------|----------|
| Standards/specifications | EN 60934 |
| Standards/specifications | UL 1077  |

## Mounting

|               |                 |
|---------------|-----------------|
| Mounting type | DIN rail: 35 mm |
|---------------|-----------------|

# TMC 2 M1 120 0,6A - Thermal-magnetic device circuit breaker




0914950

<https://www.phoenixcontact.com/us/products/0914950>

## Drawings

Diagram



# TMC 2 M1 120 0,6A - Thermal-magnetic device circuit breaker



0914950

<https://www.phoenixcontact.com/us/products/0914950>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/0914950>



**CSA**

Approval ID: 074317



**UL Recognized**

Approval ID: FILE E 140459



**VDE Zeichengenehmigung**

Approval ID: 40029348

**UAE-RoHS**

Approval ID: 23-10-88787

# TMC 2 M1 120 0,6A - Thermal-magnetic device circuit breaker



0914950  
<https://www.phoenixcontact.com/us/products/0914950>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27140401 |
| ECLASS-15.0 | 27140401 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC003538 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# TMC 2 M1 120 0,6A - Thermal-magnetic device circuit breaker



0914950

<https://www.phoenixcontact.com/us/products/0914950>

## Environmental product compliance

### EU RoHS

|                                         |      |
|-----------------------------------------|------|
| Fulfills EU RoHS substance requirements | Yes  |
| Exemption                               | 6(c) |

### China RoHS

|                                        |                                                                                                                                                                                                                                   |
|----------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-25                                                                                                                                                                                                                           |
|                                        | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |                                      |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1)                 |
| SCIP                                | a487f4fb-a574-45e1-8e38-9053e63116ed |

### EF3.0 Climate Change

|         |               |
|---------|---------------|
| CO2e kg | 7.812 kg CO2e |
|---------|---------------|

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)