

ST 1-SILED 12 - Fuse plug

0920423

<https://www.phoenixcontact.com/us/products/0920423>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Fuse plug, nom. voltage: 400 V, nominal current: 10 A, width: 9.9 mm, height: 45.4 mm, color: black

Commercial data

Item number	0920423
Packing unit	50 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	BE19
Product key	BE1Z3X
GTIN	4017918010232
Weight per piece (including packing)	9.84 g
Weight per piece (excluding packing)	9.84 g
Customs tariff number	85369095
Country of origin	PL

ST 1-SILED 12 - Fuse plug

0920423

<https://www.phoenixcontact.com/us/products/0920423>



Technical data

Product properties

Product type	Fuse
--------------	------

Electrical properties

Nominal current I_N	10 A
Fuse	G / 6,3 x 32
LED voltage range	5 V ... 15 V

Input data

LED voltage range	5 V ... 15 V
-------------------	--------------

Connection data

Nominal current	10 A
Nominal voltage	400 V (In the event of a defective fuse, the downstream circuit is not disconnected.)

Dimensions

Width	9.9 mm
Height	45.4 mm

Material specifications

Color	black (RAL 9005)
Flammability rating according to UL 94	V2
Insulating material group	CTI 600
Insulating material	PA
Static insulating material application in cold	-60 °C
Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21))	130 °C
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3
Calorimetric heat release NFPA 130 (ASTM E 1354)	28 MJ/kg
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
---------------------------------	---

ST 1-SILED 12 - Fuse plug

0920423

<https://www.phoenixcontact.com/us/products/0920423>



Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

ST 1-SILED 12 - Fuse plug

0920423

<https://www.phoenixcontact.com/us/products/0920423>



Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/0920423>



EAC

Approval ID: RU C-DE.BL08.B.00714

ST 1-SILED 12 - Fuse plug

0920423

<https://www.phoenixcontact.com/us/products/0920423>



Classifications

ECLASS

ECLASS-13.0	27250305
ECLASS-15.0	27250305

ETIM

ETIM 9.0	EC002018
----------	----------

UNSPSC

UNSPSC 21.0	39121600
-------------	----------

ST 1-SILED 12 - Fuse plug



0920423

<https://www.phoenixcontact.com/us/products/0920423>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com