

MINI MCR-EX-NAM-2T - Isolation switch amplifier



1157852

<https://www.phoenixcontact.com/in/products/1157852>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Ex i-NAMUR signal conditioner for operating proximity sensors and switches in the Ex area. The signals are transmitted to the safe area via 2 transistor outputs (passive). Standard configuration, Line fault detection, Safety Integrity Level (SIL, IEC 61508): 3, Screw connection

Commercial data

Item number	1157852
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	*****
Product key	DK1223
GTIN	4063151163303
Weight per piece (including packing)	122.1 g
Weight per piece (excluding packing)	122.1 g
Customs tariff number	85365019
Country of origin	DE

MINI MCR-EX-NAM-2T - Isolation switch amplifier



1157852

<https://www.phoenixcontact.com/in/products/1157852>

Technical data

Product properties

Product type	Isolating switch amplifier
Product family	MINI Analog Pro
Configuration	DIP switches

System properties

Functionality

Configuration	DIP switches
---------------	--------------

Electrical properties

Electrical isolation between input and output	yes
Line monitoring	Line fault detection

Electrical isolation

Overvoltage category	II (≤ 5000 m)
Pollution degree	2 (≤ 5000 m)

Electrical isolation Input/output, power supply IEC/EN 61010-1

Standards/regulations	IEC/EN 61010-1
Rated insulation voltage	300 V _{rms}
Test voltage	2.5 kV AC (50 Hz, 60 s)
Insulation	Double/reinforced insulation

Electrical isolation Input/output, power supply IEC/EN 60079-11

Standards/regulations	IEC/EN 60079-11
Rated insulation voltage	265 V _{rms}

Electrical isolation Input/output, power supply IEC/EN 60079-7

Standards/regulations	IEC/EN 60079-7
Rated insulation voltage	251 V _{rms}

Supply

Nominal supply voltage	24 V DC
Supply voltage range	19.2 V DC ... 30 V DC
Power consumption	≤ 650 mW

Input data

Signal: NAMUR

Number of inputs	1
Available input sources	NAMUR proximity sensors (IEC/EN 60947-5-6)
	floating switch contacts
	Switch contacts with resistance circuit

MINI MCR-EX-NAM-2T - Isolation switch amplifier



1157852

<https://www.phoenixcontact.com/in/products/1157852>

Output data

Switching: Transistor

Output description	passive
Max. switching current	50 mA
Switching frequency	$\leq 10 \text{ kHz}$ ($I_{OUT} \geq 5 \text{ mA}$) $\leq 20 \text{ kHz}$ ($I_{OUT} \geq 30 \text{ mA}$ (further information in the data sheet))

Connection data

Connection method	Screw connection
Stripping length	10 mm
Screw thread	M3
Conductor cross-section rigid	0.2 mm ² ... 1.5 mm ² (with ferrule) 0.14 mm ² ... 2.5 mm ² (without ferrule)
Conductor cross-section flexible	0.14 mm ² ... 2.5 mm ²
Conductor cross-section AWG	24 ... 12 (flexible)
Tightening torque	0.5 Nm ... 0.6 Nm

Ex data

Ex installation (EPL)	Gc Div. 2
Ex i circuits (EPL)	Ga Da Ma Div. 1

Safety data

Max. internal inductance L_i	negligible
Max. internal capacitance C_i	negligible
Max. output voltage U_o	10.1 V
Max. output current I_o	10.9 mA
Max. output power P_o	28 mW
Safety-related maximum voltage U_m	253 V AC 125 V DC
IIA (simple circuit): Max. external inductivity L_o / Max. external capacitance C_o	300 mH / 93 μF
IIB/IIIC (simple circuit): Max. external inductivity L_o / Max. external capacitance C_o	100 mH / 19.4 μF
IIC (simple circuit): Max. external inductivity L_o / Max. external capacitance C_o	300 mH / 2.87 μF
I (simple circuit): Max. external inductivity L_o / Max. external capacitance C_o	300 mH / 160 μF
IIB/IIA (mixed circuit): Max. external inductivity L_o / Max. external capacitance C_o	100 mH / 1 μF
IIIC (mixed circuit): Max. external inductivity L_o / Max. external capacitance C_o	100 mH / 1 μF

MINI MCR-EX-NAM-2T - Isolation switch amplifier



1157852

<https://www.phoenixcontact.com/in/products/1157852>

IIC (mixed circuit): Max. external inductivity L_o / Max. external capacitance C_o	100 mH / 500 nF, 50 mH / 570 nF, 5 mH / 590 nF, 1 mH / 590 nF, 10 μ H / 590 nF
I/IIB/IIA/IIIC (mixed circuit): Max. external inductivity L_o / Max. external capacitance C_o	100 mH / 1 μ F, 5 mH / 1 μ F, 1 mH / 1 μ F, 10 μ H / 1 μ F
I (mixed circuit): Max. external inductivity L_o / Max. external capacitance C_o	100 mH / 1 μ F

Signaling

Status display	Green LED (supply voltage)
	Yellow LED (switching state / status, lights up when output circuit is active)
	Red LED (line errors)

Dimensions

Width	6.2 mm
Height	109.81 mm
Depth	119.2 mm

Material specifications

Color	gray (RAL 7042)
Housing material	PBT

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Permissible humidity (operation)	5 % ... 95 % (non-condensing)

Altitude range (IEC/EN 61010-1)

Height range	> 2000 m ... 3000 m
Ambient temperature (operation)	-40 °C ... 63 °C
Rated insulation voltage	300 V _{rms} (Input/output, power supply)
Insulation	Double/reinforced insulation

Altitude range (IEC/EN 61010-1)

Height range	> 3000 m ... 4000 m
Ambient temperature (operation)	-40 °C ... 56 °C
Rated insulation voltage	300 V _{rms} (Input/output, power supply)
Insulation	Double/reinforced insulation

Altitude range (IEC/EN 61010-1)

Height range	> 4000 m ... 5000 m
Ambient temperature (operation)	-40 °C ... 49 °C
Rated insulation voltage	150 V _{rms} (Input/output, power supply)
Insulation	Double/reinforced insulation

MINI MCR-EX-NAM-2T - Isolation switch amplifier



1157852

<https://www.phoenixcontact.com/in/products/1157852>

Altitude range (IEC/EN 60079-11)

Height range	> 2000 m ... 3000 m
Ambient temperature (operation)	-40 °C ... 63 °C
Safety-related maximum voltage U_m	121 V AC
	110 V DC
Rated insulation voltage	150 V _{rms} (Input/output, power supply)

Altitude range (IEC/EN 60079-11)

Height range	> 3000 m ... 4000 m
Ambient temperature (operation)	-40 °C ... 56 °C
Safety-related maximum voltage U_m	33 V AC/DC
Rated insulation voltage	60 V _{rms} (Input/output, power supply)

Altitude range (IEC/EN 60079-11)

Height range	> 4000 m ... 5000 m
Ambient temperature (operation)	-40 °C ... 49 °C
Safety-related maximum voltage U_m	33 V AC/DC
Rated insulation voltage	60 V _{rms} (Input/output, power supply)

Altitude range (IEC/EN 60079-7)

Height range	> 2000 m ... 3000 m
Ambient temperature (operation)	-40 °C ... 63 °C
Rated insulation voltage	162 V _{rms} (Input/output, power supply)

Altitude range (IEC/EN 60079-7)

Height range	> 3000 m ... 4000 m
Ambient temperature (operation)	-40 °C ... 56 °C
Rated insulation voltage	60 V _{rms} (Input/output, power supply)

Altitude range (IEC/EN 60079-7)

Height range	> 4000 m ... 5000 m
Ambient temperature (operation)	-40 °C ... 49 °C
Rated insulation voltage	60 V _{rms} (Input/output, power supply)

Approvals

CE

Certificate	CE-compliant
-------------	--------------

ATEX

Identification	⊕ II (1) G [Ex ia Ga] IIC
	⊕ II (1) D [Ex ia Da] IIIC
	⊕ II 3 (1) G Ex ec [ia Ga] IIC T4 Gc
	⊕ I (M1) [Ex ia Ma] I
Certificate	IBExU 21 ATEX 1061 X

IECEx

MINI MCR-EX-NAM-2T - Isolation switch amplifier



1157852

<https://www.phoenixcontact.com/in/products/1157852>

Identification	[Ex ia Ga] IIC
	[Ex ia Da] IIIC
	Ex ec [ia Ga] IIC T4 Gc
	[Ex ia Ma] I
Certificate	IECEX IBE 21.0022 X

CCC / China-Ex

Identification	[Ex ia Ga] IIC
	[Ex ia Da] IIIC
	Ex ec [ia Ga] IIC T4 Gc
Certificate	2023122316116235

UL, USA/Canada

Identification	UL 61010-2-201 Listed
	Class I, Div. 1, Groups A, B, C, D
	Class II, Div. 1, Groups E, F, G
	Class III, Div. 1
	Class I, Zone 0, 1, 2, Groups IIC, IIB, IIA
	Class I, Div. 2, Groups A, B, C, D T4
	Class I, Zone 2
	AEx ec [ia Ga] IIC T4 Gc; AEx ec [ia IIIC Da] IIC T4 Gc
	Ex ec [ia Ga] IIC T4 Gc X; Ex ec [ia IIIC Da] IIC T4 Gc X
	Class I, Zone 0, [AEx ia Ga] IIC, [Ex ia Ga] IIC X
	Class I, Zone 20, [AEx ia Da] IIIC, [Ex ia Da] IIIC X
Certificate	UL C.D.-No 097285872

Shipbuilding approval

Certificate	DNV TAA00003FZ
-------------	----------------

Safety Integrity Level (SIL, IEC 61508)

Identification	3
----------------	---

INMETRO

Identification	[Ex ia Ma] I
	[Ex ia Ga] IIC
	[Ex ia Da] IIIC
	Ex ec [ia Ga] IIC T4 Gc
Certificate	DNV 23.0188 X

Shipbuilding data

Temperature	B
Humidity	B
Vibration	A
EMC	A
Enclosure	Required protection according to the Rules shall be provided upon installation on board

MINI MCR-EX-NAM-2T - Isolation switch amplifier



1157852

<https://www.phoenixcontact.com/in/products/1157852>

EMC data

Electromagnetic compatibility	Tested in accordance with the following standards and regulations: EN 61326-1 For industrial use, NAMUR NE 21
Noise immunity	EN 61000-6-2
Noise immunity	EN 61326-3-2

Noise emission

Standards/regulations	EN 61000-6-4
-----------------------	--------------

Standards and regulations

GB Standard

Standards/regulations	GB/T 3836.1
	GB/T 3836.3
	GB/T 3836.4

Mounting

Mounting position	any
-------------------	-----


MINI MCR-EX-NAM-2T - Isolation switch amplifier

1157852

<https://www.phoenixcontact.com/in/products/1157852>

Drawings

Block diagram



MINI MCR-EX-NAM-2T - Isolation switch amplifier



1157852

<https://www.phoenixcontact.com/in/products/1157852>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/1157852>



cULus Listed

Approval ID: E238705



Functional Safety

Approval ID: 1435.IM.131623/19

DNV

Approval ID: TAA00003FZ



IECEx

Approval ID: IECEx IBE 21.0022X



ATEX

Approval ID: IBExU21ATEX1061 X



CCC

Approval ID: 20231223161162352023

INMETRO

Approval ID: DNV 23.0188 X



cULus Listed

Approval ID: E196811



cULus Listed

Approval ID: E196811

MINI MCR-EX-NAM-2T - Isolation switch amplifier



1157852

<https://www.phoenixcontact.com/in/products/1157852>

Classifications

ECLASS

ECLASS-13.0	27210121
ECLASS-15.0	27210121

ETIM

ETIM 9.0	EC001485
----------	----------

UNSPSC

UNSPSC 21.0	39121000
-------------	----------

MINI MCR-EX-NAM-2T - Isolation switch amplifier



1157852

<https://www.phoenixcontact.com/in/products/1157852>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
	2,2',6,6'-tetrabromo-4,4'-isopropylidenediphenol(CAS: 79-94-7)
SCIP	2a5b527f-e640-4aa0-9fce-461e2a4c0656

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.
A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420
info@phoenixcontact.co.in