

EPC 1502 - Edge device



1185416
<https://www.phoenixcontact.com/us/products/1185416>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



PLCnext Industrial Edge Computer with Intel® Celeron® N3350 processor. This small form factor programmable edge device supports IEC 61131-3, MATLAB Simulink, C/C++, and is perfect for protocol converting, data collection, and cloud computing.

Your advantages

- Local output of visualizations via DisplayPort
- Seamless support in PLCnext Engineer for OT programming
- Connection to PROFICLOUD
- Connection to PLCnext Store, for installing e.g. Node-RED, InfluxDB or Docker-Portainer
- Numerous protocols supported such as: http, https, FTP, SNTP, SNMP, SMTP, SQL, MySQL, DCP, etc.
- Two independent Ethernet interfaces
- High-level programming languages: IEC61131-3, C/C++, MATLAB Simulink
- Consistent graphical programming interfaces

Commercial data

Item number	1185416
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR12
Product key	DRBABE
GTIN	4063151225339
Weight per piece (including packing)	750 g
Weight per piece (excluding packing)	585 g
Customs tariff number	84715000
Country of origin	TW

EPC 1502 - Edge device



1185416

<https://www.phoenixcontact.com/us/products/1185416>

Technical data

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Product properties

Product type	Controller
Product family	PLCnext Control
Type	Stand-alone

Computer data

Processor	Intel® Celeron® N3350 1.10 GHz
Trusted Platform Module	fTPM 1.2 (Encryption technology not Chinese)
RAM	2 GB LPDDR4
Data storage system	eMMC internal, 32 GB, ~15 GB useable
Cooling	passive

Display

Display type	none
--------------	------

System properties

Retentive data storage	Remanent data is not supported
Programmable under	High-level language
	IEC 61131-3

IEC 61131 runtime system

Program memory	8 Mbyte
Data storage system	12 Mbyte

Functionality

Programming languages supported	Instruction list (IL)
	Symbolic flowchart (SFC)
	Ladder diagram (LD)
	Function block diagram (FBD)
	Structured text (ST)
	C++
	C#
	Java
	Python®
	Simulink®

System requirements

Engineering tool	PLCnext Engineer
	Eclipse®

EPC 1502 - Edge device

1185416

<https://www.phoenixcontact.com/us/products/1185416>



	Visual Studio®
	MATLAB®/ Simulink®

Electrical properties

Supply

Supply voltage	24 V DC
----------------	---------

Interfaces

Interfaces	1x DP++ 2x USB 3.0
LAN chipset	Intel® I210-AT

Dimensions

External dimensions

Width / Height / Depth	99 mm / 92 mm / 46 mm
------------------------	-----------------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP30
Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Permissible humidity (operation)	5 % ... 85 % (non-condensing)
Shock	15g, 11 ms in accordance with IEC 60068-2-27
Vibration (operation)	1g, according to EN 60068-2-6

Approvals

Conformity/Approvals

Conformance	CE-compliant
FCC	Title 47 Part 15 Subpart B:2018 Class A

Mounting

Mounting type	DIN rail mounting Panel mounting
---------------	-------------------------------------

EPC 1502 - Edge device



1185416

<https://www.phoenixcontact.com/us/products/1185416>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1185416>



IECEE CB Scheme
Approval ID: US-39601-M1-UL



UL Listed
Approval ID: E238705 D12:D1050



cUL Listed
Approval ID: E238705 D12:D1050

EPC 1502 - Edge device



1185416
<https://www.phoenixcontact.com/us/products/1185416>

Classifications

ECLASS

ECLASS-13.0	19200102
ECLASS-15.0	19200102

ETIM

ETIM 9.0	EC001413
----------	----------

UNSPSC

UNSPSC 21.0	43211500
-------------	----------

EPC 1502 - Edge device



1185416

<https://www.phoenixcontact.com/us/products/1185416>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-15
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	d0a3fc16-3b7f-402f-b615-b65772b9a45c

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com