

# UNIFOX-PC VDE - Needle-nose pliers



1212205

<https://www.phoenixcontact.com/us/products/1212205>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Needle-nose pliers with blade, angled 45°, notched grip area, VDE 1000 V AC/1500 V DC tested

## Your advantages

- Individually tested safety tools according to DIN EN 60900 (VDE 0682-201)
- Notched gripping surface and sharp cutting edge
- Ergonomically shaped two-component handles for fatigue-free and non-slip use
- VDE tested

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1212205       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | BH31          |
| Product key                          | BH3162        |
| GTIN                                 | 4046356454216 |
| Weight per piece (including packing) | 202.48 g      |
| Weight per piece (excluding packing) | 200.5 g       |
| Customs tariff number                | 82032000      |
| Country of origin                    | DE            |

# UNIFOX-PC VDE - Needle-nose pliers



1212205

<https://www.phoenixcontact.com/us/products/1212205>

## Technical data

### Notes

#### Environmental Product Compliance

California Proposition 65

Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

### Product properties

|                  |                                                  |
|------------------|--------------------------------------------------|
| Product type     | Universal tools                                  |
| Application      | Aluminum                                         |
|                  | Copper                                           |
| Product property | Cutting edge is inductively hardened             |
|                  | Finely notched gripping surface                  |
|                  | Long narrow jaws                                 |
|                  | Ergonomic two-component handle                   |
|                  | Special tool steel, die-forged and oil-hardened\ |
|                  | VDE tested                                       |

### Dimensions

|        |        |
|--------|--------|
| Length | 170 mm |
|--------|--------|

### Material specifications

|       |       |
|-------|-------|
| Color | black |
|-------|-------|

### Cable/line

|                         |           |
|-------------------------|-----------|
| External cable diameter | ≤ 8.00 mm |
|-------------------------|-----------|

### Standards and regulations

|       |                                  |
|-------|----------------------------------|
| Tests | DIN EN 60900 (VDE 0682 PART 201) |
|       | DIN ISO 5745                     |

# UNIFOX-PC VDE - Needle-nose pliers



1212205

<https://www.phoenixcontact.com/us/products/1212205>

## Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212205>



**EAC**

Approval ID: RU x-DE.xx08.B.02974



**VDE approval of drawings**

Approval ID: 40052526

# UNIFOX-PC VDE - Needle-nose pliers



1212205

<https://www.phoenixcontact.com/us/products/1212205>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 21043816 |
| ECLASS-15.0 | 21043816 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC000835 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 27112100 |
|-------------|----------|

# UNIFOX-PC VDE - Needle-nose pliers



1212205  
<https://www.phoenixcontact.com/us/products/1212205>

## Environmental product compliance

|                                         |                                                                                     |
|-----------------------------------------|-------------------------------------------------------------------------------------|
| EU RoHS                                 |                                                                                     |
| Fulfills EU RoHS substance requirements | Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE |
| EU REACH SVHC                           |                                                                                     |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt%                                                          |

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)