

ANT-OMNI-2459-04 - Antenna

1284780

<https://www.phoenixcontact.com/us/products/1284780>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Multiband omnidirectional antenna for freely mobile applications, compact design, frequency band: 2.4 GHz / 5 GHz / 6 GHz, gain: 2.0 dBi / 2.5 dBi / 3.0 dBi, degree of protection: IP68/IP69K, shock- and vibration-resistant, connection: N (male)

Your advantages

- Compact design
- Ideally suited for freely mobile applications with 2.4 GHz, 5 GHz, or 6 GHz
- Universal use with the wide frequency range
- Shock- and vibration-resistant

Commercial data

Item number	1284780
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN23
Product key	DNN2Z1
GTIN	4063151490621
Weight per piece (including packing)	49.6 g
Weight per piece (excluding packing)	49.5 g
Customs tariff number	85177100
Country of origin	CN

ANT-OMNI-2459-04 - Antenna

1284780

<https://www.phoenixcontact.com/us/products/1284780>



Technical data

Notes

Note on application

Note on application

Only for industrial use

Product properties

Product type	Antenna
Radiation characteristics	Omnidirectional
Gain	1.5 dBi (1.7 GHz ... 2.0 GHz) 2 dBi (2.0 GHz ... 2.7 GHz) 1.5 dBi (2.7 GHz ... 4.2 GHz) 2.5 dBi (4.9 GHz ... 5.9 GHz) 3 dBi (5.9 GHz ... 7.1 GHz)
Polarization	Linear vertical

Electrical properties

Frequency band	2.4 GHz 5 GHz 6 GHz
Frequency range	1.7 GHz ... 7.1 GHz
Impedance	50 Ω
Maximum capacity	120.00 W
Voltage standing wave ratio VSWR in a 50 Ω system	≤ 2.00

Connection data

Connection technology	
Connection method	N (male)

Dimensions

Length	55 mm
Diameter	22 mm

Material specifications

Material	ASA, Acrylic ester styrene-acrylonitrile
Flammability rating according to UL 94	HB

Environmental and real-life conditions

Ambient conditions	
Degree of protection	IP68/IP69K
Ambient temperature (operation)	-40 °C ... 85 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C

ANT-OMNI-2459-04 - Antenna

1284780

<https://www.phoenixcontact.com/us/products/1284780>



Approvals

Electronic devices in rail vehicles

Shock (operation)	In accordance with EN 61373 (category 1, class B)
Vibration (operation)	In accordance with EN 61373 (category 1, class B)

Standards and regulations


Standards/specifications	EN 45545-2
Note	Fire protection on railway vehicles
Standards/specifications	EN 50155
Note	Railway application

Mounting

Mounting type	Control cabinet mounting
Assembly note	Accessories required Outdoors and indoors

Drawings

Schematic diagram



Installation example

ANT-OMNI-2459-04 - Antenna

1284780

<https://www.phoenixcontact.com/us/products/1284780>



Classifications

ECLASS

ECLASS-13.0	19070105
ECLASS-15.0	19070105

ETIM

ETIM 9.0	EC001698
----------	----------

UNSPSC

UNSPSC 21.0	43223100
-------------	----------

1284780

<https://www.phoenixcontact.com/us/products/1284780>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-25
An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.	

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	e4f5c4be-b3f1-4518-8b7d-aaa1b6c6cf23

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com