

# WP 6215-WHPS - Web panel

1290809

<https://www.phoenixcontact.com/us/products/1290809>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

IP66 Touch panel with 21.5-inch widescreen (16:9) HD, PCAP display, Software: Qt Browser



## Your advantages

- Easy startup – just enter the IP and URL
- Flexible, thanks to open web standard and free choice of web server and visualization software
- No security updates are required for JAVA or Flash plug-ins thanks to HTML5
- Ideal for use with PLCnext Engineer or CODESYS
- Embedded Linux operating system
- Visualization of self-programmed JavaScript applications possible

## Commercial data

Item number	1290809
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	DR17
Product key	DRCADF
GTIN	4063151523138
Weight per piece (including packing)	2,260 g
Weight per piece (excluding packing)	2,100 g
Customs tariff number	84714100
Country of origin	TW

# WP 6215-WHPS - Web panel

1290809

<https://www.phoenixcontact.com/us/products/1290809>



## Technical data

### Notes

Note on application

Note on application

Only for industrial use

### Product properties

Product type	Operator panel
Computer data	
Processor	Arm® Cortex®-A53, 1.6 GHz
Operating system	Yocto/Linux®
Data storage system	Flash eMMC, 8 GB
Slots	1x microSD

### Display

Display type	54.6 cm / 21.5"-TFT
Screen resolution	1920 x 1080 Pixel(s) (Full HD)
Touch technology	projective-capacitive (PCAP)
Display lighting type	LED
Brightness	400 cd/m², typical (adjustable)
MTBF	50000 h
Color spectrum	16.7 million colors
Reading angle left	89.00 °
Reading angle right	89.00 °
Reading angle top	89.00 °
Reading angle bottom	89.00 °

### Interfaces

Interfaces	2x USB 2.0
	1x USB 3.0, Typ C
	1x COM (RS-232/422/485)
Optional interfaces	Without optional interface
Network	1x Ethernet (10/100/1000 Mbps), RJ45
Bus system	without bus system

### System properties

User software	QT browser
System requirements	
Runtime system	Qt Browser

### Electrical properties

Service life of battery	5 years (typical)
-------------------------	-------------------

# WP 6215-WHPS - Web panel



1290809

<https://www.phoenixcontact.com/us/products/1290809>

## Supply

Supply voltage (DC)	24 V DC $\pm 20\%$
Supply voltage range	18 V DC ... 32 V DC
Power supply unit	24 V DC $\pm 20\%$
Max. current consumption	1.81 A (24 V DC)
Typical current consumption	1.37 A (24 V DC)

## Real-time clock

Realtime clock	Yes (battery-backed)
----------------	----------------------

## Mounting

Mounting type	Front mounting
---------------	----------------

## Material specifications

Material front plate	Aluminum (natural anodized)
Housing material	Aluminum cast alloy, powder-coated

## Connection data

Connection method	Screw connection
Conductor cross-section, rigid	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section, flexible	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section AWG	24 ... 12
Stripping length	7 mm

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP66 (front), IP20 (back)
Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 60 °C
Permissible humidity (operation)	10 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	10 % ... 95 % (non-condensing)
Vibration (operation)	1g

## Dimensions

### External dimensions

Width / Height / Depth	532 mm / 346 mm / 51 mm (Dimensions of the front plate)
------------------------	---

### Installation dimensions

Width / Height / Installation depth	522 mm / 336 mm / (Installation cutout)
-------------------------------------	---

# WP 6215-WHPS - Web panel

1290809

<https://www.phoenixcontact.com/us/products/1290809>



## Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1290809>



**IECEE CB Scheme**

Approval ID: US-39088-UL



**UL Listed**

Approval ID: E238705



**IECEE CB Scheme**

Approval ID: US-39088-UL



**UL Listed**

Approval ID: E238705

# WP 6215-WHPS - Web panel

1290809

<https://www.phoenixcontact.com/us/products/1290809>



## Classifications

### ECLASS

ECLASS-13.0	27330201
ECLASS-15.0	27330201

### ETIM

ETIM 9.0	EC001412
----------	----------

### UNSPSC

UNSPSC 21.0	43211900
-------------	----------

# WP 6215-WHPS - Web panel

1290809

<https://www.phoenixcontact.com/us/products/1290809>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-15
An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.	

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)