


VIOK 1,5-3D/PE-EX BU - Initiator/actuator terminal block



1043463

<https://www.phoenixcontact.com/us/products/1043463>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Initiator/actuator terminal block, nom. voltage: 400 V, nominal current: 24 A, connection method: Screw connection, 2nd, 3rd and 4th level, Rated cross section: 2.5 mm², cross section: 0.2 mm² - 4 mm², mounting type: NS 35/7,5, NS 35/15, color: blue

Commercial data

Item number	1043463
Packing unit	50 pc
Minimum order quantity	50 pc
Product key	BE1218
GTIN	4055626607481
Weight per piece (including packing)	27.36 g
Weight per piece (excluding packing)	25.36 g
Country of origin	PL

VIOK 1,5-3D/PE-EX BU - Initiator/actuator terminal block



1043463

<https://www.phoenixcontact.com/us/products/1043463>

Technical data

Product properties

Product type	Sensor/actuator terminal block
Number of connections	7
Number of rows	4

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Rated surge voltage	6 kV
Maximum power dissipation for nominal condition	0.77 W

Connection data

Number of connections per level	2
Nominal cross section	2.5 mm ²

2nd, 3rd and 4th level

Connection method	Screw connection
Screw thread	M3
Note	Please observe the current carrying capacity of the DIN rails.
Tightening torque	0.5 ... 0.6 Nm
Stripping length	8 mm
Internal cylindrical gage	A3
Connection in acc. with standard	IEC 60947-7-1/IEC 60947-7-2
Conductor cross-section rigid	0.2 mm ² ... 4 mm ²
Cross section AWG	24 ... 12 (converted acc. to IEC)
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section, flexible [AWG]	24 ... 14 (converted acc. to IEC)
Conductor cross-section flexible (ferrule without plastic sleeve)	0.25 mm ² ... 2.5 mm ²
Flexible conductor cross-section (ferrule with plastic sleeve)	0.25 mm ² ... 2.5 mm ²
Cross-section with insertion bridge, rigid	4 mm ²
Cross-section with insertion bridge, flexible	2.5 mm ²
Nominal current	24 A
Maximum load current	26 A (with a 2.5 mm ² conductor cross-section)
Nominal voltage	400 V (when using EB insertion bridges, the nominal voltage is reduced to 250 V.)
Nominal cross section	2.5 mm ²

Ex data

Rated data (ATEX/IECEx)

Identification	⊕ II 2 G Ex eb IIC Gb
----------------	-----------------------

VIOK 1,5-3D/PE-EX BU - Initiator/actuator terminal block



1043463

<https://www.phoenixcontact.com/us/products/1043463>

Operating temperature range	-50 °C ... 105 °C
Ex-certified accessories	1205053 SZS 0,6X3,5 1201442 E/UK
List of bridges	Insertion bridge / EB 2- DIK GY / 2715898 Insertion bridge / EB 2- DIK RD / 2716693 Insertion bridge / EB 2- DIK BU / 2716648 Insertion bridge / EB 3- DIK GY / 2715908 Insertion bridge / EB 3- DIK RD / 2716745 Insertion bridge / EB 3- DIK BU / 2716651 Insertion bridge / EB 10- DIK GY / 2715937 Insertion bridge / EB 10- DIK RD / 2716774 Insertion bridge / EB 10- DIK BU / 2716680
Bridge data	16 A / 2.5 mm ² ΔT 45 K
Ex temperature increase	37 K (20 A / 2.5 mm ²)
at bridging with insertion bridge	176 V
Rated insulation voltage	160 V
output	(Permanent)

Ex level General

Rated voltage	176 V
Rated current	20 A (ΔT 45 K)
Maximum load current	25 A (ΔT 45 K)

Ex connection data General

Torque range	0.5 Nm ... 0.6 Nm
Nominal cross section	2.5 mm ²
Rated cross section AWG	14
Connection capacity rigid	0.2 mm ² ... 4 mm ²
Connection capacity AWG	24 ... 12
Connection capacity flexible	0.2 mm ² ... 2.5 mm ²
Connection capacity AWG	24 ... 14
2 conductors with same cross section, solid	0.2 mm ² ... 1 mm ²
2 conductors with the same cross-section AWG rigid	24 ... 17
2 conductors with same cross section, stranded	0.2 mm ² ... 1 mm ²
2 conductors with the same cross-section AWG flexible	24 ... 17
output	(Permanent)

Ex level Level 1

Contact resistance	0.8 mΩ
output	(Permanent)

Ex level Level 2

Contact resistance	0.6 mΩ
output	(Permanent)

Ex level Level 3

VIOK 1,5-3D/PE-EX BU - Initiator/actuator terminal block



1043463

<https://www.phoenixcontact.com/us/products/1043463>

Contact resistance	0.5 mΩ
--------------------	--------

Dimensions

Width	6.2 mm
Height	82.5 mm
Depth on NS 35/7,5	70 mm
Depth on NS 35/15	77.5 mm

Material specifications

Color	blue (RAL 5015)
Flammability rating according to UL 94	V2
Insulating material group	I
Insulating material	PA

Mechanical properties

Mechanical data

Open side panel	No
-----------------	----

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

Standards and regulations

Connection in acc. with standard	IEC 60947-7-1/IEC 60947-7-2
----------------------------------	-----------------------------

Mounting

Mounting type	NS 35/7,5
	NS 35/15

VIOK 1,5-3D/PE-EX BU - Initiator/actuator terminal block




1043463

<https://www.phoenixcontact.com/us/products/1043463>

Drawings

Circuit diagram



VIOK 1,5-3D/PE-EX BU - Initiator/actuator terminal block



1043463

<https://www.phoenixcontact.com/us/products/1043463>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1043463>



EAC Ex

Approval ID: RU C-DE.Ax07.B.03227



EAC Ex

Approval ID: KZ 7500525010101950



ATEX

Approval ID: SEV23ATEX0682U

VIOK 1,5-3D/PE-EX BU - Initiator/actuator terminal block



1043463

<https://www.phoenixcontact.com/us/products/1043463>

Classifications

ECLASS

ECLASS-13.0	27250112
ECLASS-15.0	27250112

ETIM

ETIM 9.0	EC000900
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

VIOK 1,5-3D/PE-EX BU - Initiator/actuator terminal block



1043463

<https://www.phoenixcontact.com/us/products/1043463>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com