

EV-CC-AC1-M3-CC-SER-HS-MSTB - AC charging controller



1081335

<https://www.phoenixcontact.com/us/products/1081335>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The EV-CC-AC1-M3-CBC-SER-HS-MSTB charging controller with housing for DIN rail mounting and plug-in connection technology is used to charge electric vehicles on the 3-phase AC power grid in accordance with IEC 61851-1, mode 3. Optimized for charging stations with permanently mounted vehicle charging connector. All charging functions and comprehensive configuration settings are already integrated.

Commercial data

Item number	1081335
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	EM01
Product key	XWBRAA
GTIN	4055626807652
Weight per piece (including packing)	373.3 g
Weight per piece (excluding packing)	257 g
Customs tariff number	85371098
Country of origin	DE

EV-CC-AC1-M3-CC-SER-HS-MSTB - AC charging controller



1081335

<https://www.phoenixcontact.com/us/products/1081335>

Technical data

Product properties

Product type	AC charging controller
Product family	CHARX control basic
Application	AC charging controller for private and commercial applications (EU/CN)
Operating mode	Stand-Alone
Number of charging points	1
Charging mode	Mode 3, Case C

System properties

Charging controllers

Number of charging points	1
---------------------------	---

Electrical properties

Type of charging current	AC
Current consumption	< 1 W
Note on the connection method	with MSTB connection

Supply

Supply voltage	230 V
Supply voltage range	100 V AC ... 240 V AC (nominal voltage range)
Max. current consumption	40 mA
Nominal power consumption	< 1 W (No-load)
Frequency range	50 Hz ... 60 Hz

Input data

Digital

Number of digital inputs	5
Frequency range	50 Hz ... 60 Hz
Nominal power consumption	< 0.5 W (No-load)
Nominal current I_N	≤ 1 mA
Nominal input voltage U_N	12 V
Input voltage range U1	0 V ... 3 V (Off)
Input voltage range U2	9 V ... 15 V (On)

Output data

Digital

Output name	4 digital outputs
Connection technology	Spring-cage connection
Maximum output voltage	30 V
Maximum output current	0.5 A (Total current for all outputs; internally supplied)

EV-CC-AC1-M3-CC-SER-HS-MSTB - AC charging controller



1081335

<https://www.phoenixcontact.com/us/products/1081335>

	0.6 A (Per output; externally supplied)
--	---

Switching

Output name	Relay output C _{1,2}
Minimum switching power	1500 VA
Maximum switching voltage	250 V AC (External supply)
Max. switching current	6 A

Connection data

Conductor connection

Connection method	plug-in push-in spring connection
Conductor cross-section rigid	0.2 mm ² ... 2.5 mm ²
Conductor cross-section flexible	0.2 mm ² ... 1.5 mm ²
Conductor cross-section AWG	24 ... 16

Interfaces

Interface	RS-485
-----------	--------

RS-485

Interface	RS-485 2-wire
Bus system	RS-485
Connection method	Pluggable spring-cage terminal blocks
Number of interfaces	1
Transmission speed	9.6 kbps (Standard)
Transmission speed range	9.6 kbps ... 19.2 kbps (adjustable)
Data flow control/protocols	Modbus/RTU (slave)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-35 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Permissible humidity (operation)	30 % ... 95 %

Approvals

Conformity/Approvals

Conformance	CE-compliant
-------------	--------------

Standards and regulations

Standards

Standards/regulations	IEC 61851-1
-----------------------	-------------

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

EV-CC-AC1-M3-CC-SER-HS-MSTB - AC charging controller



1081335
<https://www.phoenixcontact.com/us/products/1081335>

Mounting position	any
-------------------	-----

EV-CC-AC1-M3-CC-SER-HS-MSTB - AC charging controller



1081335
<https://www.phoenixcontact.com/us/products/1081335>

Classifications

ECLASS

ECLASS-13.0	27144703
ECLASS-15.0	27144703

ETIM

ETIM 9.0	EC002889
----------	----------

UNSPSC

UNSPSC 21.0	39121800
-------------	----------

EV-CC-AC1-M3-CC-SER-HS-MSTB - AC charging controller



1081335

<https://www.phoenixcontact.com/us/products/1081335>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-10
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
	2,2',6,6'-tetrabromo-4,4'-isopropylidenediphenol(CAS: 79-94-7)

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com