

VS-MP-PPC/PPC-PO - Coupling



1403684

<https://www.phoenixcontact.com/us/products/1403684>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Coupling, design: Version 14, degree of protection: IP65, material: Metal, connection method: Coupling, color: black

Product description

Push/pull power and data coupling; version 14

Commercial data

Item number	1403684
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB17
Product key	ABNOGA
GTIN	4046356664332
Weight per piece (including packing)	256.5 g
Weight per piece (excluding packing)	183.146 g
Customs tariff number	85366990
Country of origin	DE

Technical data

Product properties

Product type	Network distributor box
Type	Version 14
Connection profile	Power
Number of slots	1

Electrical properties

Nominal voltage U_N	24 V
Nominal current I_N	16 A
Transmission medium	Copper

Connection data

Connection technology

Connection method	Coupling
-------------------	----------

Dimensions

Width	42 mm
Height	51 mm
Length	115 mm

Material specifications

Color	black
Housing material	Metal

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≤ 100 (Power)
-----------------------------	--------------------

Environmental and real-life conditions


Ambient conditions

Degree of protection	IP65
Ambient temperature (operation)	-40 °C ... 70 °C

Mounting

Mounting type	Screw mounting
---------------	----------------

Drawings



VS-MP-PPC/PPC-PO - Coupling



1403684

<https://www.phoenixcontact.com/us/products/1403684>

Classifications

ECLASS

ECLASS-13.0	27061801
ECLASS-15.0	27440325

ETIM

ETIM 9.0	EC003249
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

VS-MP-PPC/PPC-PO - Coupling



1403684

<https://www.phoenixcontact.com/us/products/1403684>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol(CAS: 119-47-1)
SCIP	4a65bb11-4b13-47f6-9359-86ba20b0b4b7

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com