

SAC-4P-M8MS/ 0,5-542/M12FR BK - Sensor/actuator cable



1406200

<https://www.phoenixcontact.com/us/products/1406200>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 4-position, PVC, yellow, Plug straight M8, on Socket angled M12 SPEEDCON, coding: A, cable length: 0.5 m

Commercial data

Item number	1406200
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	BF13
Product key	AF1ICB
GTIN	4046356798501
Weight per piece (including packing)	28.3 g
Weight per piece (excluding packing)	28.3 g
Customs tariff number	85444290
Country of origin	US

SAC-4P-M8MS/ 0,5-542/M12FR BK - Sensor/actuator cable



1406200

<https://www.phoenixcontact.com/us/products/1406200>

Technical data

Product properties

Product type	Sensor/actuator cable
Application	Standard, U.S. cables
Number of positions	4
No. of cable outlets	1
Shielded	no
Coding	A

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Material specifications

Flammability rating according to UL 94	HB
Seal material	NBR
Material of grip body	TPU, hardly inflammable, self-extinguishing
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Material for screw connection	Zinc die-cast, nickel-plated
Outer sheath, material	PVC

Electrical properties

Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	48 V AC
	60 V DC
Nominal current I_N	4 A

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 100
-----------------------------	------------

Signaling

Status display	no
Status display present	no

Connection data

Conductor connection

Tightening torque	0.4 Nm (M12 connector)
	0.2 Nm (M8 connectors)

SAC-4P-M8MS/ 0,5-542/M12FR BK - Sensor/actuator cable



1406200

<https://www.phoenixcontact.com/us/products/1406200>

Connector

Connection 1

Type	Plug straight M8
Number of positions	4


Connection 2

Type	Socket angled M12 SPEEDCON
Number of positions	4
Locking type	SPEEDCON
Coding type	A

Cable/line

Cable length	0.5 m
--------------	-------

PVC yellow 105 °C [542]

Dimensional drawing	
Cable weight	25 kg/km
UL AWM Style	2517 (105 °C / 300 V)
Number of positions	4
Shielded	no
Cable type	PVC yellow 105 °C [542]
Conductor structure signal line	7x 0.20 mm
AWG signal line	24
Wire diameter incl. insulation	1.12 mm ±0.03 mm
External cable diameter	4.40 mm ±0.2 mm
Outer sheath, material	PVC
External sheath, color	yellow
Conductor material	Tin-plated Cu litz wires
Material wire insulation	PVC
Single wire, color	brown, blue, black, white
Overall twist	4 wires, twisted
Max. conductor resistance	max. 79.7 Ω/km (20 °C)
Insulation resistance	≥ (550 M Ohms/m @ 500V)
Nominal voltage, cable	300 V
Minimum bending radius, flexible installation	8 x D
Smallest bending radius, movable installation	36 mm

SAC-4P-M8MS/ 0,5-542/M12FR BK - Sensor/actuator cable



1406200

<https://www.phoenixcontact.com/us/products/1406200>

Flame resistance	FT4
Other resistance	UV resistant
Ambient temperature (operation)	-30 °C ... 105 °C (cable, fixed installation)
	-5 °C ... 105 °C (Cable, flexible installation)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
	IP67
	IP68
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 90 °C (Plug / socket)
Ambient temperature (operation) (Cable, fixed installation)	-40 °C ... 80 °C (cable, fixed installation)
Ambient temperature (operation) (Cable, flexible installation)	-5 °C ... 80 °C (Cable, flexible installation)

Standards and regulations

Standard designation	M12 connector
Standards/specifications	IEC 61076-2-101
Standard designation	M8 connector
Standards/specifications	IEC 61076-2-104


SAC-4P-M8MS/ 0,5-542/M12FR BK - Sensor/actuator cable

1406200

<https://www.phoenixcontact.com/us/products/1406200>


Drawings

Dimensional drawing



M8 x 1 male plug, straight version

Dimensional drawing




M12 x 1 socket, angled

SAC-4P-M8MS/ 0,5-542/M12FR BK - Sensor/actuator cable

1406200

<https://www.phoenixcontact.com/us/products/1406200>

Schematic diagram




Pin assignment M8 plug, 4-pos., view male side

SAC-4P-M8MS/ 0,5-542/M12FR BK - Sensor/actuator cable

1406200


<https://www.phoenixcontact.com/us/products/1406200>

Schematic diagram



Pin assignment M12 socket, 4-pos., A-coded, view female side

Circuit diagram



Contact assignment of M8 plugs / M12 sockets

SAC-4P-M8MS/ 0,5-542/M12FR BK - Sensor/actuator cable



1406200
<https://www.phoenixcontact.com/us/products/1406200>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1406200>

 UL Listed Approval ID: FILE E 221474				
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
keine				
	30 V	4 A	-	-

 cUL Listed Approval ID: FILE E 221474				
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
keine				
	30 V	4 A	-	-

SAC-4P-M8MS/ 0,5-542/M12FR BK - Sensor/actuator cable



1406200

<https://www.phoenixcontact.com/us/products/1406200>

Classifications

ECLASS

ECLASS-13.0	27060311
ECLASS-15.0	27060311

ETIM

ETIM 9.0	EC001855
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

SAC-4P-M8MS/ 0,5-542/M12FR BK - Sensor/actuator cable



1406200
<https://www.phoenixcontact.com/us/products/1406200>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%
EF3.0 Climate Change	
CO2e kg	0.225 kg CO2e

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com