

ECM-UC-100A-UI - Current measuring transducer



1136513

<https://www.phoenixcontact.com/us/products/1136513>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Current measuring transducers for measuring AC, DC, and distorted currents. Configuration via USB-C interface via the web server (without 24 V DC). Current measuring ranges: 0 A ... 125 A. Standard configuration, Push-in connection

Commercial data

Item number	1136513
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	C444
Product key	CMMA34
GTIN	4063151072810
Weight per piece (including packing)	141.2 g
Weight per piece (excluding packing)	141.2 g
Customs tariff number	85437090
Country of origin	DE

ECM-UC-100A-UI - Current measuring transducer

1136513

<https://www.phoenixcontact.com/us/products/1136513>



Technical data

Product properties

Product type	Current measuring transducer
Insulation characteristics	
Insulation	Safe isolation in accordance with IEC/EN 61010-1
Overvoltage category	III (300 V)
Pollution degree	2

Electrical properties

Step response (10-90%)	200 ms (AC/DC) 20 ms (DC)
Maximum temperature coefficient	< 0.02 %/K
Maximum transmission error	0.5 % (of nominal range value under nominal conditions)
Rated insulation voltage	300 V AC (to earth)

Electrical isolation IEC 61010-2-030

Standards/regulations	IEC 61010-2-030
Measuring category	III (300 V)

Electrical isolation Input/output

Test voltage	4 kV AC (50 Hz, 60 s)
--------------	-----------------------

Electrical isolation Input/power supply

Test voltage	4 kV AC (50 Hz, 60 s)
--------------	-----------------------

Electrical isolation Output/power supply

Test voltage	2 kV AC (50 Hz, 60 s)
--------------	-----------------------

Supply

Nominal supply voltage	24 V DC
Nominal supply voltage range	12 V DC ... 24 V DC -20 % ... +25 %
Supply voltage range	9.6 V DC ... 30 V DC
Power consumption	≤ 2 W (30 V DC)

Input data

Signal: digital

Voltage input signal	0 V DC ... 30 V DC
Current input signal	2 mA ... 15 mA

Measurement

Input current range	0 A AC ... 100 A AC -100 A DC ... 100 A DC
Measuring range	0 A AC/DC ... 50 A AC/DC
Setting range for min. input current	0 A AC/DC ... 9.4 A AC/DC

ECM-UC-100A-UI - Current measuring transducer



1136513

<https://www.phoenixcontact.com/us/products/1136513>

	0 A AC/DC ... 18.8 A AC/DC
Setting range for max. input current	0 A AC/DC ... 62.5 A AC/DC (DIN/EN 61010-1)
	0 A AC/DC ... 125 A AC/DC (DIN/EN 61010-1)
	-125 A DC ... 125 A DC (DIN/EN 61010-1)
Overload capacity	2 x I_N (continuous), depending on the fed-through conductor
Surge strength	20 x I_N (1 s), depending on the fed-through conductor
Frequency measuring range	0 Hz
	10 Hz ... 100 Hz
	10 Hz ... 200 Hz
	10 Hz ... 500 Hz
	10 Hz ... 1000 Hz
Curve type	AC, DC or distorted currents

Output data

Signal: Voltage/current

Voltage output signal	0 V ... 10 V
	0 V ... 5 V
	1 V ... 5 V
	2 V ... 10 V
	-10 V ... 10 V
	-5 V ... 5 V
	10 V ... -10 V
	5 V ... -5 V
	10 V ... 0 V
	5 V ... 0 V
Current output signal	0 mA ... 20 mA
	4 mA ... 20 mA
	20 mA ... 0 mA
	20 mA ... 4 mA
Load/output load voltage output	> 10 kΩ
Load/output load current output	< 500 Ω

Connection data

Connection method	Push-in connection
Stripping length	10 mm
Conductor cross-section rigid	0.2 mm ² ... 2.5 mm ²
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section AWG	24 ... 13

Circular conductor

Conductor cross-section rigid	25 mm ²
Conductor cross-section AWG	3

Interfaces

ECM-UC-100A-UI - Current measuring transducer



1136513

<https://www.phoenixcontact.com/us/products/1136513>

WBM

Designation	WBM: Default address, USB-C interface
IP address	192.168.128.1

Dimensions

Item dimensions

Width	22.6 mm
Height	106.7 mm
Depth	113.8 mm
Depth (Device depth (DIN rail mounting))	114.5 mm (Snapped onto DIN rail NS 35/7,5 in accordance with EN 60715)

Circular conductor

Diameter	11 mm
----------	-------

Material specifications

Color	gray (RAL 7042)
Flammability rating according to UL 94	V0 (Housing)
Housing material	PA 6.6-FR

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 60 °C -40 °F ... 140 °F
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Altitude	≤ 4000 m
Permissible humidity (operation)	≤ 95 % (non-condensing)

Approvals

CE

Certificate	CE-compliant
-------------	--------------

UKCA

Certificate	UKCA-compliant
-------------	----------------

UL, USA/Canada

Identification	Ind. Cont. Eq. E238705-E196811
----------------	--------------------------------

EMC data

Electromagnetic compatibility	Conformance with EMC directive
Low Voltage Directive	Conformance with Low Voltage Directive
Noise immunity	EN 61000-6-2

Noise emission

ECM-UC-100A-UI - Current measuring transducer

1136513

<https://www.phoenixcontact.com/us/products/1136513>



Standards/regulations	EN 61000-6-4
-----------------------	--------------

Standards and regulations

Standards/regulations	IEC 61010-1
Standards/regulations	IEC/EN 61131-2 (type 3)
Standards/regulations	IEC/EN 61131-2 (type 3)

Mounting

Mounting position	vertical or horizontal
-------------------	------------------------

Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1136513>



cULus Listed

Approval ID: E238705



cULus Listed

Approval ID: E196811



cULus Listed

Approval ID: E196811

ECM-UC-100A-UI - Current measuring transducer

1136513

<https://www.phoenixcontact.com/us/products/1136513>



Classifications

ECLASS

ECLASS-13.0	27210123
ECLASS-15.0	27210123

ETIM

ETIM 9.0	EC002475
----------	----------

UNSPSC

UNSPSC 21.0	39121000
-------------	----------

ECM-UC-100A-UI - Current measuring transducer

1136513

<https://www.phoenixcontact.com/us/products/1136513>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.	

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1) 2,2',6,6'-tetrabromo-4,4'-isopropylidenediphenol(CAS: 79-94-7)
-------------------------------------	--

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com