

NBC-M12MSD/ 2,0-93F/M12FSD - Network cable



1192145

<https://www.phoenixcontact.com/us/products/1192145>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Network cable, Ethernet CAT5e (100 Mbps), 4-position, TPE, highly flexible, turquoise, shielded, Plug straight M12, coding: D / IP65, on Socket straight M12, coding: D / IP65, cable length: 2 m

Commercial data

Item number	1192145
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	BF15
Product key	AF1IHC
GTIN	4063151343651
Weight per piece (including packing)	22.22 g
Weight per piece (excluding packing)	22.22 g
Customs tariff number	85444290
Country of origin	US

Technical data

Product properties

Product type	Data cable preassembled
Application	Standard, U.S. cables
Sensor type	Ethernet
Number of positions	4
Shielded	yes
Coding	D

Interfaces

Bus system	Ethernet
Signal type/category	Ethernet CAT5e, 100 Mbps

Signaling

Status display	no
Status display present	no

Electrical properties

Nominal voltage U_N	48 V AC
	60 V DC
Nominal current I_N	4 A (Plug/socket in accordance with IEC 61076-2-101, cable technical data is to be observed)
Transmission medium	Copper
Transmission speed	100 Mbps

Connector

Connection 1

Type	Plug straight M12 / IP65
Coding type	D (Data)
Material	CuSn (Contact)
	Ni/Au (Contact surface)
	PA (Contact carrier)
	TPU, hardly inflammable, self-extinguishing (Grip body)
	Zinc die-cast, nickel-plated (Screw connection)
	FKM (Seal)
Degree of protection	IP65

Connection 2

Type	Socket straight M12 / IP65
Coding type	D (Data)
Material	CuSn (Contact)
	Ni/Au (Contact surface)
	PA (Contact carrier)

NBC-M12MSD/ 2,0-93F/M12FSD - Network cable



1192145

<https://www.phoenixcontact.com/us/products/1192145>

	TPU, hardly inflammable, self-extinguishing (Grip body)
	Zinc die-cast, nickel-plated (Screw connection)
	FKM (Seal)
Degree of protection	IP65

Cable/line

Cable length	2 m
--------------	-----

Highly flexible Ethernet CAT5e [93F]

Dimensional drawing		
UL AWM Style	2463 (80 °C / 600 V)	
Number of positions	4	
Shielded	yes	
Cable type	Highly flexible Ethernet CAT5e [93F]	
Conductor structure	2x2xAWG24/7, SF/UTP	
Conductor structure signal line	7x 0.20 mm (7x32)	
AWG signal line	24	
Conductor cross section	2x 2x 0.2 mm ²	
Wire diameter incl. insulation	1.2 mm	
External cable diameter	6.70 mm ±0.25 mm	
Outer sheath, material	TPE	
External sheath, color	turquoise	
Conductor material	Tin-plated Cu litz wires	
Material wire insulation	PE	
Single wire, color	white/orange-orange, white/green-green	
Twisted pairs	2 cores to the pair	
Overall twist	2 pairs to the core	
Optical shield covering	75 %	
Wave impedance	100 Ω ±15 Ω (at 100 MHz)	
Cable impedance	100 Ω ±15 Ω (at 1 ... 100 MHz)	
Nominal voltage, cable	600 V	
Test voltage	2000 V	
Dynamic load capacity (bending)	Max. bending cycles: 1000000, Bending radius: 10 x D, Traversing path: 0.23 m, Traversing rate: 1.5 m/s, Acceleration: 20.5 m/s ²	
	Max. bending cycles: 20000000, Bending radius: 20 X D (126 cycles/min. at 20 °C)	
Dynamic load capacity (torsion)	Torsion: 360 °/m (1 lb. load), Torsion cycles: 3000000, Torsional	

NBC-M12MSD/ 2,0-93F/M12FSD - Network cable



1192145

<https://www.phoenixcontact.com/us/products/1192145>

	frequency: 71 cycles/min, Ambient temperature (operation): 20 °C
Near end crosstalk attenuation (NEXT)	50 dB (with 100 MHz (IEC 62153-4-9))
Return attenuation (RL)	20 dB (at 10 MHz (+6LOG))
	26 dB (at 20 MHz)
	26 dB (at 100 MHz (-5LOG))
Flame resistance	VW-1
Other resistance	Resistant to welding splashes (Abrasion and oil resistance)
	UV resistant (CMX outdoor)
Ambient temperature (operation)	-40 °C ... 80 °C (Cable, flexible installation)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
	IP65
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 85 °C (M12 connector)


Standards and regulations

M12

Standard designation	M12 connector
Standards/specifications	IEC 61076-2-101

Drawings

Dimensional drawing




Plug, M12 x 1, straight, shielded

Dimensional drawing




M12 x 1 socket, straight, shielded

Schematic diagram



Pin assignment M12 male connector, 4-pos., D-coded, male side

Schematic diagram




Pin assignment M12 socket, 4-pos., D-coded, female side

1192145

<https://www.phoenixcontact.com/us/products/1192145>

Circuit diagram



Contact assignment of the M12 connector and the M12 socket

NBC-M12MSD/ 2,0-93F/M12FSD - Network cable



1192145

<https://www.phoenixcontact.com/us/products/1192145>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1192145>

 UL Listed Approval ID: FILE E 335024				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	60 V	1.5 A	-	-

 cUL Listed Approval ID: File E335024				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	60 V	1.5 A	-	-

Classifications

ECLASS

ECLASS-13.0	27060307
ECLASS-15.0	27060307

ETIM

ETIM 9.0	EC001855
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------