

# NBC-R4QC/5,0-93B/R4QC - Network cable



1408977

<https://www.phoenixcontact.com/us/products/1408977>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Assembled PROFINET cable, CAT5e, shielded, star quad, AWG 22 stranded (7-wire), RAL 6018 (yellow-green), RJ45 plug/IP67 push-pull plastic housing on RJ45 plug/IP67 push-pull plastic housing, line, length: 5 m

## Your advantages

- Compact angle
- Perfect for industrial applications
- PVC cable for flexible installations
- Worldwide approval with CE, UL, WEEE, and EAC
- Secure connection and disconnection with reliable locking clip protection
- Ideal EMC properties, thanks to 360° shielding
- Simultaneous power transmission with PoE++
- Resistant to shock and vibrations, thanks to robust molding
- High-speed data transmission with up to 1 Gbps (CAT5)

## Commercial data

Item number	1408977
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	AB11
Product key	ABNABA
GTIN	4046356857055
Weight per piece (including packing)	402.9 g
Weight per piece (excluding packing)	402.9 g
Customs tariff number	85444210
Country of origin	PL

# NBC-R4QC/5,0-93B/R4QC - Network cable

1408977

<https://www.phoenixcontact.com/us/products/1408977>



## Technical data

### Product properties

Product type	Data cable preassembled
Product family	RJ45 INDUSTRIAL PN4 CAT5
Sensor type	PROFINET
Number of positions	4
Number of slots	1
Shielded	yes

### Insulation characteristics

Overvoltage category	I
Degree of pollution	2

### Signaling

Status display	no
Status display present	no

### Electrical properties

Rated voltage (III/3)	72 V (DC)
Nominal voltage $U_N$	48 V
Nominal current $I_N$	1 A
Transmission medium	Copper
Transmission speed	100 Mbps
Transmission characteristics (category)	CAT5 (IEC 11801:2002)
Transmission speed	100 Mbps
Wave impedance	100 $\Omega$

### Material specifications

Color	black
Flammability rating according to UL 94	V0
Outer sheath, material	PVC
Conductor material	Tin-plated Cu litz wires

### Connector

#### Connection 1

Type	Plug straight RJ45
Locking type	Push Pull
Handle color	black
Material	CuSn (Contact) Ni/Au (Contact surface) PC (Contact carrier) PA GF (Housing)
Insertion/withdrawal cycles	$\geq 750$

# NBC-R4QC/5,0-93B/R4QC - Network cable

1408977

<https://www.phoenixcontact.com/us/products/1408977>



Degree of protection	IP67
Ambient temperature (operation)	-40 °C ... 70 °C

## Connection 2

Type	Plug straight RJ45
Locking type	Push Pull
Handle color	black
Material	CuSn (Contact) Ni/Au (Contact surface) PC (Contact carrier) PA GF (Housing)
Insertion/withdrawal cycles	≥ 750
Degree of protection	IP67
Ambient temperature (operation)	-40 °C ... 70 °C

## Cable/line

Cable length	5.00 m
--------------	--------

PROFINET PVC stranded CAT5 [93B]

### Dimensional drawing



UL AWM Style	21695 (80 °C / 600 V)
Number of positions	4
Shielded	yes
Cable type	PROFINET PVC stranded CAT5 [93B]
Conductor structure	1x4xAWG22/7, SF/TQ
AWG signal line	22
Conductor cross section	4x 0.34 mm <sup>2</sup>
Wire diameter incl. insulation	1.5 mm ±0.1 mm
External cable diameter	6.50 mm ±0.2 mm
Outer sheath, material	PVC
External sheath, color	green RAL 6018
Conductor material	Tin-plated Cu litz wires
Material wire insulation	PE
Single wire, color	white, yellow, blue, orange
Overall twist	Star quad
Optical shield covering	85 %
Insulation resistance	≥ 5 GΩ*km
Loop resistance	≤ 120.00 Ω/km

# NBC-R4QC/5,0-93B/R4QC - Network cable

1408977

<https://www.phoenixcontact.com/us/products/1408977>



Wave impedance	100 $\Omega$ $\pm 5 \Omega$ (at 100 MHz)
Nominal voltage, cable	$\leq 600 \text{ V}$
Test voltage Core/Core	2000 V ((50 Hz/1 min))
Test voltage Core/Shield	2000.00 V ((50 Hz/1 min))
Minimum bending radius, fixed installation	4 x D
Minimum bending radius, flexible installation	8 x D
Flame resistance	UL 1581, Section 1060 and UL 2556, Section 9.3 (FT1) UL 1685 (CSA FT 4) UL 1581, Section 1100 and UL 2556, Section 9.1 (HFT/FT2)
Resistance to oil	OIL RES I according to UL 2256
Other resistance	UV resistant (according to UL 1581, Section 1200)
Ambient temperature (operation)	-40 $^{\circ}\text{C}$ ... 80 $^{\circ}\text{C}$ (cable, fixed installation) -10 $^{\circ}\text{C}$ ... 70 $^{\circ}\text{C}$ (Cable, flexible installation)

## Environmental and real-life conditions

Ambient conditions

Degree of protection IP65/IP67

## Standards and regulations

Standards/specifications IEC PAS 61076-3-117

# NBC-R4QC/5,0-93B/R4QC - Network cable


1408977

<https://www.phoenixcontact.com/us/products/1408977>



## Drawings

Schematic diagram



Connector pin assignment plug RJ45


# NBC-R4QC/5,0-93B/R4QC - Network cable

1408977

<https://www.phoenixcontact.com/us/products/1408977>



Circuit diagram



Contact assignment of RJ45 plugs

# NBC-R4QC/5,0-93B/R4QC - Network cable



1408977

<https://www.phoenixcontact.com/us/products/1408977>

## Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1408977>



**EAC**

Approval ID: 19060508

# NBC-R4QC/5,0-93B/R4QC - Network cable

1408977

<https://www.phoenixcontact.com/us/products/1408977>



## Classifications

### ECLASS

ECLASS-13.0	27060307
ECLASS-15.0	27060307

### ETIM

ETIM 9.0	EC001855
----------	----------

### UNSPSC

UNSPSC 21.0	26121600
-------------	----------

# NBC-R4QC/5,0-93B/R4QC - Network cable

1408977

<https://www.phoenixcontact.com/us/products/1408977>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol(CAS: 119-47-1)
	2-(2H-benzotriazol-2-yl)-4-(1,1,3,3-tetramethylbutyl)phenol (UV-329)(CAS: 3147-75-9)
SCIP	8d688244-7c11-469f-af52-a7548c891d6f

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

### Phoenix Contact USA

586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)