

# CK2,5-M-6 AG - Crimp contact



1409209

<https://www.phoenixcontact.com/us/products/1409209>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Crimp contact, series: PRC 35, Pin, rated current: 32 A, contact material: CuZn



## Product description

Pin contact for PRC device connectors

## Your advantages

- Crimp contacts for PRC device connectors for assembly
- 3 variants for wire cross sections of 2.5 / 4.0 / 6.0 mm<sup>2</sup>

## Commercial data

Item number	1409209
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	AB03
Product key	ABLCEA
GTIN	4046356864480
Weight per piece (including packing)	2.333 g
Weight per piece (excluding packing)	2.26 g
Customs tariff number	85366990
Country of origin	DE

## Technical data

### Notes

Notes on operation	Crimp the wire with the crimp contact in accordance with DIN EN 60352-2
Note on application	Please remove the crimping pliers locator

### Safety note

Safety note	<ul style="list-style-type: none"><li>• <b>WARNING:</b> Commission properly functioning products only. The products must be regularly inspected for damage. Decommission defective products immediately. Replace damaged products. Repairs are not possible.</li><li>• <b>WARNING:</b> Only electrically qualified personnel may install and operate the product. They must observe the following safety notes. The qualified personnel must be familiar with the basics of electrical engineering. They must be able to recognize and prevent danger. The relevant symbol on the packaging indicates that only personnel familiar with electrical engineering are allowed to install and operate the product.</li><li>• <b>WARNING:</b> The connectors may not be plugged in or disconnected under load. Ignoring the warning or improper use may damage persons and/or property.</li><li>• Assembled products may not be manipulated or improperly opened.</li><li>• Only use mating connectors that are specified in the technical data of the standards listed (e.g. the ones listed in the product accessories online at <a href="https://www.phoenixcontact.com/products">phoenixcontact.com/products</a>).</li><li>• When using the product in direct connection with third-party manufacturers, the user is responsible.</li><li>• For operating voltages &gt; 50 V AC, conductive connector housings must be grounded</li><li>• Ensure that the protective or functional ground has been properly connected.</li><li>• VDE 0100/1.97 § 411.1.3.2 and DIN EN 60 204/11.98 § 14.1.3 are applicable when combining several circuits in a cable and/or connector</li><li>• Observe the corresponding technical data. You will find information:<ul style="list-style-type: none"><li>◦ On the product</li><li>◦ On the packing label</li><li>◦ In the supplied documentation</li><li>◦ Online at <a href="https://www.phoenixcontact.com/products">phoenixcontact.com/products</a> under the product</li></ul></li><li>• Only use tools recommended by Phoenix Contact</li><li>• The installation notes/Design In documents online on the download page at <a href="https://www.phoenixcontact.com/products">phoenixcontact.com/products</a> must be observed for this product.</li><li>• Use a protective cap to protect connectors that are not in use. The suitable accessories are available online in the accessory section of the product at <a href="https://www.phoenixcontact.com/products">phoenixcontact.com/products</a></li><li>• Operate the connector only when it is fully plugged in.</li><li>• Operate the connector only when it is fully plugged in and interlocked.</li></ul>
-------------	---

# CK2,5-M-6 AG - Crimp contact

1409209

<https://www.phoenixcontact.com/us/products/1409209>



- Ensure that when laying the cable, the tensile load on the connectors does not exceed the upper limit specified in the standards.
- Observe the minimum bending radius of the cable. Lay the cable without twisting it.
- The connector warms up in normal operation. Depending on the ambient conditions, the surface of the connector can continue to warm up. In this case, the user is responsible for posting warnings (e.g. DIN EN ISO 13732-1:2008-12).

## Product properties

Product type	Crimp contact
Series	PRC 35

## Connection data

### Connection technology

Contact connection type	Pin
Connection method	Crimp connection

## Material specifications

Material Contact	CuZn (Contact material, Pb < 0.1)
Material Contact surface	Ag
Flammability rating according to UL 94	V0

## Dimensions

Width [w]	5.3 mm
Height [h]	31.2 mm
Length [l]	5.3 mm

## Electrical properties

Rated current	32 A (in accordance with IEC 61535)
---------------	-------------------------------------

## Mechanical properties

Mechanical data	
Insertion/withdrawal cycles	100

## Environmental and real-life conditions

Ambient conditions	
Ambient temperature (assembly)	5 °C ... 85 °C

# CK2,5-M-6 AG - Crimp contact

1409209

<https://www.phoenixcontact.com/us/products/1409209>



## Classifications

### ECLASS

ECLASS-13.0	27440691
ECLASS-15.0	27440691

### ETIM

ETIM 9.0	EC002863
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# CK2,5-M-6 AG - Crimp contact

1409209

<https://www.phoenixcontact.com/us/products/1409209>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)