

CHARX GBH4I-DC125-2,0M - Vehicle charging inlet



1271834

<https://www.phoenixcontact.com/us/products/1271834>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



CHARX connect universal, DC GB/T, Vehicle charging inlet, up to 250 A in Boost mode, 125 A permanent, 1000 V DC, Single wires, length: 2 m, Front and rear mounting, M6, housing: black, for charging with direct current (DC), GB/T 20234.3-2015, A protective cap is supplied as standard for the DC contacts.

Product description

Vehicle charging inlets for charging with direct current (DC), compatible with GB/T vehicle charging connectors (EVSE), for installation in electric vehicles (EV).

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1271834 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | EM01 |
| Product key | XWCAIG |
| GTIN | 4063151463151 |
| Weight per piece (including packing) | 3,000 g |
| Weight per piece (excluding packing) | 2,074 g |
| Customs tariff number | 85444290 |
| Country of origin | PL |

CHARX GBH4I-DC125-2,0M - Vehicle charging inlet



1271834

<https://www.phoenixcontact.com/us/products/1271834>

Technical data

Notes

| | |
|---------|---------------------------------------------------------------|
| General | A protective cap is supplied as standard for the DC contacts. |
|---------|---------------------------------------------------------------|

Product properties

| | |
|---------------------|-------------------------------------------------------------------------------------|
| Product type | Vehicle charging inlet |
| Product family | CHARX connect universal |
| Application | for charging with direct current (DC) for installation in electric vehicles (EV) |
| Charging standard | DC GB/T |
| Charging mode | Mode 4 |
| Customer variations | On request |

Electrical properties

| | |
|-------------------------------|------------------------------------------|
| Note on the connection method | Crimp connection, cannot be disconnected |
| Coding | 1 kΩ (between PE and CC1) |
| Temperature measurement | DC contacts: 2x PT1000 (DIN EN 60751) |

Charging power and current (DC charging)

| | |
|--------------------------|----------|
| Type of charging current | DC |
| Charging current | 125 A DC |
| Charging power | 125 kW |
| Rated voltage | 1000 V |

Charging power and current (DC charging in Boost Mode)

| | |
|--------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Type of charging current | DC Boost Mode |
| Charging current | up to 250 A DC |
| Charging power | up to 250 kW |
| Rated voltage | 1000 V |
| Note | The specifications refer to charging in Boost Mode and are dependent on ambient conditions. For further details, see the packing slip in the download area. |

Pin assignment (Leistungskontakte)

| | |
|---------------|------------------|
| Number | 3 (DC+, DC-, PE) |
| Rated voltage | 1000 V DC |
| Rated current | 125 A DC |

Pin assignment (Signalkontakte)

| | |
|---------------|------------------------------|
| Number | 6 (S+, S-, A+, A-, CC1, CC2) |
| Rated voltage | 30 V AC |
| Rated current | 2 A |

Locking actuator

| | |
|------------------|--------------------------|
| Locking actuator | without locking actuator |
|------------------|--------------------------|

CHARX GBH4I-DC125-2,0M - Vehicle charging inlet



1271834

<https://www.phoenixcontact.com/us/products/1271834>

Temperature sensors (Pt 1000)

| | |
|-----------------------|-------------------------------|
| Sensor type | Pt 1000 |
| Standards/regulations | DIN EN 60751 |
| Attachment point | 2 sensors for the DC contacts |

Dimensions

Vehicle charging inlet

| | |
|--------|----------|
| Width | 93 mm |
| Height | 93 mm |
| Depth | 136.3 mm |

Bore dimensions

| | |
|--------|-------|
| Width | 72 mm |
| Height | 72 mm |
| Depth | 72 mm |

Material specifications

| | |
|----------------------------|--------------|
| Color (Housing) | black (9005) |
| Color (Mating face) | black (9005) |
| Material (Housing) | Plastic |
| Material (Contact surface) | Silver |

Cable/line

| | |
|--------------|--------------|
| Cable length | 2 m |
| Cable type | Single wires |

Single-core wires for DC

| | |
|-------------------------|------------------------|
| Cable length | 2 m |
| Cable structure | 2 x 35 mm ² |
| Single wire, material | Silicone |
| Single wire, color | OG |
| External cable diameter | 14.10 mm ±0.3 mm |
| Cable resistance | ≤ 0.527 Ω/km |

Single-core wire for PE

| | |
|-------------------------|------------------------|
| Cable length | 2 m |
| Cable structure | 1 x 25 mm ² |
| Single wire, material | Silicone |
| Single wire, color | GN/YE |
| External cable diameter | 8.60 mm ±0.1 mm |
| Cable resistance | ≤ 0.743 Ω/km |

Single-core wires for locking actuator

| | |
|-----------------|-------------------------|
| Cable length | 1 m |
| Cable structure | 4 x 0.5 mm ² |

CHARX GBH4I-DC125-2,0M - Vehicle charging inlet

1271834

<https://www.phoenixcontact.com/us/products/1271834>



| | |
|-------------------------|----------------------------|
| Single wire, material | PVC |
| Single wire, color | BU/RD, BU/GN, BU/YE, BU/BN |
| External cable diameter | 1.60 mm ±0.20 mm |
| Cable resistance | ≤ 37.1 Ω/m |

Single-core wires for Pt 1000 temperature sensors

| | |
|-------------------------|-------------------------|
| Cable length | 1 m |
| Cable structure | 3 x 0.5 mm ² |
| Single wire, material | PVC |
| Single wire, color | BN |
| | GN |
| | YE |
| External cable diameter | 1.60 mm ±0.20 mm |
| Cable resistance | ≤ 37.1 Ω/m |

Single-core wires for communication

| | |
|-------------------------|-------------------------|
| Cable length | 1 m |
| Cable structure | 2 x 0.5 mm ² |
| Single wire, material | PVC |
| Single wire, color | BK |
| | WH |
| External cable diameter | 1.60 mm ±0.20 mm |
| Cable resistance | ≤ 37.1 Ω/m |

Mechanical properties

Mechanical data

| | |
|-----------------------------|---------|
| Insertion/withdrawal cycles | > 10000 |
| Insertion force | < 100 N |
| Withdrawal force | < 100 N |

Environmental and real-life conditions

Ambient conditions

| | |
|-----------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Degree of protection (Vehicle charging inlet) | IP55 (plugged in; when plugged in and ready to operate, the degree of protection is only ensured if both plug-in components are original products from Phoenix Contact or suitable standard-compliant products) |
| | IP67 (Inner area of vehicle charging inlet) |
| Ambient temperature (operation) | -40 °C ... 40 °C (60°C, maximum (current reduction required, observe the DC contact temperature limit value of 90°C)) |
| Altitude | 4000 m (above sea level) |

Standards and regulations

Standards

| | |
|-----------------------|-------------------|
| Standards/regulations | GB/T 20234.3-2015 |
|-----------------------|-------------------|

CHARX GBH4I-DC125-2,0M - Vehicle charging inlet

1271834

<https://www.phoenixcontact.com/us/products/1271834>



Mounting

| | |
|------------------------------------------|-----------------------------------------------------------------------|
| Mounting type | Front and rear mounting (0 to 90 degree frontal inclination possible) |
| Mounting hole diameter | 6.70 mm (ø) |
| Fixing screws | M6 |
| Screws included in the scope of delivery | none |

CHARX GBH4I-DC125-2,0M - Vehicle charging inlet




1271834

<https://www.phoenixcontact.com/us/products/1271834>


Drawings

Dimensional drawing



Dimensional drawing

Connection diagram



Pin assignment of vehicle charging inlets


CHARX GBH4I-DC125-2,0M - Vehicle charging inlet



1271834


<https://www.phoenixcontact.com/us/products/1271834>

Connection diagram



Installation positions

Schematic diagram



Operating instructions

CHARX GBH4I-DC125-2,0M - Vehicle charging inlet



1271834

<https://www.phoenixcontact.com/us/products/1271834>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27144706 |
| ECLASS-15.0 | 27144706 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC002898 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121800 |
|-------------|----------|

CHARX GBH4I-DC125-2,0M - Vehicle charging inlet

1271834

<https://www.phoenixcontact.com/us/products/1271834>



Environmental product compliance

EU RoHS

| | |
|-----------------------------------------|--------------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 6(c), 7(c)-I |

China RoHS

| | |
|----------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|---------------------------------------------------------------------------------------------------------|
| REACH candidate substance (CAS No.) | 2-ethylhexyl 10-ethyl-4,4-diethyl-7-oxo-8-oxa-3,5-dithia-4-stannatetradecanoate (DOTE)(CAS: 15571-58-1) |
| | Lead(CAS: 7439-92-1) |
| SCIP | Bis(2-(2-methoxyethoxy)ethyl)ether(CAS: 143-24-8) cc8bce8d-5315-4728-b0fb-4a22ef1382c5 |

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com