

SACC-CI-M12MSB-5P SMD R32 - Contact carrier



1411985

<https://www.phoenixcontact.com/us/products/1411985>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact carrier, 5-position, Pin, straight, M12, B-coding, SMD reflow, this item is expected to be lead-free from Q1 2027 in accordance with RoHS II without exception 6c (Pb < 0.1%), a lead-free alternative is possible on request in advance

Your advantages

- Reduced mounting costs thanks to two-piece device connector
- Packaging available for automated pick and place assembly
- All common pin assignments and codings available
- Easy device integration thanks to mechanical port screw connections with threaded attachment, press-in contour or direct integration in the front plate
- Optional shield connection and seal for the device when not plugged in

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1411985 |
| Packing unit | 100 pc |
| Minimum order quantity | 100 pc |
| Sales key | AB23 |
| Product key | ABQBGN |
| GTIN | 4046356991766 |
| Weight per piece (including packing) | 6.5 g |
| Weight per piece (excluding packing) | 3.305 g |
| Customs tariff number | 85366990 |
| Country of origin | DE |

SACC-CI-M12MSB-5P SMD R32 - Contact carrier

1411985

<https://www.phoenixcontact.com/us/products/1411985>



Technical data

Notes

| | |
|--------------------|--|
| Notes on operation | The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration. |
|--------------------|--|

Product properties

| | |
|---------------------|----------------|
| Product type | Contact insert |
| Application | Signal |
| Number of positions | 5 |
| Seal present | no |
| Shielded | no |
| Coding | B |
| Thread type | M12 |

Insulation characteristics

| | |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution | 3 |

Electrical properties

| | |
|-----------------------|----------------------------|
| Rated surge voltage | 1.5 kV |
| Contact resistance | $\leq 3 \text{ m}\Omega$ |
| Insulation resistance | $\geq 100 \text{ M}\Omega$ |
| Nominal voltage U_N | 60 V |
| Nominal current I_N | 4 A |

Connection data

| | |
|-------------------|------------|
| Connection method | SMD reflow |
|-------------------|------------|

Material specifications

| | |
|--|------|
| Material Insulating body | PA |
| Material Contact | CuZn |
| Material Contact surface | Au |
| Flammability rating according to UL 94 | V0 |

Connector

Connection 1

| | |
|-------------------|----------|
| Head design | Pin |
| Head cable outlet | straight |
| Head thread type | M12 |
| Coding | B |

SACC-CI-M12MSB-5P SMD R32 - Contact carrier

1411985

<https://www.phoenixcontact.com/us/products/1411985>



Mechanical properties

Mechanical data

| | |
|-----------------------------|-------|
| Insertion/withdrawal cycles | > 100 |
|-----------------------------|-------|

Environmental and real-life conditions

Ambient conditions

| | |
|---|---|
| Degree of protection | IP67 (correctly plugged in and locked) |
| Ambient temperature (operation) (male connector/female connector) | -55 °C ... 105 °C (Plug / socket) -55 °C ... 105 °C (without mechanical actuation) |
| UL Type Rating | Type 4 (indoor use only) |

Standards and regulations

| | |
|--------------------------|------------------------------|
| Standard designation | M12 circular connector |
| Standards/specifications | according to IEC 61076-2-101 |

Packaging specifications

| | |
|-------------------|------|
| Type of packaging | Belt |
|-------------------|------|

SACC-CI-M12MSB-5P SMD R32 - Contact carrier


1411985

<https://www.phoenixcontact.com/us/products/1411985>



Drawings

Schematic diagram



Pin assignment M12 male connector, 5-pos., B-coded, male side

SACC-CI-M12MSB-5P SMD R32 - Contact carrier

1411985

<https://www.phoenixcontact.com/us/products/1411985>



Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1411985>

| cULus Recognized | | | | |
|------------------|-----------------------|-----------------------|-------------------|----------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| keine | 60 V | 4 A | - | - |

SACC-CI-M12MSB-5P SMD R32 - Contact carrier

1411985

<https://www.phoenixcontact.com/us/products/1411985>



Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27440223 |
| ECLASS-15.0 | 27440223 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC003557 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

Environmental product compliance

EU RoHS

| | |
|---|------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 6(c) |

China RoHS

| | |
|---|---------|
| Environment friendly use period (EFUP) | EFUP-50 |
| An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. | |

EU REACH SVHC

| | |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| SCIP | 2ff620b1-9261-47de-af71-ea0dc8cdd6cc |

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com