

# VS-M12MS-IP67/B-94B-LI/5,0 - Network cable



1412354

<https://www.phoenixcontact.com/us/products/1412354>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Network cable, Ethernet CAT5 (1 Gbps), 8-position, PUR halogen-free, water blue RAL 5021, Plug straight M12, coding: A / IP67, on Plug straight RJ45 Clip locking / IP67, cable length: 5 m



## Commercial data

Item number	1412354
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF04
Product key	AF1CMI
GTIN	4046356475525
Weight per piece (including packing)	264.9 g
Weight per piece (excluding packing)	264.9 g
Customs tariff number	85444210
Country of origin	PL

1412354

<https://www.phoenixcontact.com/us/products/1412354>

## Technical data

### Product properties

Product type	Data cable preassembled
Application	Standard
Sensor type	Ethernet
Number of positions	8
No. of cable outlets	1
Shielded	yes

### Insulation characteristics

Degree of pollution	3
---------------------	---

### Interfaces

Signal type/category	Ethernet CAT5 (based on IEC 11801), 1 Gbps
----------------------	--

### Electrical properties

Nominal voltage $U_N$	30 V AC
	30 V DC
Transmission medium	Copper
Transmission speed	1 Gbps


### Mechanical properties

Mechanical data	
Insertion/withdrawal cycles	$\geq 100$

### Material specifications

Flammability rating according to UL 94	HB
--	----

### Connector

Connection 1	
Dimensional drawing	
	Pin assignment M12 plug, 8-pos., A-coded, view plug side
Type	M12 Plug, angled, 8-position, shielded (Advanced Shielding Technology), Keying: A
Number of positions	8
Shielded	yes
Shielding	Advanced Shielding Technology
Signal type/category	Ethernet CAT5, 1 bps

# VS-M12MS-IP67/B-94B-LI/5,0 - Network cable



1412354

<https://www.phoenixcontact.com/us/products/1412354>

Insertion/withdrawal cycles	$\geq 100$
Insulation resistance	$\geq 100 \Omega$
Overvoltage category	II
Degree of pollution	3
Tightening torque	0.4 Nm (M12 connector)
Material Contact	CuZn
Material Contact surface	Ni/Au
Material Contact carrier	PA 6.6
Material Screw connection	Die-cast zinc, nickel-plated
Material Grip body	TPU, hardly inflammable, self-extinguishing
Material Seal	FKM
Flammability rating according to UL 94	V0
Ambient temperature (operation)	-25 °C ... 85 °C
Standard designation	M12 connector
Standards/regulations	IEC 61076-2-101

## Connection 2

Dimensional drawing	
	Connector pin assignment plug RJ45
Type	RJ45 Plug, straight, 8-position, Snap-in locking
Number of positions	8
Signal type/category	Ethernet CAT6 (IEC 11801:2002), 1 Gbps
Insertion/withdrawal cycles	$\geq 750$
Insertion force	30 N (per signal contact)
Withdrawal force	50 N (per signal contact)
Degree of pollution	2
Material Contact	CuSn
Material Contact surface	Ni/Au
Material Contact carrier	PC
Color (Housing)	gray
Flammability rating according to UL 94	V2
Degree of protection	IP67
	IP65
Ambient temperature (operation)	-40 °C ... 60 °C

## Cable/line

Cable length	5 m
--------------	-----

# VS-M12MS-IP67/B-94B-LI/5,0 - Network cable



1412354

<https://www.phoenixcontact.com/us/products/1412354>

Ethernet flexible CAT5, 4-pair [94B]

Dimensional drawing



Cable weight	47 kg/km
UL AWM Style	20963 (80°C/30 V)
Number of positions	8
Shielded	yes
Cable type	Ethernet flexible CAT5, 4-pair [94B]
Conductor structure	4x2xAWG26/7, SF/UTP
Signal runtime	5.3 ns/m
Conductor structure signal line	7x 0.16 mm
AWG signal line	26
Conductor cross section	4x 2x 0.14 mm <sup>2</sup>
Wire diameter incl. insulation	0.96 mm
External cable diameter	6.40 mm ±0.2 mm
Outer sheath, material	PUR
External sheath, color	water blue RAL 5021
Conductor material	Bare Cu litz wires
Material wire insulation	Foamed PE
Single wire, color	white/blue-blue, white/orange-orange, white/green-green, white/brown-brown
Thickness, outer sheath	1.05 mm
Twisted pairs	2 cores to the pair
Overall twist	4 pairs for core
Optical shield covering	70 %
Insulation resistance	≥ 5 GΩ*km
Coupling resistance	≤ 100.00 mΩ/m (at 10 MHz)
Loop resistance	≤ 290.00 Ω/km
Wave impedance	100 Ω ±5 Ω (at 100 MHz)
Cable capacity	48 nF/km (at 1 kHz)
Nominal voltage, cable	≤ 100 V
Test voltage Core/Core	700 V (50 Hz, 1 min.)
Test voltage Core/Shield	700.00 V (50 Hz, 1 min.)
Minimum bending radius, fixed installation	4 x D
Minimum bending radius, flexible installation	8 x D
Smallest bending radius, fixed installation	26 mm
Smallest bending radius, movable installation	52 mm

# VS-M12MS-IP67/B-94B-LI/5,0 - Network cable

1412354

<https://www.phoenixcontact.com/us/products/1412354>



Tensile strength	≤ 100 N
Near end crosstalk attenuation (NEXT)	71.3 dB (with 1 MHz) 62.3 dB (at 4 MHz) 56.3 dB (at 10 MHz) 53.2 dB (at 16 MHz) 51.8 dB (at 20 MHz) 48.9 dB (at 31.25 MHz) 44.4 dB (at 62.5 MHz) 41.3 dB (at 100 MHz)
Power-summed near end crosstalk attenuation (PSNEXT)	62.3 dB (with 1 MHz) 53.3 dB (at 4 MHz) 47.3 dB (at 10 MHz) 44.2 dB (at 16 MHz) 42.8 dB (at 20 MHz) 39.9 dB (at 31.25 MHz) 35.4 dB (at 62.5 MHz) 32.3 dB (at 100 MHz)
Return attenuation (RL)	23 dB (at 4 MHz) 24.1 dB (at 8 MHz) 25 dB (at 10 MHz) 25 dB (at 16 MHz) 25 dB (at 20 MHz) 23.6 dB (at 31.25 MHz) 21.5 dB (at 62.5 MHz) 20.1 dB (at 100 MHz)
Shield attenuation	3.2 dB (with 1 MHz) 6 dB (at 4 MHz) 9.5 dB (at 10 MHz) 12.1 dB (at 16 MHz) 13.6 dB (at 20 MHz) 17.1 dB (at 31.25 MHz) 24.8 dB (at 62.5 MHz) 32 dB (at 100 MHz)
Halogen-free	according to IEC 60754-1
Flame resistance	according to IEC 60332-1-2
Resistance to oil	in accordance with EN 60811-2-1
Ambient temperature (operation)	-40 °C ... 80 °C (cable, fixed installation) -20 °C ... 80 °C (Cable, flexible installation)
Ambient temperature (installation)	-20 °C ... 80 °C

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP65 (M12 connector)
----------------------	----------------------

# VS-M12MS-IP67/B-94B-LI/5,0 - Network cable

1412354

<https://www.phoenixcontact.com/us/products/1412354>



IP67 (RJ45 connector)

# VS-M12MS-IP67/B-94B-LI/5,0 - Network cable




1412354

<https://www.phoenixcontact.com/us/products/1412354>


## Drawings

Dimensional drawing




Plug, M12 x 1, straight, shielded

Dimensional drawing



Circuit diagram



# VS-M12MS-IP67/B-94B-LI/5,0 - Network cable

1412354

<https://www.phoenixcontact.com/us/products/1412354>



## Classifications

### ECLASS

ECLASS-13.0	27060307
ECLASS-15.0	27060307

### ETIM

ETIM 9.0	EC001855
----------	----------

### UNSPSC

UNSPSC 21.0	26121600
-------------	----------

# VS-M12MS-IP67/B-94B-LI/5,0 - Network cable



1412354

<https://www.phoenixcontact.com/us/products/1412354>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol(CAS: 119-47-1)
SCIP	80ac49ab-5c14-44d7-bfd6-85dd293b7827

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road

Middletown, PA 17057, United States

(+717) 944-1300

[info@phoenixcon.com](mailto:info@phoenixcon.com)