

SACC-CI-M12FSB-5CON-L180 THR - Contact carrier



1414070

<https://www.phoenixcontact.com/us/products/1414070>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact carrier, 5-position, Socket, straight, M12, B-coding, THR solder connection, this item is expected to be lead-free from Q1 2026 in accordance with RoHS II without exception 6c (Pb < 0.1%), a lead-free alternative is possible on request in advance

Your advantages

- Reduced mounting costs thanks to two-piece device connector
- Packaging available for automated pick and place assembly
- All common pin assignments and codings available
- Easy device integration thanks to mechanical port screw connections with threaded attachment, press-in contour or direct integration in the front plate
- Additional gasket for the device when not plugged in

Commercial data

Item number	1414070
Packing unit	60 pc
Minimum order quantity	60 pc
Sales key	AB23
Product key	ABQAGS
GTIN	4055626074405
Weight per piece (including packing)	4.766 g
Weight per piece (excluding packing)	2.402 g
Customs tariff number	85366930
Country of origin	DE

Technical data

Product properties

Product type	Contact insert
Application	Signal
Number of positions	5
Shielded	no
Coding	B
Thread type	M12

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Contact resistance	$\leq 3 \text{ m}\Omega$
Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	60 V

Connection data

Connection method	THR solder connection
-------------------	-----------------------

Material specifications

Flammability rating according to UL 94	V0
--	----

Connector

Connection 1

Head design	Socket
Head cable outlet	straight
Head thread type	M12
Coding	B

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	> 100
-----------------------------	-------

Environmental and real-life conditions

Ambient conditions

Degree of protection (when plugged in)	IP67 (correctly plugged in and locked)
Degree of protection	IP67 (correctly plugged in and locked)
UL Type Rating	Type 4 (indoor use only)

Standards and regulations

SACC-CI-M12FSB-5CON-L180 THR - Contact carrier



1414070

<https://www.phoenixcontact.com/us/products/1414070>

Standard designation	M12 circular connector
Standards/specifications	according to IEC 61076-2-101

Packaging specifications


Type of packaging	Tray
-------------------	------

1414070

<https://www.phoenixcontact.com/us/products/1414070>

Drawings

Schematic diagram



Pin assignment M12 socket, 5-pos., B-coded, female side

SACC-CI-M12FSB-5CON-L180 THR - Contact carrier



1414070

<https://www.phoenixcontact.com/us/products/1414070>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1414070>

 cUL Recognized Approval ID: E118976-20100522				
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
keine				
	60 V	4 A	22	-

 UL Recognized Approval ID: E118976-20100522				
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
keine				
	60 V	4 A	22	-

SACC-CI-M12FSB-5CON-L180 THR - Contact carrier



1414070

<https://www.phoenixcontact.com/us/products/1414070>

Classifications

ECLASS

ECLASS-13.0	27440223
ECLASS-15.0	27440223

ETIM

ETIM 9.0	EC003557
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

1414070

<https://www.phoenixcontact.com/us/products/1414070>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	f3221bc4-744d-4074-a340-faa52389d211

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com