

1414107

<https://www.phoenixcontact.com/us/products/1414107>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Launch fiber single mode (OS2)



Your advantages

- High reliability with comprehensive quality assurance measures
- Intuitive front-panel operation and clear control cabinet layout thanks to uniform design

Commercial data

Item number	1414107
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ABNIBC
GTIN	4055626023434
Weight per piece (including packing)	37 g
Weight per piece (excluding packing)	37 g
Country of origin	BG

1414107

<https://www.phoenixcontact.com/us/products/1414107>

Technical data

Product properties

Product type	Data cable preassembled
Number of positions	3
Set comprises	1411049 FOC-TOOL-GOF KONF SET

Electrical properties

Attenuation	≤ 0.5 dB
	≤ 0.5 dB
Transmission speed	100 Gbps
Transmission speed	100 GBit/s

Mechanical properties

Tensile strength short-term/long-term	50 N
---------------------------------------	------

Mechanical data

Smallest bending radius	30 mm
-------------------------	-------

Cable/line

Cable weight	15.80 kg/km
Cable type	Single-mode fiberglass
Cable structure	Compact wire (TB)
External cable diameter	2.00 mm
Individual wire diameter	900 µm
Tensile strength short-term/long-term	50 N
Whip length	250 mm
Flame resistance	yes

FO cable

Number of fibers	2
Fiber type	Multimode

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-25 °C ... 70 °C
Ambient temperature (storage/transport)	-25 °C ... 70 °C

Standards and regulations

Flame resistance	yes
------------------	-----

FOC-SC-LC-OS2-LS-CABLE/3 - FO accessories



1414107

<https://www.phoenixcontact.com/us/products/1414107>

Classifications

ECLASS

ECLASS-13.0	27061003
ECLASS-15.0	27061003

ETIM

ETIM 9.0	EC002607
----------	----------

UNSPSC

UNSPSC 21.0	27111500
-------------	----------

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com