

HC-M-08-GBIT-CT-M-SH - Contact insert module



1353603

<https://www.phoenixcontact.com/us/products/1353603>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact insert module, number of positions: 8, Pin, Crimp connection, 48 V, 5 A, 0.08 mm² ... 0.5 mm², external cable diameter: 4.5 mm ... 9 mm, application: Data, without crimp contacts, Shielded transmission to the module frame

Commercial data

Item number	1353603
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF62
Product key	AF7ACE
GTIN	4063151678364
Weight per piece (including packing)	52.8 g
Weight per piece (excluding packing)	22.22 g
Customs tariff number	85389099
Country of origin	PL

HC-M-08-GBIT-CT-M-SH - Contact insert module



1353603

<https://www.phoenixcontact.com/us/products/1353603>

Technical data

Notes

General	Connectors may be operated only when there is no load/voltage.
---------	--

Mounting

Assembly note	To ensure correct use, installation in housing with IP54 protection or better is required
---------------	---

Product properties

Product type	Modular contact insert
Series	HC-M-08-GBIT
Application	Data
Sensor type	Ethernet
Number of positions	8
Connection profile	8
Contact numbering	1 - 8
No. of cable outlets	1
Number of module slots	1
Contact material type	turned
Shielded	yes

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Connection data


Connection technology

Connection technology	Crimp connection
-----------------------	------------------

Conductor connection

Conductor cross section	0.08 mm ² ... 0.5 mm ²
Connection cross section AWG	28 ... 20
Stripping length of the individual wire	4.2 mm

Dimensions

Dimensional drawing	
Width	26.35 mm
Height	41.4 mm
Length	13.9 mm

HC-M-08-GBIT-CT-M-SH - Contact insert module



1353603

<https://www.phoenixcontact.com/us/products/1353603>

Mechanical characteristics

Contact diameter	1 mm
------------------	------

Electrical properties

Rated voltage (III/3)	48 V
Rated surge voltage	0.8 kV
Rated current	5 A
Transmission characteristics (category)	CAT6 _A

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 500
-----------------------------	-------

Material specifications

Flammability rating according to UL 94	V0
Contact material	Copper alloy
Contact surface material	Au
Contact carrier material	PC
Standards/regulations	PC

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-25 °C ... 85 °C (including heating up of contacts)
---------------------------------	---

HC-M-08-GBIT-CT-M-SH - Contact insert module


1353603

<https://www.phoenixcontact.com/us/products/1353603>




Drawings

Dimensional drawing



Male insert

Diagram



Derating diagram

HC-M-08-GBIT-CT-M-SH - Contact insert module



1353603

<https://www.phoenixcontact.com/us/products/1353603>

Classifications

ECLASS

ECLASS-13.0	27440218
ECLASS-15.0	27440218

ETIM

ETIM 9.0	EC000438
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

HC-M-08-GBIT-CT-M-SH - Contact insert module



1353603

<https://www.phoenixcontact.com/us/products/1353603>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com