


FOC-SJ:A-SJ:A-GZ02/2 - FO patch cable



1400699

<https://www.phoenixcontact.com/us/products/1400699>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Assembled FO cable, zip cord cable, multi-mode fiberglass 50/125 µm, OM3, plug: SC-RJ/SC-RJ, degree of protection: IP20, for installation in cable ducts or control cabinets, length: 2 m

Your advantages

- Multi-mode patch cable for indoor installation
- All components satisfy UL 94, V0
- 2.8 mm single elements made from halogen-free and flame-retardant material
- Interferometer tests at every stage of the certification process
- Excellent mechanical and optical properties
- Satisfies optical and mechanical industry standards
- Connector with UPC polishing for optimum attenuation values
- Insertion loss ≤ 0.5 dB
- Return attenuation ≥ 35 dB

Commercial data

Item number	1400699
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	AB16
Product key	ABNIBC
GTIN	4046356735018
Weight per piece (including packing)	22.22 g
Weight per piece (excluding packing)	22.22 g
Customs tariff number	85447000
Country of origin	DE

Technical data

Product properties

Product type	Data cable preassembled
Number of positions	2
No. of conductors	2

Electrical properties

Attenuation	≤ 0.5 dB (with 850 nm)
	≤ 0.5 dB (with 1300 nm)
Transmission medium	Multi-mode fiberglass

Mechanical properties

Tensile strength short-term/long-term	50 N
---------------------------------------	------

Mechanical data

Smallest bending radius	30 mm
-------------------------	-------

Material specifications

Color	blue
Flammability rating according to UL 94	V0
Ferrule material	Zirconia ceramics

Dimensions

External dimensions

External diameter min.	2.8 mm
External diameter max.	5.7 mm

Mechanical characteristics

Ferrule diameter	2.50 mm
------------------	---------

Connector

Connection 1

Type	Plug straight SC-RJ
------	---------------------

Connection 2

Type	Plug straight SC-RJ
------	---------------------

Cable/line

Cable length	2.00 m
Cable weight	8.30 kg/km
Cable type	Fiberglass
Cable type	Zip cord
External cable diameter	2.00 mm (Zip cord)

FOC-SJ:A-SJ:A-GZ02/2 - FO patch cable



1400699

<https://www.phoenixcontact.com/us/products/1400699>

Outer sheath, material	LSZH
External sheath, color	aqua
Wire diameter incl. insulation	900 µm
Individual wire diameter	900 µm (low-bend)
Single wire, color	-
Tensile strength short-term/long-term	600 N
Smallest bending radius, fixed installation	15 mm
Smallest bending radius, movable installation	30 mm
Cable, attenuation	2.5 dB/km (at 850 nm), 0.7 dB/km (at 1300 nm)
Halogen-free	complying with IEC 60754-1/2
Flame resistance	yes

FO cable

Number of fibers	2
Fiber	50/125 µm
Fiber type	Multimode fiberglass 50/125 µm
Cable, attenuation	2.5 dB/km (at 850 nm), 0.7 dB/km (at 1300 nm)
Transmission medium	Multi-mode fiberglass

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-10 °C ... 60 °C
Ambient temperature (storage/transport)	-10 °C ... 60 °C
Ambient temperature (assembly)	-5 °C ... 50 °C
Ambient temperature (installation)	-5 °C ... 50 °C

Standards and regulations

Flame resistance	yes
------------------	-----

FOC-SJ:A-SJ:A-GZ02/2 - FO patch cable



1400699

<https://www.phoenixcontact.com/us/products/1400699>

Classifications

UNSPSC

UNSPSC 21.0	26121607
-------------	----------

FOC-SJ:A-SJ:A-GZ02/2 - FO patch cable



1400699
<https://www.phoenixcontact.com/us/products/1400699>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com