

G-INS-M50-M68N-NNES-S - Cable gland

1424530

<https://www.phoenixcontact.com/us/products/1424530>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable gland, material for screw connection: Brass, nickel-plated, application: Standard, external cable diameter 22 mm ... 32 mm, shielding: no, connecting thread: M50 x 1.5, color: silver-colored, with O-ring

Commercial data

Item number	1424530
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF68
Product key	AF7DAX
GTIN	4055626374352
Weight per piece (including packing)	289 g
Weight per piece (excluding packing)	290.9 g
Customs tariff number	74198090
Country of origin	TR

G-INS-M50-M68N-NNES-S - Cable gland



1424530

<https://www.phoenixcontact.com/us/products/1424530>

Technical data

Mounting

Assembly note	1) Mount screw connection support in the housing using the correct torque 2) Insert cable 3) Tighten union nut using the correct torque
---------------	---

Product properties

Product type	Cable screw gland
Application	Standard
No. of conductors	1
Manufacturer	BIMED
Manufacturer Designation	BMBC-06
Shielded	no
Execution of the strain relief	A

Characteristics

Category of shock impact	7
Design, Strain relief	A

Dimensions

Dimensional drawing	
Length	58 mm
Length of the connecting thread	9 mm
Hole diameter	50.1 mm ... 50.3 mm
Wrench size, union nut	50 mm
Wrench size, support	55 mm
Hexagon angular dimension	64 mm
Thread type connection side	M50 x 1.5
Thread pitch	1.5 mm

Connection data

Tightening torque	42 Nm ± 1.5 Nm (Cap nut)
	18 Nm (Support sleeve)

Material specifications

Color	brass color
Material Compression ring	PA 6
Seal material O-ring	Perbunan
Seal material Cable seal	CR

G-INS-M50-M68N-NNES-S - Cable gland

1424530

<https://www.phoenixcontact.com/us/products/1424530>



Material for screw connection

Brass, nickel-plated

Cable/line

External cable diameter Cable 1	22 mm ... 32 mm
External cable diameter	22 mm ... 32 mm (for UL 514 B)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP66
	IP68 (5 bar, 30 min.)
Ambient temperature (operation)	IP69

Ambient temperature (operation)	-40 °C ... 100 °C (static)
---------------------------------	----------------------------

G-INS-M50-M68N-NNES-S - Cable gland


1424530

<https://www.phoenixcontact.com/us/products/1424530>



Drawings

Dimensional drawing



Dimensional drawing

G-INS-M50-M68N-NNES-S - Cable gland

1424530

<https://www.phoenixcontact.com/us/products/1424530>



Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1424530>

DNV

Approval ID: TAE00003WY



UL Listed

Approval ID: E199260



cUL Listed

Approval ID: E199260

G-INS-M50-M68N-NNES-S - Cable gland

1424530

<https://www.phoenixcontact.com/us/products/1424530>



Classifications

ECLASS

ECLASS-13.0	27140801
ECLASS-15.0	27140801

ETIM

ETIM 9.0	EC000441
----------	----------

UNSPSC

UNSPSC 21.0	39121300
-------------	----------

G-INS-M50-M68N-NNES-S - Cable gland

1424530

<https://www.phoenixcontact.com/us/products/1424530>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.	

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	49e6a994-078a-439e-b1e3-50b0e46d33c4

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com