

# HC-EVO-B24-HHFS-EL-AL - Housing

1411473

<https://www.phoenixcontact.com/us/products/1411473>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



HEAVYCON EVO sleeve housing, EMC version, without powder coating, with bayonet flange for EVO screw connection, B24, for single locking latch, height: 88 mm, without EVO screw connection.

## Your advantages

- Flexible cable outlet direction, lateral or straight

## Commercial data

Item number	1411473
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF57
Product key	AF7APM
GTIN	4046356932738
Weight per piece (including packing)	275.6 g
Weight per piece (excluding packing)	268.4 g
Customs tariff number	85389099
Country of origin	DE

# HC-EVO-B24-HHFS-EL-AL - Housing

1411473

<https://www.phoenixcontact.com/us/products/1411473>



## Technical data

### Notes

General	For contact inserts HC-B24, BB46, D64, DD108, M
---------	-------------------------------------------------

### Product properties

Product type	Housing with locking latch
Housing type	Sleeve housing
Application	Standard
Type	B24
No. of cable outlets	1
Cable outlet	straight
Pg screw connection	none

### Dimensions

Dimensional drawing	
Width	44 mm
Height	88 mm
Length	120 mm

### Material specifications

Housing material	Die-cast aluminum, salt water resistant
Housing surface material	uncoated

### Mechanical properties

Mechanical data	
Locking type	Pin

### Mounting

Assembly note	The sleeve base housing must be supplemented with the EVO screw connection. The EVO screw connection is available in 4 sizes. It enables the creation of a straight or a lateral cable outlet. The EVO screw connection is assembled by hand or using a pipe wrench.
---------------	----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

### Environmental and real-life conditions

Ambient conditions	
Degree of protection	IP66
	IP67
	4 (UL 50e)

# HC-EVO-B24-HHFS-EL-AL - Housing

1411473

<https://www.phoenixcontact.com/us/products/1411473>



Enclosure rating (NEMA)	4X (UL 50e) 12 (UL 50e)
Impact strength	IK08
Ambient temperature (operation)	-40 °C ... 125 °C

# HC-EVO-B24-HHFS-EL-AL - Housing


1411473

<https://www.phoenixcontact.com/us/products/1411473>



## Drawings

Dimensional drawing



Dimensional drawing

# HC-EVO-B24-HHFS-EL-AL - Housing

1411473

<https://www.phoenixcontact.com/us/products/1411473>



## Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1411473>

**DNV**

Approval ID: TAE000037S



**cUL Recognized**

Approval ID: E255026



**UL Recognized**

Approval ID: E255026



**EAC**

Approval ID: RU C-DE.AI30.B.01102

# HC-EVO-B24-HHFS-EL-AL - Housing

1411473

<https://www.phoenixcontact.com/us/products/1411473>



## Classifications

### ECLASS

ECLASS-13.0	27440202
ECLASS-15.0	27440202

### ETIM

ETIM 9.0	EC000437
----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# HC-EVO-B24-HHFS-EL-AL - Housing

1411473

<https://www.phoenixcontact.com/us/products/1411473>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
-----------------------------------------	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)