

SACC-DSIV-M 8MS-4CON-L 90 - Device connector rear mounting



1440096

<https://www.phoenixcontact.com/us/products/1440096>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Device connector rear mounting, 4-position, Pin, angled, M8, A-coding, Wave soldering



Your advantages

- Standard pin assignments and codings for signal transmission with a uniform design-in design

Commercial data

Item number	1440096
Packing unit	20 pc
Minimum order quantity	20 pc
Sales key	AB22
Product key	ABQJAA
GTIN	4046356480888
Weight per piece (including packing)	4.63 g
Weight per piece (excluding packing)	4.5 g
Customs tariff number	85366990
Country of origin	DE

SACC-DSIV-M 8MS-4CON-L 90 - Device connector rear mounting



1440096

<https://www.phoenixcontact.com/us/products/1440096>

Technical data

Mounting

Mounting type	Rear mounting (M8 x 1, with flat nut)
---------------	---------------------------------------

Product properties

Product type	Circular connectors (device side)
Number of positions	4
Shielded	no
Coding	A
Thread type	M8

Insulation characteristics

Ovvoltage category	II
Degree of pollution	3

Material specifications

Material Housing	CuZn
Material Housing surface	Ni
Material Insulating body	PA 6.6
Material Contact	CuZn
Material Contact surface	Au
Flammability rating according to UL 94	HB
Seal material	NBR

Electrical properties

Rated surge voltage	1.5 kV
Contact resistance	$\leq 3 \text{ m}\Omega$
Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	48 V AC 60 V DC
Nominal current I_N	4 A

Connection data

Conductor connection	
Connection method	Wave soldering
Contact connection type	Pin

Connector

Connection 1	
Head design	Pin
Head cable outlet	angled

SACC-DSIV-M 8MS-4CON-L 90 - Device connector rear mounting



1440096

<https://www.phoenixcontact.com/us/products/1440096>

Head thread type	M8
Coding	A

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 85 °C
Ambient temperature (operation)	-25 °C ... 85 °C
UL Type Rating	Type 4 (indoor use only)

Standards and regulations

Standard designation	M8 circular connector
Standards/specifications	according to IEC 61076-2-104

SACC-DSIV-M 8MS-4CON-L 90 - Device connector rear mounting




1440096

<https://www.phoenixcontact.com/us/products/1440096>

Drawings

Schematic diagram



Pin assignment M8 plug, 4-pos., view male side

SACC-DSIV-M 8MS-4CON-L 90 - Device connector rear mounting



1440096

<https://www.phoenixcontact.com/us/products/1440096>

Classifications

ECLASS

ECLASS-13.0	27440110
ECLASS-15.0	27440110

ETIM

ETIM 9.0	EC003568
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SACC-DSIV-M 8MS-4CON-L 90 - Device connector rear mounting



1440096

<https://www.phoenixcontact.com/us/products/1440096>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50 An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
--	--

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	32f01563-8ca8-4184-b00a-1266c5551fd0

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com