

G-ESIS-M25-M68N-NEPDS-S - Cable gland

1415126

<https://www.phoenixcontact.com/us/products/1415126>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable gland, material for screw connection: Brass, nickel-plated, application: Ex, external cable diameter 10 mm ... 17 mm, shielding: no, connecting thread: M25 x 1.5, color: silver-colored, with O-ring

Your advantages

- Dust protection during storage and transport provided by a dust cap.
- Weatherproof sealing material
- Halogen-free

Commercial data

Item number	1415126
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BF68
Product key	AF7DDX
GTIN	4055626037875
Weight per piece (including packing)	68.91 g
Weight per piece (excluding packing)	68.91 g
Customs tariff number	74198090
Country of origin	DE

G-ESIS-M25-M68N-NEPDS-S - Cable gland

1415126

<https://www.phoenixcontact.com/us/products/1415126>



Technical data

Product properties

Product type	Cable screw gland
Application	Ex
No. of conductors	1
Manufacturer	WISKA
Manufacturer Designation	EMSKE-L 25
Shielded	no

Ex data

Cable types that can be used	for unarmored cables
Suited for EX-applications	yes

Dimensions

Dimensional drawing	
Length	38 mm
Length of the connecting thread	12 mm
Hole diameter	25.1 mm ... 25.3 mm
Wrench size, union nut	29 mm
Wrench size, support	29 mm
Hexagon angular dimension	32 mm
Thread type connection side	M25 x 1.5
Thread pitch	1.5 mm

Connection data

Tightening torque	10 Nm (Support sleeve)
-------------------	------------------------

Material specifications

Color	brass color
Material Compression ring	PA
Seal material Cable seal	EPDM
Material for screw connection	Brass, nickel-plated

Cable/line

External cable diameter	10 mm ... 17 mm
-------------------------	-----------------

Environmental and real-life conditions

G-ESIS-M25-M68N-NEPDS-S - Cable gland

1415126

<https://www.phoenixcontact.com/us/products/1415126>



Ambient conditions

Degree of protection	IP66
	IP68 (5 bar / 0.5 h)
Ambient temperature (operation)	-40 °C ... 75 °C (static)

Approvals

ATEX	II 2 G/D EEx e II IP68
IECEx	Ex e IIC Gb, Ex tb IIIC Db

G-ESIS-M25-M68N-NEPDS-S - Cable gland


1415126

<https://www.phoenixcontact.com/us/products/1415126>



Drawings

Dimensional drawing



G-ESIS-M25-M68N-NEPDS-S - Cable gland

1415126

<https://www.phoenixcontact.com/us/products/1415126>



Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1415126>



cUL Recognized

Approval ID: E179850



UL Recognized

Approval ID: E179850



EAC Ex

Approval ID: RU C-DE.HA67.B.00120



GL

Approval ID: 20259-04 HH



IECEx

Approval ID: IECEx PTB 13.0027X



ATEX

Approval ID: PTB 04 ATEX 1112 X

G-ESIS-M25-M68N-NEPDS-S - Cable gland

1415126

<https://www.phoenixcontact.com/us/products/1415126>



Classifications

ECLASS

ECLASS-13.0	27140802
ECLASS-15.0	27140802

ETIM

ETIM 9.0	EC000441
----------	----------

UNSPSC

UNSPSC 21.0	39121300
-------------	----------

G-ESIS-M25-M68N-NEPDS-S - Cable gland

1415126

<https://www.phoenixcontact.com/us/products/1415126>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.	

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	e8d047a2-5d7f-4428-a822-c6ed11b9da61

EF3.0 Climate Change

CO2e kg	0.889 kg CO2e
---------	---------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com