

# G-ESISEC-M50-L68L-NEPDS-S - Cable gland



1415169

<https://www.phoenixcontact.com/us/products/1415169>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable gland, material for screw connection: Brass, nickel-plated, application: Ex, external cable diameter 21 mm ... 35 mm, shielding: yes, connecting thread: M50 x 1.5, color: silver-colored, with O-ring

## Your advantages

- Dust protection during storage and transport provided by a dust cap.
- Weatherproof sealing material
- Halogen-free

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1415169       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | BF68          |
| Product key                          | AF7DDX        |
| GTIN                                 | 4055626037981 |
| Weight per piece (including packing) | 367.8 g       |
| Weight per piece (excluding packing) | 367.8 g       |
| Customs tariff number                | 74198090      |
| Country of origin                    | DE            |

# G-ESISEC-M50-L68L-NEPDS-S - Cable gland



1415169

<https://www.phoenixcontact.com/us/products/1415169>

## Technical data

### Mounting

|               |                                                                                                                                                                                                                                                                                                                                                                                                                                          |
|---------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Assembly note | Mounting the screw connection: <ul style="list-style-type: none"><li>- Mount cable gland support</li><li>- Strip outer cable sheath. Expose around 7 mm of the cable shield.</li><li>- Push the outer cone over the braided shield</li><li>- Push the inner cone under the shield</li><li>- Insert both, together with the cable, in the mounted screw connection support</li><li>- Tighten union nut with the required torque</li></ul> |
|---------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|


### Product properties

|                          |                   |
|--------------------------|-------------------|
| Product type             | Cable screw gland |
| Application              | Ex                |
| No. of conductors        | 1                 |
| Manufacturer             | WISKA             |
| Manufacturer Designation | EMSKE-L 50 EMV-Z  |
| Shielded                 | yes               |

### Ex data

|                              |                      |
|------------------------------|----------------------|
| Cable types that can be used | for unarmored cables |
| Suited for EX-applications   | yes                  |

### Dimensions

|                                 |                                                                                      |
|---------------------------------|--------------------------------------------------------------------------------------|
| Dimensional drawing             |  |
| Length                          | 57 mm                                                                                |
| Length of the connecting thread | 15 mm                                                                                |
| Hole diameter                   | 50.1 mm ... 50.3 mm                                                                  |
| Wrench size, union nut          | 55 mm                                                                                |
| Wrench size, support            | 55 mm                                                                                |
| Hexagon angular dimension       | 61 mm                                                                                |
| Thread type connection side     | M50 x 1.5                                                                            |
| Thread pitch                    | 1.5 mm                                                                               |

### Connection data

|                   |                        |
|-------------------|------------------------|
| Tightening torque | 30 Nm (Support sleeve) |
|-------------------|------------------------|

### Material specifications

# G-ESISEC-M50-L68L-NEPDS-S - Cable gland



1415169

<https://www.phoenixcontact.com/us/products/1415169>

|                               |                      |
|-------------------------------|----------------------|
| Color                         | brass color          |
| Material Compression ring     | PA                   |
| Seal material Cable seal      | EPDM                 |
| Material for screw connection | Brass, nickel-plated |

## Cable/line

|                         |                 |
|-------------------------|-----------------|
| External cable diameter | 21 mm ... 35 mm |
|-------------------------|-----------------|

## Environmental and real-life conditions

### Ambient conditions

|                                 |                           |
|---------------------------------|---------------------------|
| Degree of protection            | IP66                      |
|                                 | IP68 (5 bar / 0.5 h)      |
| Ambient temperature (operation) | -40 °C ... 75 °C (static) |

## Approvals

|       |                            |
|-------|----------------------------|
| ATEX  | II 2 G/D EEx e II IP68     |
| IECEX | Ex e IIC Gb, Ex tb IIIC Db |


# G-ESISEC-M50-L68L-NEPDS-S - Cable gland



1415169

<https://www.phoenixcontact.com/us/products/1415169>

## Drawings



# G-ESISEC-M50-L68L-NEPDS-S - Cable gland



1415169

<https://www.phoenixcontact.com/us/products/1415169>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1415169>



**cUL Recognized**

Approval ID: E179850



**UL Recognized**

Approval ID: E179850



**EAC Ex**

Approval ID: RU C-DE.HA67.B.00120



**GL**

Approval ID: 20259-04 HH



**IECEx**

Approval ID: IECEx PTB 13.0027X



**ATEX**

Approval ID: PTB 04 ATEX 1112 X

# G-ESISEC-M50-L68L-NEPDS-S - Cable gland



1415169

<https://www.phoenixcontact.com/us/products/1415169>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27140802 |
| ECLASS-15.0 | 27140802 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC000441 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121300 |
|-------------|----------|

## Environmental product compliance

## EU RoHS

|                                         |      |
|-----------------------------------------|------|
| Fulfills EU RoHS substance requirements | Yes  |
| Exemption                               | 6(c) |

## China RoHS

|                                        |                                                                                                                                                                                                                                   |
|----------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-50                                                                                                                                                                                                                           |
|                                        | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

## EU REACH SVHC

|                                     |                                      |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1)                 |
| SCIP                                | a415fc04-53ad-4310-9676-48a270a30ccb |

## EF3.0 Climate Change

|         |               |
|---------|---------------|
| CO2e kg | 6.267 kg CO2e |
|---------|---------------|