

FOC-OP12-OP12-GL02/60 - Connecting cable

1415230

<https://www.phoenixcontact.com/us/products/1415230>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Double-end preassembled cable, type: circular connector, degree of protection: IP68, number of positions: 12



Product description

Robust connecting cable Q-ODC-12 to Q-ODC-12, push-pull interlocking, degree of protection: IP68

Your advantages

- Compact design with MT ferrule
- Push-pull interlocking
- For extreme ambient conditions
- Robust connector for 12 fibers, degree of protection: IP68 (when connected)

Commercial data

Item number	1415230
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	AB15
Product key	ABNHAA
GTIN	4055626045740
Weight per piece (including packing)	3,315 g
Weight per piece (excluding packing)	3,245 g
Customs tariff number	85447000
Country of origin	PL

FOC-OP12-OP12-GL02/60 - Connecting cable

1415230

<https://www.phoenixcontact.com/us/products/1415230>



Technical data

Product properties

Product type	Data cable preassembled
Sensor type	Ethernet
Number of positions	12

Electrical properties

Attenuation	typ. 0.2 dB
	max. 0.6 dB
Transmission medium	Multi-mode fiberglass

Mechanical properties

Tensile strength short-term/long-term	500 N
---------------------------------------	-------

Material specifications

Flammability rating according to UL 94	V0
Outer sheath, material	LSFH

Connector

Connection 1

Locking type	Push Pull
Handle color	black
Insertion/withdrawal cycles	500 (In the event of repeated cleaning)
Degree of protection	IP68 (IEC 60529)
	IP68
Ambient temperature (operation)	-40 °C ... 85 °C (IEC 61300-2-22)

Connection 2

Locking type	Push Pull
Handle color	black
Insertion/withdrawal cycles	500 (In the event of repeated cleaning)
Degree of protection	IP68 (IEC 60529)
Ambient temperature (operation)	-40 °C ... 85 °C (IEC 61300-2-22)

Cable/line

Cable length	60 m
Cable weight	55.00 kg/km
Cable type	Multimode fiberglass
Cable type	Zip cord, fiberglass
Cable abbreviation	12.../H(ZNG)H-...70
External cable diameter	7 mm
Outer sheath, material	LSFH
External sheath, color	black

FOC-OP12-OP12-GL02/60 - Connecting cable

1415230

<https://www.phoenixcontact.com/us/products/1415230>



Wire diameter incl. insulation	250 µm
Individual wire diameter	250 µm
Smallest bending radius, fixed installation	≥ 70 mm
Tensile strength short-term/long-term	500 N
Lateral pressure short term	500.00 N/cm
Lateral pressure, long-term	200.00 N/cm
Halogen-free	complying with IEC 60754-1/2

FO cable

Number of fibers	12
Fiber	62.5/125 µm OM1
Fiber type	Multimode fiberglass 62.5/125 µm
Attenuation	typ. 0.15 dB
Transmission medium	Multi-mode fiberglass

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP68
Ambient temperature (operation)	-40 °C ... 85 °C (IEC 61300-2-22)
Shock	50g, in accordance with IEC 61300-2-9

FOC-OP12-OP12-GL02/60 - Connecting cable

1415230

<https://www.phoenixcontact.com/us/products/1415230>



Classifications

ECLASS

ECLASS-13.0	27061003
-------------	----------

ETIM

ETIM 8.0	EC002641
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

FOC-OP12-OP12-GL02/60 - Connecting cable

1415230

<https://www.phoenixcontact.com/us/products/1415230>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road

Middletown, PA 17057, United States

(+717) 944-1300

info@phoenixcon.com