

# MC-3/7-MULTI-67-PVO-BK - Cable feed-through plates



1415235

<https://www.phoenixcontact.com/us/products/1415235>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable feed-through plates, no. of conductors: 7, external cable diameter: 1x 30 mm ... 60 mm, 4x 10 mm ... 14 mm, 2x 24 mm ... 54 mm, material: galvanized sheet steel (Core), material: TPE-SEBS (external material), color: black, length: 222 mm, width: 92 mm, height: 43 mm

## Your advantages

- Oil-resistant according to UL 157

## Commercial data

Item number	1415235
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF67
Product key	AF7CAX
GTIN	4055626039411
Weight per piece (including packing)	287.3 g
Weight per piece (excluding packing)	278.9 g
Customs tariff number	39269097
Country of origin	FI

# MC-3/7-MULTI-67-PVO-BK - Cable feed-through plates



1415235

<https://www.phoenixcontact.com/us/products/1415235>

## Technical data

### Notes

General	incl. mounting screws
General	2 mm thick coated, galvanized sheet steel

### Product properties

Product type	Cable feed-through
No. of conductors	7

### Connection data

External cable diameter	1x 30 mm ... 60 mm
Tightening torque	1.5 Nm ... 2 Nm (Mounting screws)

### Dimensions

Dimensional drawing	
Width	92 mm
Height	43 mm
Length	222 mm
Drill hole distance, horizontal	62 mm
Drill hole distance, vertical	194 mm
Hole diameter	8.5 mm

### Material specifications

Color	black (RAL 9005)
Material interior	galvanized sheet steel (Core)
Material exterior	TPE-SEBS (external material)
Flammability rating according to UL 94	V0

### Cable/line

External cable diameter 30-60 mm	1x 30 mm ... 60 mm
External cable diameter 10-14 mm	4x 10 mm ... 14 mm
External cable diameter 24-54 mm	2x 24 mm ... 54 mm

### Environmental and real-life conditions

Ambient conditions	
Degree of protection	IP66 (Minimum sheet thickness >= 2.5 mm)

# MC-3/7-MULTI-67-PVO-BK - Cable feed-through plates



1415235

<https://www.phoenixcontact.com/us/products/1415235>

Ambient temperature (operation)	IP67 (Minimum sheet thickness $\geq$ 2.5 mm) -40 °C ... 100 °C
---------------------------------	---

## Mounting

Assembly note	<p>M8 mounting screw, torque: 1.5 - 2.0 Nm, SW5 Allen key</p> <p>The mounting screws included should be used for assembly.</p> <p>Assembly steps:</p> <ol style="list-style-type: none"><li>1) Fix Multigates with the mounting screws provided (observe torque)</li><li>2) Make a hole in the membrane (with a screwdriver) or cut off the tip of the cone</li><li>3) Guide the cable through the opening (from the outside). Withdraw the cable approximately 20 mm (to improve strain relief).</li></ol>
---------------	---

# MC-3/7-MULTI-67-PVO-BK - Cable feed-through plates




1415235

<https://www.phoenixcontact.com/us/products/1415235>

## Drawings

Dimensional drawing



Dimensional drawing


# MC-3/7-MULTI-67-PVO-BK - Cable feed-through plates



1415235

<https://www.phoenixcontact.com/us/products/1415235>

Dimensional drawing



Wall cutout drawing

# MC-3/7-MULTI-67-PVO-BK - Cable feed-through plates



1415235

<https://www.phoenixcontact.com/us/products/1415235>

## Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1415235>



**EAC-RoHS**

Approval ID: RU D-DE.HB35.B.00387

# MC-3/7-MULTI-67-PVO-BK - Cable feed-through plates



1415235

<https://www.phoenixcontact.com/us/products/1415235>

## Classifications

### ECLASS

ECLASS-13.0	27400569
ECLASS-15.0	27400569

### ETIM

ETIM 9.0	EC001004
----------	----------

### UNSPSC

UNSPSC 21.0	31163000
-------------	----------

# MC-3/7-MULTI-67-PVO-BK - Cable feed-through plates



1415235

<https://www.phoenixcontact.com/us/products/1415235>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.0 Climate Change

CO2e kg	2.536 kg CO2e
---------	---------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road

Middletown, PA 17057, United States

(+717) 944-1300

[info@phoenixcon.com](mailto:info@phoenixcon.com)