

PV-1P-100,0/S04-10,0 - Cable reel

1459537

<https://www.phoenixcontact.com/us/products/1459537>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Cable ring, black PE-X, 1-pos., cable length: 100 m



Commercial data

Item number	1459537
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	ABLBDX
GTIN	4046356618830
Weight per piece (including packing)	22.22 g
Weight per piece (excluding packing)	22.22 g
Country of origin	DE

PV-1P-100,0/S04-10,0 - Cable reel

1459537

<https://www.phoenixcontact.com/us/products/1459537>



Technical data

Product properties

Number of positions	1
Shielded	no

Electrical properties

Nominal current I_N	≤ 98 A (up to +60 °C)
-----------------------	----------------------------

Dimensions

Width	6.35 mm
Height	6.35 mm
Length	100 m

Material specifications

Outer sheath, material	PE-X
Conductor material	Tin-plated Cu litz wires

Cable/line

Cable length	10 m
--------------	------

PV1-F cables [S04]

Shielded	no
Cable weight	127 kg/km
Cable type	PV1-F cables
Cable type (abbreviation)	S04
External cable diameter	6.90 mm ± 0.2 mm
Outer sheath, material	PE-X
External sheath, color	black-gray RAL 7021
Material, inner sheath	PE-X
Conductor structure, voltage supply	80x 0.40 mm
AWG power supply	8
Thickness, insulation	≥ 0.50 mm (Inner sheath)
Cable resistance	1.95 Ω/m (at 20 °C)
Smallest bending radius, fixed installation	34.5 mm
Smallest bending radius, movable installation	69 mm

Standards and regulations

Flame resistance	IEC 60332-1-2
Other resistance	Resistance to acids and alkalis
	Resistant to salt water
	Resistant to ozone

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-50 An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
--	--

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com