

# PSR-PLC21-2CO-24DC-SC - Coupling relay

1480226

<https://www.phoenixcontact.com/us/products/1480226>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Safe coupling relay with force-guided contacts, electrically isolated, 2 changeover contacts, 1-channel, fixed screw terminal block, width: 14 mm

## Commercial data

Item number	1480226
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	DN01
Product key	DNA162
GTIN	4063151897741
Weight per piece (including packing)	80.38 g
Weight per piece (excluding packing)	76 g
Customs tariff number	85364190
Country of origin	DE

# PSR-PLC21-2CO-24DC-SC - Coupling relay

1480226

<https://www.phoenixcontact.com/us/products/1480226>



## Technical data

### Notes

#### Note on application

Note on application

Only for industrial use

### Product properties

Product type	Coupling relay
Product family	PLC-INTERFACE
Application	Forcibly guided contacts
Mechanical service life	approx. $10^7$ cycles
Relay type	Electromechanical relay in accordance with IEC/EN 61810

### Insulation characteristics

Ovvoltage category	III
Degree of pollution	2

### Times

Typ. starting time with $U_s$	< 70 ms (when controlled via A1)
Typical release time	< 50 ms (on demand via A1)
Recovery time	500 ms (following demand of the safety function)

### Electrical properties

Maximum power dissipation for nominal condition	4.825 W ( $U_B = 30$ V, $U_S = 24$ V, $I_S = 30$ mA, $I_L^2 = 37$ A, $R_{contact} = 0.1$ $\Omega$ )
Nominal operating mode	100% operating factor
Rated insulation voltage	250 V AC
Rated surge voltage/insulation	Basic insulation 4 kV between all current paths and housing Safe isolation, reinforced insulation 6 kV between 250 V load current paths and 24 V logic paths

### Supply

Designation	A1/A2
Rated control circuit supply voltage $U_S$	21.6 V DC ... 28.8 V DC
Rated control circuit supply voltage $U_S$	24 V DC -10 % / +20 %
Rated control supply current $I_S$	30 mA
Inrush current	typ. 100 mA ( $\Delta t = 10$ ms at $U_s$ )
Filter time	1 ms (Test pulse width, high test pulse and low test pulse) 1 s (Test pulse rate, high test pulse and low test pulse)
Power consumption at $U_D$	650 mW (to $U_s$ )
Protective circuit	Serial protection against polarity reversal
	Suppressor diode, 38.6 V/600 W
Status display	1 x green LED (PWR)

### Output data

# PSR-PLC21-2CO-24DC-SC - Coupling relay

1480226

<https://www.phoenixcontact.com/us/products/1480226>



Relay: Changeover contacts (11/12/14, 21/22/24)

Output description	safety-related
	1oo1 structure
Number of outputs	2
Contact switching type	2 changeover contacts
Contact material	AgNi
Switching voltage	min. 5 V AC/DC max. 250 V AC/DC
Switching power	min. 150 mW (N/O contact / N/C contact)
Inrush current	max. 6 A (N/O contact) max. 4 A (N/C contact)
Switching capacity	6 A (AC1, 230 V) 3 A (AC15, 230 V) 6 A (DC1, 24 V, N/O contact) 4 A (DC1, 24 V, N/C contact) 3 A (DC13, 24 V, N/O contact)
Limiting continuous current	6 A (N/O contact, high demand) 4 A (N/O contact, low demand) 4 A (N/C contact, high-demand) 2.4 A (N/C contact, low-demand)
Sq. Total current	37 A <sup>2</sup> (N/O contact, high-demand, observe derating) 16 A <sup>2</sup> (N/C contact, high-demand, observe derating)
Switching frequency	max. 1 Hz
Mechanical service life	10 <sup>7</sup> cycles
Output fuse	6 A gL/gG 4 A gL/gG (for low-demand applications)

## Connection data

Conductor connection

Connection method	Screw connection
Conductor cross-section rigid	0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section flexible	0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section flexible, with ferrule without plastic sleeve	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section AWG	26 ... 14
Stripping length	8 mm
Screw thread	M3
Tightening torque	0.5 Nm

## Signaling

Operating voltage display	1 x green LED (PWR)
---------------------------	---------------------

## Dimensions

Width	14 mm
-------	-------

# PSR-PLC21-2CO-24DC-SC - Coupling relay

1480226

<https://www.phoenixcontact.com/us/products/1480226>



Height	80 mm
Depth	104 mm

## Material specifications

Color (Housing)	yellow (RAL 1018)
Housing material	PA

## Characteristics

Safety data: EN ISO 13849

Category	1
Performance level (PL)	c

Safety data: IEC 61508 – High-demand for 1-channel wiring (1oo1 structure)

Safety Integrity Level (SIL)	2
------------------------------	---

Safety data: IEC 61508 – Low-demand for 1-channel wiring (1oo1 structure)

Safety Integrity Level (SIL)	2
------------------------------	---

Safety data: EN IEC 62061

Safety Integrity Level (SIL)	2
------------------------------	---

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20
Min. degree of protection of inst. location	IP54
Ambient temperature (operation)	-20 °C ... 60 °C (observe derating)
Ambient temperature (storage/transport)	-20 °C ... 85 °C
Maximum altitude	≤ 2000 m (Above sea level)
Max. permissible humidity (storage/transport)	75 % (on average; 95% occasionally, non-condensing)
Max. permissible relative humidity (operation)	75 % (on average; 95% occasionally, non-condensing)
Shock	10g for $\Delta t = 11$ ms (continuous shock: 5g for $\Delta t = 16$ ms)
Vibration (operation)	10 Hz ... 150 Hz, amplitude 0.75 mm, 1g

## Approvals

CE

Identification	CE-compliant
----------------	--------------

Electronic devices in rail vehicles

Vibration (operation)	10 Hz ... 150 Hz, amplitude $\pm 0,75$ mm, 1g
-----------------------	---

## Mounting

Mounting type	DIN rail mounting
Assembly note	See derating curve
Mounting position	vertical or horizontal

# PSR-PLC21-2CO-24DC-SC - Coupling relay


1480226

<https://www.phoenixcontact.com/us/products/1480226>



## Drawings

Block diagram



# PSR-PLC21-2CO-24DC-SC - Coupling relay

1480226

<https://www.phoenixcontact.com/us/products/1480226>



## Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1480226>



### Functional Safety

Approval ID: 4478015124326



### cULus Listed

Approval ID: E140324

# PSR-PLC21-2CO-24DC-SC - Coupling relay

1480226

<https://www.phoenixcontact.com/us/products/1480226>



## Classifications

### ECLASS

ECLASS-13.0	27371601
ECLASS-15.0	27371601
ECLASS-15.0 ASSET	27250101

### ETIM

ETIM 9.0	EC001437
----------	----------

### UNSPSC

UNSPSC 21.0	39122300
-------------	----------

# PSR-PLC21-2CO-24DC-SC - Coupling relay

1480226

<https://www.phoenixcontact.com/us/products/1480226>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.	

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	51d1e278-3deb-43ec-9dbd-c5c8e6cae076

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

### Phoenix Contact USA

586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)