

# HC-Q12-I-CT-F - Contact insert

1418625

<https://www.phoenixcontact.com/us/products/1418625>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact insert, number of positions: 12+PE, size: D7, number of connections per position: 1, Socket, Crimp connection, 400 V, 12 A, 0.14 mm<sup>2</sup> ... 2.5 mm<sup>2</sup>

## Your advantages

- Can be keyed in seconds thanks to plastic profiles
- 16 coding options without loss of contact space
- Contact insert including IP65 sealing screw
- Shock and vibration-resistant in accordance with DIN EN 61373

## Commercial data

Item number	1418625
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF61
Product key	AF7ABJ
GTIN	4055626249384
Weight per piece (including packing)	15.2 g
Weight per piece (excluding packing)	14.7 g
Customs tariff number	85389099
Country of origin	CN

# HC-Q12-I-CT-F - Contact insert

1418625

<https://www.phoenixcontact.com/us/products/1418625>



## Technical data

### Notes

General	For HC-D7 housing, crimp contacts CK1,6-ED (crimp contacts not included in scope of supply)
General	Connectors may be operated only when there is no load/voltage.

### Mounting

Assembly note	To ensure correct use, installation in housing with IP54 protection or better is required
	Contact insert including IP67 sealing screw.

### Product properties

Product type	Contact insert with a fixed no. of positions
Series	HC-Q
Type	D7
Number of positions	12
Connection profile	12+PE
Contact numbering	1 - 12
Number of connections per position	1
Contact material type	turned
	rolled

### Insulation characteristics

Overvoltage category	III
Degree of pollution	3

### Dimensions

Dimensional drawing	
Width	21 mm
Height	43.1 mm
Length	21 mm

### Mechanical characteristics

Contact diameter	1.6 mm
------------------	--------

### Connection data

Connection technology	Crimp connection
	PE connection

# HC-Q12-I-CT-F - Contact insert

1418625

<https://www.phoenixcontact.com/us/products/1418625>



Number of connections per position	1
Connection in acc. with standard	IEC / EN

## Conductor connection

Conductor cross section	0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Connection cross section AWG	26 ... 14
Tightening torque	0.5 Nm ... 0.8 Nm (Mounting screws for mounting in the HEAVYCON housing)
Stripping length of the individual wire	8 mm
	6 mm (2.5 mm <sup>2</sup> )

## Electrical properties

Rated voltage (III/3)	400 V
Rated surge voltage	6 kV
Rated current	12 A

## Mechanical properties

Mechanical data	
Insertion/withdrawal cycles	≥ 500

## Material specifications

Flammability rating according to UL 94	V0
Contact material	Copper alloy
Contact surface material	Ag (alternatively Au)
Contact carrier material	PC
Standards/regulations	PC

## Environmental and real-life conditions

Ambient conditions	
Ambient temperature (operation)	-40 °C ... 125 °C (including heating up of contacts)

## Standards and regulations

Testing	
Standards/regulations	PC: Fire protection in rail vehicles - requirement sets R22, R23, and R24 acc. to DIN EN 45545-2 (Risk level HL1 - HL3)

# HC-Q12-I-CT-F - Contact insert




1418625

<https://www.phoenixcontact.com/us/products/1418625>


## Drawings

Dimensional drawing



Dimensional drawing: HC-Q 12-I-CT-F

Schematic diagram



Pin assignment connection side. Position A and B for coding profiles

## HC-Q12-I-CT-F - Contact insert

1418625

<https://www.phoenixcontact.com/us/products/1418625>



## Schematic diagram

HC-Q 12-I-CT-M		HC-Q 12-I-CT-F	
A	B	B	A
			
			
			
			
			
			
			
			
			
			
			
			
			
			
			

### Coding scheme


# HC-Q12-I-CT-F - Contact insert




1418625

<https://www.phoenixcontact.com/us/products/1418625>

Diagram



Diagram



# HC-Q12-I-CT-F - Contact insert

1418625

<https://www.phoenixcontact.com/us/products/1418625>



## Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1418625>

**DNV**

Approval ID: TAE000037S

 <b>CSA</b> Approval ID: 13631	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $mm^2$
keine	600 V	12 A	- 14	-

 <b>UL Recognized</b> Approval ID: E118976	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $mm^2$
keine	600 V	15 A	- 14	-

 <b>UL Recognized</b> Approval ID: E468743	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $mm^2$
keine	600 V	15 A	-	-

# HC-Q12-I-CT-F - Contact insert

1418625

<https://www.phoenixcontact.com/us/products/1418625>



## Classifications

### ECLASS

ECLASS-13.0	27440205
ECLASS-15.0	27440205

### ETIM

ETIM 9.0	EC000438
----------	----------

### UNSPSC

UNSPSC 21.0	39121500
-------------	----------

# HC-Q12-I-CT-F - Contact insert

1418625

<https://www.phoenixcontact.com/us/products/1418625>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)