

# HC-Q04-I-CT-M - Contact insert

1419898

<https://www.phoenixcontact.com/us/products/1419898>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact insert, number of positions: 4, size: D7, number of connections per position: 1, Pin, Crimp connection, 830 V, 40 A, 1.5 mm<sup>2</sup> ... 6 mm<sup>2</sup>, application: Power, Only suitable for plastic housings, four coding options

## Your advantages

- Shock and vibration-resistant in accordance with DIN EN 61373

## Commercial data

Item number	1419898
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF61
Product key	AF7ABJ
GTIN	4055626256177
Weight per piece (including packing)	12.8 g
Weight per piece (excluding packing)	12 g
Customs tariff number	85389099
Country of origin	CN

# HC-Q04-I-CT-M - Contact insert

1419898

<https://www.phoenixcontact.com/us/products/1419898>



## Technical data

### Notes

General	for HC-STA-D07 housing, CK 4,0 crimp contacts
General	Connectors may be operated only when there is no load/voltage.
General	Order crimp contacts separately

### Mounting

Assembly note	To ensure correct use, installation in housing with IP54 protection or better is required
---------------	---

### Product properties

Product type	Contact insert with a fixed no. of positions
Series	HC-HS
Application	Power
Type	D7
Number of positions	4
Connection profile	4
Contact numbering	1 - 4
Number of connections per position	1
Contact material type	turned

### Insulation characteristics

Overvoltage category	III
Degree of pollution	3

### Dimensions

Dimensional drawing	
Width	21 mm
Height	40 mm
Length	21 mm

### Mechanical characteristics

Contact diameter	4 mm
------------------	------

### Connection data

Connection technology	
Connection technology	Crimp connection
Number of connections per position	1
Connection in acc. with standard	IEC / EN

# HC-Q04-I-CT-M - Contact insert

1419898

<https://www.phoenixcontact.com/us/products/1419898>



## Conductor connection

Conductor cross section	1.5 mm <sup>2</sup> ... 6 mm <sup>2</sup>
Connection cross section AWG	16 ... 10
Tightening torque	0.5 Nm ... 0.8 Nm (Mounting screws for mounting in the HEAVYCON housing)
Stripping length of the individual wire	9 mm (1.5 mm <sup>2</sup> ... 6.0 mm <sup>2</sup> )

## Electrical properties

Rated voltage (III/3)	830 V
Rated surge voltage	8 kV
Rated current	40 A

## Mechanical properties

Mechanical data	
Insertion/withdrawal cycles	≥ 500

## Material specifications

Flammability rating according to UL 94	V0
Seal material	NBR, conductive
Contact material	Copper alloy
Contact surface material	Ag
Contact carrier material	PC
Standards/regulations	PC

## Environmental and real-life conditions

Ambient conditions	
Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 125 °C (including heating up of contacts)

## Standards and regulations

Constructional and testing regulations	DIN VDE 0627/86
	DIN VDE 0110/02.79
	DIN VDE 0110-1/04.97
	IEC 60664-1, DIN IEC 60512
	IEC 60352
Tests	DIN VDE 0627/86
	DIN VDE 0110/02.79
	DIN VDE 0110-1/04.97
	IEC 60664-1, DIN IEC 60512
	IEC 60352

## Testing

Standards/regulations	PC: Fire protection in rail vehicles - requirement sets R22, R23, and R24 acc. to DIN EN 45545-2 (Risk level HL1 - HL3)
-----------------------	---

# HC-Q04-I-CT-M - Contact insert


1419898

<https://www.phoenixcontact.com/us/products/1419898>



## Drawings

Dimensional drawing



Male insert


# HC-Q04-I-CT-M - Contact insert

1419898

<https://www.phoenixcontact.com/us/products/1419898>



Schematic diagram




# HC-Q04-I-CT-M - Contact insert

1419898

<https://www.phoenixcontact.com/us/products/1419898>



Diagram



Derating diagram

# HC-Q04-I-CT-M - Contact insert

1419898

<https://www.phoenixcontact.com/us/products/1419898>



## Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1419898>

UL Recognized				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $mm^2$
keine	600 V	50 A	- 8	-

UL Recognized				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $mm^2$
keine	600 V	45 A	-	-

# HC-Q04-I-CT-M - Contact insert

1419898

<https://www.phoenixcontact.com/us/products/1419898>



## Classifications

### ECLASS

ECLASS-13.0	27440205
ECLASS-15.0	27440205

### ETIM

ETIM 9.0	EC000438
----------	----------

### UNSPSC

UNSPSC 21.0	39121500
-------------	----------

# HC-Q04-I-CT-M - Contact insert

1419898

<https://www.phoenixcontact.com/us/products/1419898>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

### Phoenix Contact USA

586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)