

# SAC-4P-M12MS-M 8FS - Adapter

1519765

<https://www.phoenixcontact.com/us/products/1519765>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Adapter, 4-position, Plug straight M12, coding: A, on Socket straight M8, coding: A



## Commercial data

Item number	1519765
Packing unit	5 pc
Minimum order quantity	1 pc
Sales key	BF10
Product key	AF1GBA
GTIN	4046356019958
Weight per piece (including packing)	13.037 g
Weight per piece (excluding packing)	13.037 g
Customs tariff number	85366990
Country of origin	DE

# SAC-4P-M12MS-M 8FS - Adapter

1519765

<https://www.phoenixcontact.com/us/products/1519765>



## Technical data

### Product properties

Product type	M8/M12 adapters
Number of positions	4
No. of cable outlets	1
Coding	A

### Insulation characteristics

Overtoltage category	II
Degree of pollution	3

### Electrical properties

Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage $U_N$	30 V AC
	30 V DC
Nominal current $I_N$	4 A

### Signaling

Status display	no
Status display present	no

### Dimensions

Dimensional drawing	
Width	17 mm
Height	14.8 mm
Length	50.5 mm

### Material specifications

Flammability rating according to UL 94	HB
Seal material	NBR
Material of grip body	TPU, hardly inflammable, self-extinguishing
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Material for screw connection	Zinc die-cast, nickel-plated

### Connector

Connection 1	
Type	Plug straight M12

# SAC-4P-M12MS-M 8FS - Adapter

1519765

<https://www.phoenixcontact.com/us/products/1519765>



Number of positions	4
Coding type	A

## Connection 2

Type	Socket straight M8
Number of positions	4
Coding type	A

## Mechanical properties

### Mechanical data

Insertion/withdrawal cycles	≥ 100
-----------------------------	-------

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP65
	IP67
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 90 °C

## Standards and regulations

Standard designation	M12 connector
Standards/specifications	IEC 61076-2-101
Standard designation	M8 connector
Standards/specifications	IEC 61076-2-104

# SAC-4P-M12MS-M 8FS - Adapter




1519765

<https://www.phoenixcontact.com/us/products/1519765>

## Drawings

Dimensional drawing



M8/M12 adapter


# SAC-4P-M12MS-M 8FS - Adapter

1519765

<https://www.phoenixcontact.com/us/products/1519765>



Schematic diagram



Pin assignment M12 plug, 4-pos., A-coded, view plug side


# SAC-4P-M12MS-M 8FS - Adapter

1519765

<https://www.phoenixcontact.com/us/products/1519765>




Schematic diagram



Pin assignment M8 socket, 4-pos., view female side

Circuit diagram



Contact assignment of the M8/M12 adapter

# SAC-4P-M12MS-M 8FS - Adapter

1519765

<https://www.phoenixcontact.com/us/products/1519765>



## Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1519765>

	<b>EAC</b>	Approval ID: RU C-DE.AI30.B.01102
--	------------	-----------------------------------

<b>UL Listed</b> Approval ID: E221474				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $mm^2$
keine	30 V	4 A	-	-

<b>cUL Listed</b> Approval ID: E221474				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $mm^2$
keine	30 V	4 A	-	-

# SAC-4P-M12MS-M 8FS - Adapter

1519765

<https://www.phoenixcontact.com/us/products/1519765>



## Classifications

### ECLASS

ECLASS-13.0	27440106
ECLASS-15.0	27440106

### ETIM

ETIM 9.0	EC002925
----------	----------

### UNSPSC

UNSPSC 21.0	31251500
-------------	----------

# SAC-4P-M12MS-M 8FS - Adapter

1519765

<https://www.phoenixcontact.com/us/products/1519765>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.0 Climate Change

CO2e kg	0.061 kg CO2e
---------	---------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road

Middletown, PA 17057, United States

(+717) 944-1300

[info@phoenixcon.com](mailto:info@phoenixcon.com)