

CUC-V14-C1ZNI-S/R4P8 - RJ45 connector

1422664

<https://www.phoenixcontact.com/us/products/1422664>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



RJ45 connector, degree of protection: IP65/IP67, number of positions: 8, 1 Gbps, CAT5, material: Metal, connection method: IDC fast connection, connection cross section: AWG 23- 22, cable outlet: straight, Ethernet

Your advantages

- Push-pull ADVANCE connector
- Locking system to prevent inadvertent release
- Protected data transmission thanks to 360° shielding concept
- Highest ESD and EMC resistance for reliable transmission

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1422664 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | AB17 |
| Product key | ABNOAA |
| GTIN | 4055626311333 |
| Weight per piece (including packing) | 101.5 g |
| Weight per piece (excluding packing) | 88.647 g |
| Customs tariff number | 85366990 |
| Country of origin | PL |

CUC-V14-C1ZNI-S/R4P8 - RJ45 connector

1422664

<https://www.phoenixcontact.com/us/products/1422664>



Technical data

Notes

| | |
|---------|--|
| General | This product corresponds to the PROFINET Cabling and Interconnection Technology Guideline for PROFINET regulations, version 3.01, Order No. 2252 |
|---------|--|

Product properties

| | |
|----------------------|-----------------------------|
| Product type | Data connector (cable side) |
| Type | RJ45 |
| Sensor type | Ethernet |
| Number of positions | 8 |
| Connection profile | RJ45 |
| No. of cable outlets | 1 |
| Shielded | yes |
| Cable outlet | straight |

Insulation characteristics

| | |
|----------------------|---|
| Overvoltage category | I |
| Degree of pollution | 2 |

Electrical properties

| | |
|---|--|
| Rated voltage (III/3) | 72 V (DC) |
| Rated current | 1.75 A |
| Frequency range | to 100 MHz |
| Insulation resistance | > 500 MΩ |
| Nominal voltage U_N | 48 V |
| Transmission medium | Copper |
| Transmission speed | 1 Gbps |
| Transmission characteristics (category) | CAT5 |
| Transmission speed | 1 Gbps |
| Power transmission | PoE++ in accordance with: IEEE 802.3bt |

Connection data

Connection technology

| | |
|------------------------------|---|
| Connection method | IDC fast connection |
| Connection technology | QUICKON connection |
| Connection cross section AWG | 23 ... 22 (solid) 23 ... 22 (flexible) |
| Conductor cross section | 0.23 mm² ... 0.32 mm² (solid) 0.23 mm² ... 0.36 mm² (flexible) |

Dimensions

| | |
|-------|---------|
| Width | 22.4 mm |
|-------|---------|

CUC-V14-C1ZNI-S/R4P8 - RJ45 connector

1422664

<https://www.phoenixcontact.com/us/products/1422664>



| | |
|--------|-------|
| Height | 34 mm |
| Length | 95 mm |

Material specifications

| | |
|--|---------------|
| Flammability rating according to UL 94 | V0 |
| Seal material | NBR |
| Seal material, O-ring | NBR |
| Seal material cable seal | CR |
| Seal material | NBR |
| Seal material, pin connector pattern | NBR |
| Housing material | Metal |
| Housing surface material | nickel-plated |
| Contact material | Cu/Sn |
| Contact surface material | Au/Ni |
| Contact carrier material | PC |
| Material for screw connection | CuZn |

Cable/line

| | |
|-------------------------|----------------------|
| External cable diameter | 5.5 mm ... 10 mm |
| External cable diameter | 5.5 mm ... 10 mm |
| Cable cross section | 0.25 mm ² |

Mechanical properties

| | |
|-----------------------------|-------|
| Mechanical data | |
| Insertion/withdrawal cycles | ≥ 750 |

Environmental and real-life conditions

| | |
|---|------------------|
| Ambient conditions | |
| Degree of protection | IP65/IP67 |
| Ambient temperature (operation) | -40 °C ... 70 °C |
| Ambient temperature (storage/transport) | -40 °C ... 70 °C |
| Ambient temperature (assembly) | -10 °C ... 40 °C |

Standards and regulations

| | |
|--------------------------|-----------|
| Standards/specifications | IEC 61076 |
|--------------------------|-----------|

CUC-V14-C1ZNI-S/R4P8 - RJ45 connector

1422664

<https://www.phoenixcontact.com/us/products/1422664>



Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1422664>

| cULus Recognized | | | | |
|------------------|-----------------------|-----------------------|-------------------|----------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| keine | 56.5 V | 1.75 A | - | - |

CUC-V14-C1ZNI-S/R4P8 - RJ45 connector

1422664

<https://www.phoenixcontact.com/us/products/1422664>



Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27440290 |
| ECLASS-15.0 | 27440290 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC002943 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

CUC-V14-C1ZNI-S/R4P8 - RJ45 connector

1422664

<https://www.phoenixcontact.com/us/products/1422664>



Environmental product compliance

EU RoHS

| | |
|---|------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 6(c) |

China RoHS

| | |
|---|---------|
| Environment friendly use period (EFUP) | EFUP-50 |
| An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. | |

EU REACH SVHC

| | |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| SCIP | 83d16b7f-4685-4691-8e6d-59c9c7bfa9e1 |

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com