

# SAC-12P- 1,5-PUR/FR SCO - Sensor/actuator cable



1430653

<https://www.phoenixcontact.com/us/products/1430653>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 12-position, PUR halogen-free, black RAL 9005, free cable end, on Socket angled M12 SPEEDCON, coding: A, cable length: 1.5 m

## Your advantages

- Easy and safe: 100 % electrically tested plug-in components
- Save time, thanks to installation with SPEEDCON fast locking system
- Our standard: robust halogen-free PUR cable
- Save space – with high-pos. connectors

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1430653       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | BF03          |
| Product key                          | AF1CGA        |
| GTIN                                 | 4046356456463 |
| Weight per piece (including packing) | 112 g         |
| Weight per piece (excluding packing) | 110 g         |
| Customs tariff number                | 85444290      |
| Country of origin                    | DE            |

# SAC-12P- 1,5-PUR/FR SCO - Sensor/actuator cable



1430653

<https://www.phoenixcontact.com/us/products/1430653>

## Technical data

### Product properties

|                      |                       |
|----------------------|-----------------------|
| Product type         | Sensor/actuator cable |
| Application          | Standard              |
| Number of positions  | 12                    |
| No. of cable outlets | 1                     |
| Shielded             | no                    |
| Coding               | A                     |

### Insulation characteristics

|                      |    |
|----------------------|----|
| Overvoltage category | II |
| Degree of pollution  | 3  |

### Material specifications

|                                        |                                             |
|----------------------------------------|---------------------------------------------|
| Flammability rating according to UL 94 | V0                                          |
| Seal material                          | NBR                                         |
| Material of grip body                  | TPU, hardly inflammable, self-extinguishing |
| Contact material                       | CuZn                                        |
| Contact surface material               | Ni/Au                                       |
| Contact carrier material               | PA 6.6                                      |
| Material for screw connection          | Zinc die-cast, nickel-plated                |

### Electrical properties

|                       |                            |
|-----------------------|----------------------------|
| Insulation resistance | $\geq 100 \text{ M}\Omega$ |
| Nominal voltage $U_N$ | 30 V AC                    |
|                       | 30 V DC                    |
| Nominal current $I_N$ | 1.5 A                      |

### Signaling

|                        |    |
|------------------------|----|
| Status display         | no |
| Status display present | no |

### Connection data

#### Conductor connection

|                   |                        |
|-------------------|------------------------|
| Tightening torque | 0.4 Nm (M12 connector) |
|-------------------|------------------------|

### Connector

#### Connection 1

|      |                |
|------|----------------|
| Type | free cable end |
|------|----------------|

#### Connection 2

|                     |                            |
|---------------------|----------------------------|
| Type                | Socket angled M12 SPEEDCON |
| Number of positions | 12                         |

# SAC-12P- 1,5-PUR/FR SCO - Sensor/actuator cable



1430653

<https://www.phoenixcontact.com/us/products/1430653>

|              |          |
|--------------|----------|
| Locking type | SPEEDCON |
| Coding type  | A        |

## Cable/line

|              |       |
|--------------|-------|
| Cable length | 1.5 m |
|--------------|-------|

### PUR halogen-free black [PUR]

|                                               |                                                                                                                                       |
|-----------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------|
| Dimensional drawing                           |                                                     |
| Cable weight                                  | 17 kg/km                                                                                                                              |
| Number of positions                           | 12                                                                                                                                    |
| Shielded                                      | no                                                                                                                                    |
| Cable type                                    | PUR halogen-free black [PUR]                                                                                                          |
| Conductor structure signal line               | 18x 0.10 mm                                                                                                                           |
| AWG signal line                               | 26                                                                                                                                    |
| Conductor cross section                       | 12x 0.14 mm <sup>2</sup> (Signal line)                                                                                                |
| Wire diameter incl. insulation                | 1 mm ±0.05 mm (Signal line)                                                                                                           |
| External cable diameter                       | 7.20 mm                                                                                                                               |
| Outer sheath, material                        | PUR                                                                                                                                   |
| External sheath, color                        | black RAL 9005                                                                                                                        |
| Conductor material                            | Tin-plated Cu litz wires                                                                                                              |
| Material wire insulation                      | PP                                                                                                                                    |
| Single wire, color                            | white, brown, green, yellow, gray, pink, blue, red, black, violet, gray/pink, red/blue                                                |
| Overall twist                                 | 12 wires twisted in layers                                                                                                            |
| Max. conductor resistance                     | 142 Ω/km                                                                                                                              |
| Nominal voltage, cable                        | ≤ 300 V                                                                                                                               |
| Test voltage                                  | ≥ 1500 V                                                                                                                              |
| Minimum bending radius, fixed installation    | 5 x D                                                                                                                                 |
| Minimum bending radius, flexible installation | 10 x D                                                                                                                                |
| Smallest bending radius, fixed installation   | 36 mm                                                                                                                                 |
| Smallest bending radius, movable installation | 72 mm                                                                                                                                 |
| Dynamic load capacity (bending)               | Max. bending cycles: 4000000, Bending radius: 54 mm, Traversing path: 10 m, Traversing rate: 3 m/s, Acceleration: 10 m/s <sup>2</sup> |
| Halogen-free                                  | in accordance with DIN EN 50267-2-1                                                                                                   |
| Flame resistance                              | in acc. to UL VW1<br>DIN EN 60332-1-2                                                                                                 |
| Resistance to oil                             | EN 60811-2-1                                                                                                                          |

# SAC-12P- 1,5-PUR/FR SCO - Sensor/actuator cable



1430653

<https://www.phoenixcontact.com/us/products/1430653>

|                                 |                                                              |
|---------------------------------|--------------------------------------------------------------|
| Other resistance                | EN 50525-2-21:2012-01                                        |
|                                 | partly UV-resistant (in accordance with DIN EN ISO 4892-2-A) |
| Special properties              | Low adhesion surface                                         |
| Ambient temperature (operation) | -40 °C ... 80 °C (cable, fixed installation)                 |
|                                 | -5 °C ... 80 °C (Cable, flexible installation)               |

## Environmental and real-life conditions

### Ambient conditions


|                                                                   |                                                 |
|-------------------------------------------------------------------|-------------------------------------------------|
| Degree of protection                                              | IP65                                            |
|                                                                   | IP67                                            |
|                                                                   | IP68                                            |
| Ambient temperature (operation) (male connector/female connector) | -25 °C ... 85 °C (Plug / socket)                |
| Ambient temperature (operation) (Cable, fixed installation)       | -40 °C ... 80 °C (cable, fixed installation)    |
| Ambient temperature (operation) (Cable, flexible installation)    | -20 °C ... 80 °C (Cable, flexible installation) |

## Standards and regulations

|                          |                 |
|--------------------------|-----------------|
| Standard designation     | M12 connector   |
| Standards/specifications | IEC 61076-2-101 |


## Drawings

Dimensional drawing



Socket M12-SPEEDCON, angled, shielded

Schematic diagram




Pin assignment M12, 12-pos., female side view

1430653

<https://www.phoenixcontact.com/us/products/1430653>

Circuit diagram



Contact assignment of the M12 socket

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1430653>

|                                                                                                                                       |                                |                                |                   |                               |
|---------------------------------------------------------------------------------------------------------------------------------------|--------------------------------|--------------------------------|-------------------|-------------------------------|
| <div><b>UL Listed</b><br/>Approval ID: E221474</div> |                                |                                |                   |                               |
|                                                                                                                                       | Nominal voltage U <sub>N</sub> | Nominal current I <sub>N</sub> | Cross section AWG | Cross section mm <sup>2</sup> |
| keine                                                                                                                                 |                                |                                |                   |                               |
|                                                                                                                                       | 30 V                           | 1 A                            | -                 | -                             |

**EAC-RoHS**  
Approval ID: RU D-DE.HB35.B.00387

# SAC-12P- 1,5-PUR/FR SCO - Sensor/actuator cable



1430653

<https://www.phoenixcontact.com/us/products/1430653>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27060311 |
| ECLASS-15.0 | 27060311 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC001855 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 26121600 |
|-------------|----------|

# SAC-12P- 1,5-PUR/FR SCO - Sensor/actuator cable



1430653

<https://www.phoenixcontact.com/us/products/1430653>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

### EF3.0 Climate Change

|         |                |
|---------|----------------|
| CO2e kg | 10.073 kg CO2e |
|---------|----------------|

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)