

CK8,0-ED-35,00F AG - Crimp contact



1550052

<https://www.phoenixcontact.com/in/products/1550052>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimp contact, series: HC-M-...-35, Socket, turned, contact diameter: 8 mm, connection cross section: 35 mm² ... 35 mm², AWG 2...2, contact material: Cu alloy

Commercial data

Item number	1550052
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BF7
Product key	AF7AIG
GTIN	4067923025189
Weight per piece (including packing)	19.56 g
Weight per piece (excluding packing)	3.333 g
Customs tariff number	85366990
Country of origin	DE

CK8,0-ED-35,00F AG - Crimp contact

1550052

<https://www.phoenixcontact.com/in/products/1550052>



Technical data

Notes

General	for HC-M-...-35 contact carriers
Assembly note	The quality of a crimp connection is determined by DIN EN 60352-2.
Assembly note	The contacts are qualified for crimping dies in accordance with DIN 46235. Klauke, for example, offers an appropriate tool: Crimping dies from the D22 series are required for the EKM6022 battery-powered hydraulic crimping pliers. Due to the narrow crimping width of 5 mm, it is very important to make two compressions next to one another. For the EK12042 model, crimping dies from the HD13 series are required. Due to a wider crimping process, only one compression is required.

Product properties

Product type	Crimp contact
Series	HC-M-...-35
Contact material type	turned

Connection data

Connection technology	
Contact connection type	Socket
Connection method	Crimp connection

Conductor connection	
Stripping length	16 mm
Connection cross section	35 mm ² ... 35 mm ²
Connection cross section AWG	2 ... 2

Material specifications

Material Contact	Cu alloy (lead-free)
Material Contact surface	Ag

Dimensions

Diameter (Contact diameter)	8 mm
-----------------------------	------

Mechanical properties

Mechanical data	
Insertion/withdrawal cycles	≥ 500

Environmental and real-life conditions

Ambient conditions	
Ambient temperature (operation)	-40 °C ... 125 °C

CK8,0-ED-35,00F AG - Crimp contact

1550052

<https://www.phoenixcontact.com/in/products/1550052>



Classifications

ECLASS

ECLASS-13.0	27440204
ECLASS-15.0	27440204

ETIM

ETIM 9.0	EC000796
----------	----------

UNSPSC

UNSPSC 21.0	39121500
-------------	----------

CK8,0-ED-35,00F AG - Crimp contact

1550052

<https://www.phoenixcontact.com/in/products/1550052>



Environmental product compliance

EU RoHS

Fulfils EU RoHS substance requirements	Yes, No exemptions
--	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

info@phoenixcontact.co.in