

1433168

<https://www.phoenixcontact.com/us/products/1433168>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



AS-Interface distributor with IP67 protection for 1 flat-ribbon conductor, 2-pos., with screw connection, angled

Commercial data

Item number	1433168
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF10
Product key	AF1GFA
GTIN	4046356346252
Weight per piece (including packing)	24.7 g
Weight per piece (excluding packing)	24.7 g
Customs tariff number	85366990
Country of origin	DE

1433168

<https://www.phoenixcontact.com/us/products/1433168>

Technical data

Product properties

Product type	Network distributor box
Number of positions	2
Thread type	Pg9

Insulation characteristics

Degree of pollution	3
---------------------	---

Electrical properties

Nominal voltage U_N	30 V DC
Nominal current I_N	4 A
Transmission medium	Copper

Connection data

Connection technology

Connection method	AS-i penetration technique
Outside diameter	4 mm ... 6 mm

Interfaces

Bus system	AS-Interface
------------	--------------

Signaling

Status display	no
Status display present	no

Dimensions

External dimensions

Outside diameter	4 mm ... 6 mm
------------------	---------------

Material specifications

Material Housing	PA
Seal material	Neoprene
	FKM

Connector

Connection 1

Type	Load center AS-i Screw locking
Number of positions	2
Locking type	Screw locking mechanism
Material	CuZn (Contact)
	Sn (Contact surface)

1433168

<https://www.phoenixcontact.com/us/products/1433168>

	PA (Contact carrier)
	PA (Housing)

Connection 2

Type	Screw terminal block angled
Number of positions	2
Material	CuZn (Contact)
	CuSnZn (Contact surface)
	PA (Contact carrier)

Cable/line

Stripping length of the individual wire	5 mm
---	------


Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 70 °C
Ambient temperature (storage/transport)	-25 °C ... 70 °C

Drawings

Dimensional drawing



1433168

<https://www.phoenixcontact.com/us/products/1433168>

Classifications

ECLASS

ECLASS-13.0	27440106
ECLASS-15.0	27440106

ETIM

ETIM 9.0	EC002925
----------	----------

UNSPSC

UNSPSC 21.0	31251500
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	26a936e1-192c-42f9-a6a6-828a1e6c8145

EF3.0 Climate Change

CO2e kg	1.132 kg CO2e
---------	---------------