

# SACC-DSIV-MS-4CON-L90 SH SCO - Device connector rear mounting



1439913

<https://www.phoenixcontact.com/us/products/1439913>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector rear mounting, 4-position, Pin, angled, M12-SPEEDCON, A-coding, THR and wave soldering, this item is expected to be lead-free from Q2 2026 in accordance with RoHS II without exception 6c (Pb < 0.1%), a lead-free alternative is possible on request in advance

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1439913       |
| Packing unit                         | 10 pc         |
| Minimum order quantity               | 1 pc          |
| Sales key                            | AB26          |
| Product key                          | ABQEAGA       |
| GTIN                                 | 4046356476645 |
| Weight per piece (including packing) | 12.65 g       |
| Weight per piece (excluding packing) | 9.01 g        |
| Customs tariff number                | 85366990      |
| Country of origin                    | DE            |

# SACC-DSIV-MS-4CON-L90 SH SCO - Device connector rear mounting



1439913

<https://www.phoenixcontact.com/us/products/1439913>

## Technical data

### Notes

|                    |   |
|--------------------|---|
| Order information: | Lock nut is included in the scope of delivery |
|--------------------|---|

### Mounting

|               |  |
|---------------|--|
| Mounting type | Rear mounting (M12 x 1, with flat nut) |
|---------------|--|

### Product properties

|                     |                                   |
|---------------------|-----------------------------------|
| Product type        | Circular connectors (device side) |
| Number of positions | 4                                 |
| Shielded            | yes                               |
| Coding              | A                                 |
| Thread type         | M12                               |

### Insulation characteristics

|                     |    |
|---------------------|----|
| Ovvoltage category  | II |
| Degree of pollution | 3  |

### Material specifications

|  |        |
|--|--------|
| Material Housing                       | GD-Zn  |
| Material Housing surface               | Ni     |
| Material Insulating body               | PA 6.6 |
| Material Contact                       | CuZn   |
| Material Contact surface               | Au     |
| Material Seal                          | NBR    |
| Flammability rating according to UL 94 | V0     |

### Electrical properties

|                       |                            |
|-----------------------|----------------------------|
| Contact resistance    | $\leq 3 \text{ m}\Omega$   |
| Insulation resistance | $\geq 100 \text{ M}\Omega$ |
| Nominal voltage $U_N$ | 250 V                      |
| Nominal current $I_N$ | 4 A                        |

### Connection data

|                         |                        |
|-------------------------|------------------------|
| Conductor connection    |                        |
| Connection method       | THR and wave soldering |
| Contact connection type | Pin                    |

### Connector

|              |     |
|--------------|-----|
| Connection 1 |     |
| Head design  | Pin |

# SACC-DSIV-MS-4CON-L90 SH SCO - Device connector rear mounting



1439913

<https://www.phoenixcontact.com/us/products/1439913>

|                   |          |
|-------------------|----------|
| Head cable outlet | angled   |
| Head thread type  | M12      |
| Head locking type | SPEEDCON |
| Coding            | A        |

## Environmental and real-life conditions

### Ambient conditions

|   |                                  |
|---|----------------------------------|
| Degree of protection  | IP67                             |
| Ambient temperature (operation) (male connector/female connector) | -25 °C ... 85 °C (Plug / socket) |

# SACC-DSIV-MS-4CON-L90 SH SCO - Device connector rear mounting




1439913

<https://www.phoenixcontact.com/us/products/1439913>

## Drawings

Schematic diagram



Pin assignment M12 plug, 4-pos., A-coded, view plug side

# SACC-DSIV-MS-4CON-L90 SH SCO - Device connector rear mounting



1439913

<https://www.phoenixcontact.com/us/products/1439913>

## Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1439913>

| UL Recognized |  | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $mm^2$ |
|---------------|--|-----------------------|-----------------------|-------------------|----------------------|
| keine         |  | 250 V                 | 4 A                   | 22                | -                    |
|               |  |                       |                       |                   |                      |

# SACC-DSIV-MS-4CON-L90 SH SCO - Device connector rear mounting



1439913

<https://www.phoenixcontact.com/us/products/1439913>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27440110 |
| ECLASS-15.0 | 27440110 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC003568 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# SACC-DSIV-MS-4CON-L90 SH SCO - Device connector rear mounting



1439913

<https://www.phoenixcontact.com/us/products/1439913>

## Environmental product compliance

### EU RoHS

|   |      |
|---|------|
| Fulfills EU RoHS substance requirements | Yes  |
| Exemption                               | 6(c) |

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-50<br><br>An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |
|--|--|

### EU REACH SVHC

|                                     |                                      |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1)                 |
| SCIP                                | 5391c97a-318d-4574-862b-f01fbeeb5c71 |

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)