

SACC-DSIV-FS-8CON-L180-THR SH - Device connector rear mounting



1557549

<https://www.phoenixcontact.com/us/products/1557549>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Commercial data

Item number	1557549
Packing unit	60 pc
Minimum order quantity	60 pc
Sales key	AB23
Product key	ABQAIA
GTIN	4046356284066
Weight per piece (including packing)	11.73 g
Weight per piece (excluding packing)	9.382 g
Customs tariff number	85366990
Country of origin	DE

SACC-DSIV-FS-8CON-L180-THR SH - Device connector rear mounting



1557549

<https://www.phoenixcontact.com/us/products/1557549>

Technical data

Notes

Order information:	Lock nut is included in the scope of delivery
--------------------	-----------------------------------------------

Mounting

Mounting type	Rear mounting (M12 x 1, with flat nut)
---------------	----------------------------------------

Product properties

Product type	Circular connectors (device side)
Number of positions	8
Shielded	yes
Coding	A
Thread type	M12

Insulation characteristics

Ovvoltage category	II
Degree of pollution	3

Material specifications

Material Housing	GD-Zn
Material Housing surface	Ni
Material Insulating body	PA 6.6
Material Contact	Cu alloy
Material Contact surface	Au
Material Seal	NBR
Flammability rating according to UL 94	HB

Electrical properties

Contact resistance	$\leq 3 \text{ m}\Omega$
Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	60 V
Nominal current I_N	4 A

Connection data

Conductor connection	
Connection method	THR solder connection
Contact connection type	Socket

Connector

Connection 1	
Head design	Socket

SACC-DSIV-FS-8CON-L180-THR SH - Device connector rear mounting



1557549

<https://www.phoenixcontact.com/us/products/1557549>

Head cable outlet	straight
Head thread type	M12
Head locking type	SPEEDCON
Coding	A

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 85 °C (Plug / socket)

Standards and regulations

Standard designation	M12 circular connector
Standards/specifications	according to IEC 61076-2-101

SACC-DSIV-FS-8CON-L180-THR SH - Device connector rear mounting




1557549

<https://www.phoenixcontact.com/us/products/1557549>

Drawings

Schematic diagram



Pin assignment M12 socket, 8-pos., A-coded, view female side

SACC-DSIV-FS-8CON-L180-THR SH - Device connector rear mounting



1557549

<https://www.phoenixcontact.com/us/products/1557549>

Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1557549>

UL Recognized		Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine					
		30 V	2 A	24	-

SACC-DSIV-FS-8CON-L180-THR SH - Device connector rear mounting



1557549

<https://www.phoenixcontact.com/us/products/1557549>

Classifications

ECLASS

ECLASS-13.0	27440110
ECLASS-15.0	27440110

ETIM

ETIM 9.0	EC003568
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SACC-DSIV-FS-8CON-L180-THR SH - Device connector rear mounting



1557549

<https://www.phoenixcontact.com/us/products/1557549>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50 An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
----------------------------------------	--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	b8f96236-fb98-4fba-8e8e-ad9d5ad26a7d

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com