

SACB-4/ 4-10,0PUR SCO P - Distributor box



1452408

<https://www.phoenixcontact.com/us/products/1452408>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Distributor box, application: Standard, connection method: M12 socket Plastic, number of slots: 4, number of positions: 4, coding: A, slot assignment: single, status display: no, Universal; master cable connection: Fixed connection 180°, PUR/PVC, cable length: 10 m, shielding: no

Your advantages

- Safety in the field, thanks to molded housing and high degree of protection
- Save time, thanks to installation with SPEEDCON fast locking system

Commercial data

Item number	1452408
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF41
Product key	AF3CBA
GTIN	4046356553797
Weight per piece (including packing)	930 g
Weight per piece (excluding packing)	911 g
Customs tariff number	85444290
Country of origin	DE

SACB-4/ 4-10,0PUR SCO P - Distributor box

1452408

<https://www.phoenixcontact.com/us/products/1452408>



Technical data

Notes

Assembly note	NOTE: Observe the permissible bending radii when routing cables, since the degree of protection may be at risk if the bending forces are too high. Reduce mechanical loads upstream of the connector, e.g., by using cable ties.
Note on application	Unused slots are to be sealed off prior to commissioning. Suitable sealing elements are to be found under "Accessories".

Product properties

Product type	Distributor box
Application	Standard
Number of positions	4
Number of slots	4
Coding	A
LED	no

Electrical properties

Nominal voltage U_N	120 V AC
	120 V DC
Rated current, total	12 A
Max. current carrying capacity per path	2 A
Current carrying capacity per slot	4 A

Connection data

Conductor connection	
Sensor/actuator connection system	M12 socket
Tightening torque slot sensor/actuator cable	0.4 Nm
Tightening torque of mounting screw for fixing the housing	0.5 Nm

Connection assignment	
Slot/position = Wire color or connection	1 / 4 (A) = WH
	2 / 4 (A) = GN
	3 / 4 (A) = YE
	4 / 4 (A) = GY
	1-4 / 1 (+ 120 V) = BN
	1-4 / 3 (0 V) = BU
	1-4 / 5 (PE) = GNYE

Signaling

Status display present	no
------------------------	----

Dimensions


SACB-4/ 4-10,0PUR SCO P - Distributor box



1452408

<https://www.phoenixcontact.com/us/products/1452408>

Dimensional drawing



Width

54 mm

Height

23 mm

Length

117 mm

Material specifications


Material Threaded sleeve	PBT
Material Housing	PBT
Material Molding compound	PUR
Flammability rating according to UL 94	V0
Seal material O-ring	NBR
Contact material	Cu alloy
Contact surface material	gold-plated
Contact carrier material	PA

Cable/line

Cable length	10 m
--------------	------

PUR/PVC black [PUR]

Dimensional drawing



Cable weight

77.9 kg/km

UL AWM Style

20549

Number of positions

7

Shielded

no

Cable type

PUR/PVC black [PUR]

Conductor structure signal line

19x 0.15 mm

AWG signal line

22

Conductor structure, voltage supply

42x 0.15 mm

AWG power supply

18

Conductor cross section

4x 0.34 mm² (Signal line)

3x 0.75 mm² (power line)

SACB-4/ 4-10,0PUR SCO P - Distributor box

1452408

<https://www.phoenixcontact.com/us/products/1452408>



Wire diameter incl. insulation	1.3 mm ± 0.1 mm (Signal line) 1.8 mm ± 0.1 mm (power line)
External cable diameter	6.90 mm ± 0.2 mm
Outer sheath, material	PUR
External sheath, color	black RAL 9005
Conductor material	Bare Cu litz wires
Material wire insulation	PVC
Single wire, color	brown, blue, green/yellow, white, green, yellow, gray
Inner sheath thickness	≥ 0.15 mm
Thickness, outer sheath	≥ 0.38 mm
Overall twist	Wires twisted in layers
Nominal voltage, cable	300 V
Test voltage	2000 V
Minimum bending radius, fixed installation	7.5 x D
Minimum bending radius, flexible installation	10 x D
Smallest bending radius, fixed installation	52 mm
Smallest bending radius, movable installation	69 mm
Dynamic load capacity (bending)	Max. bending cycles: 1500000, Bending radius: 69 mm, Traversing path: 2 m, Traversing rate: 2 m/s
Flame resistance	DIN EN 50265
Resistance to oil	according to VDE 0472 Part 803
Other resistance	Highly resistant to acids, alkaline solutions and solvents
Special properties	Silicone-free
Ambient temperature (operation)	-40 °C ... 90 °C (cable, fixed installation) -5 °C ... 80 °C (Cable, flexible installation) 80 °C (in acc. with UL)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
	IP67
Ambient temperature (operation)	-25 °C ... 80 °C

Standards and regulations

Standard designation	M12 connector
Standards/specifications	IEC 61076-2-101

SACB-4/ 4-10,0PUR SCO P - Distributor box




1452408

<https://www.phoenixcontact.com/us/products/1452408>

Drawings

Dimensional drawing




SACB-4/ 4-10,0PUR SCO P - Distributor box

1452408

<https://www.phoenixcontact.com/us/products/1452408>




Schematic diagram



M12 slot, socket, 4-pos.

Circuit diagram



SACB-4/ 4-10,0PUR SCO P - Distributor box



1452408

<https://www.phoenixcontact.com/us/products/1452408>

Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1452408>

cUL Recognized		Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine		120 V	-	-	-

UL Recognized		Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine		120 V	-	-	-

SACB-4/ 4-10,0PUR SCO P - Distributor box

1452408

<https://www.phoenixcontact.com/us/products/1452408>



Classifications

ECLASS

ECLASS-13.0	27440108
ECLASS-15.0	27440108

ETIM

ETIM 9.0	EC002585
----------	----------

UNSPSC

UNSPSC 21.0	31251500
-------------	----------

SACB-4/ 4-10,0PUR SCO P - Distributor box

1452408

<https://www.phoenixcontact.com/us/products/1452408>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com