

PS-EE-2G-DIODE/12-48DC/2X10/SC - Redundancy module

1584245
<https://www.phoenixcontact.com/pc/products/1584245>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Redundancy module ESSENTIAL DIODE, DIN rail mounting, 12 V DC ... 48 V DC, 2x 10 A DC

Commercial data

Item number	1584245
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	CMB543
GTIN	4067923078031
Weight per piece (including packing)	421 g
Weight per piece (excluding packing)	345 g
Customs tariff number	85363030
Country of origin	CN

PS-EE-2G-DIODE/12-48DC/2X10/SC - Redundancy module



1584245

<https://www.phoenixcontact.com/pc/products/1584245>

Technical data

Input data

Nominal input voltage range	12 V DC ... 48 V DC
Input voltage range	10 V DC ... 60 V DC
Nominal input current (I_N)	2x 10 A DC (-20 °C ... 45 °C)
	1x 20 A DC (-20 °C ... 45 °C)
Reverse polarity protection	yes, < 60 V
Voltage drop, input/output	typ. 0.75 V
Transient surge protection	Varistor

Output data

Efficiency	≥ 94 % (≥ 12 V DC)
	≥ 96 % (≥ 24 V DC)
	≥ 98 % (≥ 48 V DC)
Nominal output voltage	$U_{in} - 0,8 \text{ V}$
Nominal output current (I_N)	20 A
Derating	60 °C ... 70 °C (2 % / K)

Connection data

Conductor connection

Connection method	Screw connection
rigid	0.2 mm ² ... 6 mm ²
flexible	0.2 mm ² ... 4 mm ²
flexible with ferrule without plastic sleeve	0.25 mm ² ... 4 mm ²
	1.5 mm ² (recommended)
flexible with ferrule with plastic sleeve	0.25 mm ² ... 4 mm ²
	1.5 mm ² (recommended)
rigid (AWG)	24 ... 10 (Cu)
Stripping length	8 mm (rigid/flexible/ferrule without plastic sleeve)
	11 mm (Ferrule with plastic sleeve)
Tightening torque	0.5 Nm ... 0.6 Nm
Drive form screw head	Slotted L

Conductor connection

Connection method	Screw connection
rigid	0.5 mm ² ... 16 mm ²
flexible	0.5 mm ² ... 16 mm ²
flexible with ferrule without plastic sleeve	0.5 mm ² ... 16 mm ²
	4 mm ² (recommended)
flexible with ferrule with plastic sleeve	0.5 mm ² ... 16 mm ²
	4 mm ² (recommended)
rigid (AWG)	20 ... 6 (Cu)

PS-EE-2G-DIODE/12-48DC/2X10/SC - Redundancy module



1584245

<https://www.phoenixcontact.com/pc/products/1584245>

Stripping length	10 mm (rigid/flexible/ferrule without plastic sleeve) 13 mm (Ferrule with plastic sleeve)
Tightening torque	1.2 Nm ... 1.5 Nm
Drive form screw head	Slotted L

Conductor connection

Connection method	Push-in connection
rigid	0.2 mm² ... 1.5 mm²
flexible	0.2 mm² ... 1.5 mm²
flexible with ferrule without plastic sleeve	0.25 mm² ... 1.5 mm²
flexible with ferrule with plastic sleeve	0.25 mm² ... 0.75 mm²
rigid (AWG)	24 ... 16 (Cu)
Stripping length	10 mm (rigid/flexible/ferrule without plastic sleeve) 99 mm (Ferrule with plastic sleeve)

Signaling

LED signaling

Types of signaling	DC OK (green)
Signal threshold	Input1 OK (LED lights up green) Input2 OK (LED lights up green)

Signal output Relay 13/14

Connection labeling	3.1, 3.2
Switch contact (floating)	N/O contact
Digital	30 V DC 1 A
Signal option	Redundancy OK

Signal output Relay 23/24

Connection labeling	3.3, 3.4
Switch contact (floating)	N/O contact
Digital	30 V DC 1 A
Signal option	Redundancy OK

Electrical properties

Insulation voltage input/output	500 V AC
Insulation voltage input, output / housing	500 V AC

Product properties

Product type	Redundancy module
Product family	ESSENTIAL DIODE
MTBF (IEC 61709, SN 29500)	> 2992278 h (25 °C) > 1874605 h (40 °C) > 1594343 h (45 °C)

PS-EE-2G-DIODE/12-48DC/2X10/SC - Redundancy module



1584245

<https://www.phoenixcontact.com/pc/products/1584245>

LED	yes
-----	-----

Insulation characteristics

Protection class	III
Degree of pollution	2

Dimensions

Item dimensions

Width	40 mm
Height	124 mm
Depth	126 mm

Installation dimensions

Installation distance right/left	10 mm / 10 mm
Installation distance top/bottom	30 mm / 30 mm

Mounting

Mounting type	DIN rail mounting
Mounting position	horizontal DIN rail NS 35, EN 60715

Material specifications

Flammability rating according to UL 94 (housing / terminal blocks)	V0
Housing material	Metal
Housing material	Aluminum (AlMg3) / sheet steel, zinc-plated
Foot latch material	Sheet steel, zinc-plated

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-20 °C ... 70 °C (Derating: > 45°C; 2.5%/K)
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Maximum altitude	≤ 5000 m (> 2000 m, Derating: 10 %/1000 m)
Max. permissible relative humidity (operation)	≤ 95 % (at 25 °C, non-condensing)
Dry heat (IEC 60068-2-2)	70 °C (16 h)
Humid heat cyclic (IEC 60068-2-30)	55 °C (95 %, 2 x 23 h)
Cold (IEC 60068-2-1)	- 25 °C (16 h)
Shock (operation)	18 ms, 30g, per spatial direction (IEC 60068-2-27)
Vibration (operation)	< 15 Hz, amplitude ±2.5 mm (IEC 60068-2-6)
	15 Hz ... 150 Hz, 2.3g, 90 min.

Standards and regulations

Electrical safety

Standard designation	Electrical safety
----------------------	-------------------

PS-EE-2G-DIODE/12-48DC/2X10/SC - Redundancy module



1584245

<https://www.phoenixcontact.com/pc/products/1584245>

Standards/specifications	IEC 61010-1 (SELV)
Protective extra-low voltage	
Standard designation	Protective extra-low voltage
Standards/specifications	IEC 61010-1 (SELV)

Approvals

UL

Identification	UL/C-UL Listed UL 61010-1
----------------	---------------------------

UL

Identification	UL/C-UL Listed UL 61010-2-201
----------------	-------------------------------

CB scheme

Identification	CB scheme (IEC 61010-1, IEC 61010-2-201, IEC 62368-1)
----------------	---

EMC data

Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
Low Voltage Directive	Conformance with Low Voltage Directive 2014/35/EC
Noise immunity	EN 61000-6-2:2019

Fast transients (burst)

Standards/regulations	EN 61000-4-4
-----------------------	--------------

Fast transients (burst)

Input	1 kV (Test Level 2 - asymmetrical)
Output	1 kV (Test Level 2 - asymmetrical)
Signal	1 kV (Test Level 3 - asymmetrical)
Comments	Criterion A

Surge voltage load (surge)

Standards/regulations	EN 61000-4-5
-----------------------	--------------

Surge voltage load (surge)

Input	0.5 kV (Test Level 2 - symmetrical)
	1 kV (Test Level 2 - asymmetrical)
Output	0.5 kV (Test Level 2 - symmetrical)
	1 kV (Test Level 2 - asymmetrical)
Signal	1 kV (Test Level 2 - asymmetrical)
Comments	Criterion A

Conducted interference

Standards/regulations	EN 61000-4-6
-----------------------	--------------

Conducted interference

Input/output/signal	asymmetrical
Frequency range	150 kHz ... 80 MHz
Comments	Criterion A

1584245
<https://www.phoenixcontact.com/pc/products/1584245>

Voltage	10 V (Test Level 3)
Criteria	
Criterion A	Normal operating behavior within the specified limits.
Criterion B	Temporary impairment to operational behavior that is corrected by the device itself.

PS-EE-2G-DIODE/12-48DC/2X10/SC - Redundancy module




1584245

<https://www.phoenixcontact.com/pc/products/1584245>

Drawings

Schematic diagram

Housing



Test sections, insulation voltage

PS-EE-2G-DIODE/12-48DC/2X10/SC - Redundancy module



1584245

<https://www.phoenixcontact.com/pc/products/1584245>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/pc/products/1584245>



IECEE CB Scheme

Approval ID: SG PSB-MS-00390



cULus Listed

Approval ID: 2023-12-12-E123528

PS-EE-2G-DIODE/12-48DC/2X10/SC - Redundancy module



1584245
<https://www.phoenixcontact.com/pc/products/1584245>

Classifications

ECLASS

ECLASS-13.0	27371010
ECLASS-15.0	27371010

ETIM

ETIM 9.0	EC000683
----------	----------

PS-EE-2G-DIODE/12-48DC/2X10/SC - Redundancy module



1584245

<https://www.phoenixcontact.com/pc/products/1584245>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-25
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

EF3.0 Climate Change

CO2e kg	15.67 kg CO2e
---------	---------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstraße 8
D-32825 Blomberg
+49 (0) 5235-3 00
info@phoenixcontact.com