

RC-12S1N121L00 - Cable connector

1598510

<https://www.phoenixcontact.com/us/products/1598510>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Cable connector, series: RC, straight, shielded: no, Screw locking mechanism, No. of pos.: 12, Direction of rotation: Standard, contact connection type: Socket, Solder cup, coding: N. This product is in the process of being discontinued. This product must no longer be considered for new projects. Please contact your sales representative for alternatives.

Commercial data

Item number	1598510
Packing unit	20 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	AB31
Product key	ABRAFA
GTIN	4046356220996
Weight per piece (including packing)	101.755 g
Weight per piece (excluding packing)	95.37 g
Customs tariff number	85366990
Country of origin	DE

RC-12S1N121L00 - Cable connector

1598510

<https://www.phoenixcontact.com/us/products/1598510>



Technical data

Product properties

Product type	Circular connector (cable-side)
Type of the screw connection	IP68 screw
Thread type	M23

Material specifications

Flammability rating according to UL 94	V0
--	----

Mechanical properties

Mechanical data	
Type of the screw connection	IP68 screw

Connector

Insulating body	
Coding	N
Material (Insulating body)	PBT
Material (Contact)	CuZn
Material (Contact surface)	Ni/Au
Insertion/withdrawal cycles	50
Connection method	Solder cup
Contact switching type	Socket
Application	Signal
Number of positions	12
Direction of rotation	Standard
Connection profile	12
Number Contact (Contact group 1)	12
Diameter Contact (Contact group 1)	1 mm
Litz wire cross-section min. Contact (Contact group 1)	0.08 mm ²
Litz wire cross-section max. Contact (Contact group 1)	1 mm ²
Rated current Contact (Contact group 1)	8 A (for max. connection cross section)
Rated voltage Contact (Contact group 1)	48 V AC
	74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3

Housing

Type	Cable connector housing
Thread type	M23
Design	straight
Type of locking	Screw locking mechanism

RC-12S1N121L00 - Cable connector

1598510

<https://www.phoenixcontact.com/us/products/1598510>



Pg screw connection	none
Material (Housing)	GD-Zn
Material (Housing surface)	Ni
Material (Rotating parts)	CuZn
Degree of protection (plugged in)	IP65
	IP67

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
----------------------	------

RC-12S1N121L00 - Cable connector


1598510

<https://www.phoenixcontact.com/us/products/1598510>



Drawings

Schematic diagram



Connector pin assignment


RC-12S1N121L00 - Cable connector

1598510

<https://www.phoenixcontact.com/us/products/1598510>



Schematic diagram



Connector pin assignment


RC-12S1N121L00 - Cable connector

1598510

<https://www.phoenixcontact.com/us/products/1598510>



Schematic diagram



Dimensional drawing

RC-12S1N121L00 - Cable connector

1598510

<https://www.phoenixcontact.com/us/products/1598510>



Classifications

ECLASS

ECLASS-13.0	27440116
ECLASS-15.0	27440116

ETIM

ETIM 9.0	EC002635
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

RC-12S1N121L00 - Cable connector

1598510

<https://www.phoenixcontact.com/us/products/1598510>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.	

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	88679a20-ba1f-43e2-8c08-b0b0b12d3e29

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com