

# RC-12S1N8D0000 - Contact insert



1599343

<https://www.phoenixcontact.com/us/products/1599343>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact insert, M23, number of positions: 12, contact connection type: Socket, Crimp connection, series: NC, RC, RM, TU, UC, this item is expected to be lead-free from Q4 2025 in accordance with RoHS II without exception 6c (Pb < 0.1%), a lead-free alternative is possible on request in advance

## Commercial data

Item number	1599343
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB31
Product key	ABRAFU
GTIN	4046356225465
Weight per piece (including packing)	11.7 g
Weight per piece (excluding packing)	5.1 g
Customs tariff number	85389099
Country of origin	DE

# RC-12S1N8D0000 - Contact insert

1599343

<https://www.phoenixcontact.com/us/products/1599343>



## Technical data

### Product properties

Product type	Contact insert
Series	NC
	RC
	RM
	TU
	UC
Application	Signal
Number of positions	12
Connection profile	12
Coding	N
Thread type	M23

### Electrical properties

#### Contact: Contact group 1

Contact diameter	1 mm
Min. cross section	0.14 mm <sup>2</sup>
Max. cross section	0.56 mm <sup>2</sup>
Nominal current I <sub>N</sub>	8 A (for max. connection cross section)
Nominal voltage U <sub>N</sub>	48 V AC
	74 V DC
Overvoltage category	III
Degree of pollution	3
Rated surge voltage	1.5 kV

### Connection data

Connection method	Crimp connection
-------------------	------------------

### Material specifications

Material Insulating body	PA 6.6
Material Contact	CuZn
Material Contact surface	Ni/Au

### Connector

Direction of rotation	Standard
-----------------------	----------

### Mechanical properties

Mechanical data	
Insertion/withdrawal cycles	50

### Environmental and real-life conditions

# RC-12S1N8D0000 - Contact insert

1599343

<https://www.phoenixcontact.com/us/products/1599343>



## Ambient conditions

Permissible humidity (storage/transport)	50 % ... 65 %
--	---------------

# RC-12S1N8D0000 - Contact insert


1599343

<https://www.phoenixcontact.com/us/products/1599343>



## Drawings

Schematic diagram



Connector pin assignment


# RC-12S1N8D0000 - Contact insert

1599343

<https://www.phoenixcontact.com/us/products/1599343>



Schematic diagram



Dimensional drawing

# RC-12S1N8D0000 - Contact insert

1599343

<https://www.phoenixcontact.com/us/products/1599343>



## Classifications

### ECLASS

ECLASS-13.0	27440223
ECLASS-15.0	27440223

### ETIM

ETIM 9.0	EC003557
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# RC-12S1N8D0000 - Contact insert

1599343

<https://www.phoenixcontact.com/us/products/1599343>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.	

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	8476f8cb-d1fd-435a-9660-498ef03a2933

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

### Phoenix Contact USA

586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)