

RF-12S2N8AWA00 - Device connector front mounting



1607307

<https://www.phoenixcontact.com/us/products/1607307>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector front mounting, straight, Screw locking mechanism, M23, number of positions: 12, contact connection type: Socket, Axial O-ring, shielded: yes, number of positions: 12, connection method: Crimp connection, series: RF, This product is in the process of being discontinued. This product must no longer be considered for new projects. Please contact your sales representative for alternatives.

Your advantages

- Safe use in the field, thanks to high degree of protection
- Connector for flexible on-site assembly
- Consistent EMC protection for reliable connection solutions in the industrial environment
- Crimping connection: vibration- and temperature-resistant assembly

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 1607307 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | AB31 |
| Product key | ABRAGL |
| GTIN | 4046356174879 |
| Weight per piece (including packing) | 32.7 g |
| Weight per piece (excluding packing) | 31.263 g |
| Customs tariff number | 85366990 |
| Country of origin | DE |

RF-12S2N8AWA00 - Device connector front mounting



1607307

<https://www.phoenixcontact.com/us/products/1607307>

Technical data

Notes

| | |
|--------------------|--|
| Order information: | Order crimp contacts Ø 1 mm separately |
|--------------------|--|

Mounting

| | |
|---------------|--|
| Mounting type | Front mounting/square flange (4x Ø 3.2 mm) |
|---------------|--|

Product properties

| | |
|---------------------|-----------------------------------|
| Product type | Circular connectors (device side) |
| Series | RF |
| Application | Signal |
| Application | Signal |
| Number of positions | 12 |
| Connection profile | 12 |
| Shielded | yes |
| Coding | N |
| Thread type | M23 |

Material specifications

| | |
|--------------------------|--------------|
| Material Housing | GD-Zn |
| Material Rotating parts | CuZn |
| Material Housing surface | Ni |
| Material Insulating body | PA 6.6 |
| Material Seal | FPM (O-ring) |

Electrical properties

| | |
|-----------------------|---------|
| Contact | |
| Contact diameter | 1 mm |
| Nominal current I_N | 8 A |
| Nominal voltage U_N | 48 V AC |
| | 74 V DC |
| Overvoltage category | III |
| Degree of pollution | 3 |
| Rated surge voltage | 1.5 kV |

Connection data

| | |
|-------------------------|------------------|
| Conductor connection | |
| Connection method | Crimp connection |
| Contact connection type | Socket |

Connector

| | |
|------|----------|
| Type | straight |
|------|----------|

RF-12S2N8AWA00 - Device connector front mounting

1607307

<https://www.phoenixcontact.com/us/products/1607307>



Direction of rotation

Counter direction

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|-------------------|
| Degree of protection | IP67 |
| Ambient temperature (operation) | -20 °C ... 125 °C |
| Altitude | 2000 m |

RF-12S2N8AWA00 - Device connector front mounting




1607307

<https://www.phoenixcontact.com/us/products/1607307>


Drawings

Dimensional drawing



Installation dimensions

Dimensional drawing



Dimensional drawing


RF-12S2N8AWA00 - Device connector front mounting

1607307

<https://www.phoenixcontact.com/us/products/1607307>



Schematic diagram



Contact chamber numbering (view of plug-in side), socket counter direction

RF-12S2N8AWA00 - Device connector front mounting

1607307

<https://www.phoenixcontact.com/us/products/1607307>



Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1607307>

| cUL Recognized Approval ID: E153698-20090723 | | | | |
|--|-----------------------|-----------------------|-------------------|----------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| keine | 48 V | 5 A | 20 | - |

| UL Recognized Approval ID: E153698-20090723 | | | | |
|---|-----------------------|-----------------------|-------------------|----------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| keine | 48 V | 5 A | 20 | - |

RF-12S2N8AWA00 - Device connector front mounting

1607307

<https://www.phoenixcontact.com/us/products/1607307>



Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27440109 |
| ECLASS-15.0 | 27440109 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC003569 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

RF-12S2N8AWA00 - Device connector front mounting

1607307

<https://www.phoenixcontact.com/us/products/1607307>



Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com