

# ST-06KP010 - Crimp contact

1607577

<https://www.phoenixcontact.com/us/products/1607577>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



## Your advantages

- Crimping connection: vibration- and temperature-resistant assembly
- High tensile strength of the connection
- Low contact resistance
- Easy production monitoring

## Commercial data

Item number	1607577
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	AB36
Product key	ABREAB
GTIN	4046356272933
Weight per piece (including packing)	0.239 g
Weight per piece (excluding packing)	0.239 g
Customs tariff number	85366990
Country of origin	DE

# ST-06KP010 - Crimp contact

1607577

<https://www.phoenixcontact.com/us/products/1607577>



## Technical data

### Product properties

Product type	Crimp contact
Contact material type	turned

### Connection data

Connection technology	
Contact connection type	Pin
Connection method	Crimp connection

Conductor connection	
Connection cross section	0.06 mm <sup>2</sup> ... 0.25 mm <sup>2</sup>

### Material specifications

Material Contact	CuZn
Material Metal surface contact area (middle layer)	Ni
Material Metal surface contact area (top layer)	Au

### Dimensions

Diameter (Contact diameter)	0.6 mm
-----------------------------	--------

### Mechanical properties

Mechanical data	
Insertion/withdrawal cycles	100

# ST-06KP010 - Crimp contact

1607577

<https://www.phoenixcontact.com/us/products/1607577>



## Classifications

### ECLASS

ECLASS-13.0	27440204
ECLASS-15.0	27440204

### ETIM

ETIM 9.0	EC000796
----------	----------

### UNSPSC

UNSPSC 21.0	39121500
-------------	----------

# ST-06KP010 - Crimp contact

1607577

<https://www.phoenixcontact.com/us/products/1607577>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.	

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	5afe6b3c-d868-4145-9059-cc5b579e07e4

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

### Phoenix Contact USA

586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)