

# SACB-6/12-L-C GG SCO - Distributor box header

1516755

<https://www.phoenixcontact.com/us/products/1516755>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Distributor box header, application: Standard, extended requirements, connection method: M12 socket Metal, number of slots: 6, number of positions: 5, coding: A, slot assignment: Double, status display: yes, PNP; master cable connection: Pluggable screw connection, shielding: no

## Commercial data

Item number	1516755
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF42
Product key	AF3CCD
GTIN	4017918967482
Weight per piece (including packing)	252.9 g
Weight per piece (excluding packing)	223.1 g
Customs tariff number	85366990
Country of origin	DE

SACB-6/12-L-C GG SCO - Distributor box header



1516755

<https://www.phoenixcontact.com/us/products/1516755>

## Technical data

## Notes

Assembly note	<p><b>NOTE:</b> Observe the permissible bending radii when routing cables, since the degree of protection may be at risk if the bending forces are too high. Reduce mechanical loads upstream of the connector, e.g., by using cable ties.</p>
Note on application	<p>Unused slots are to be sealed off prior to commissioning. Suitable sealing elements are to be found under "Accessories".</p>

## Product properties

Product type	Header with metric measurement slots
Application	Standard, extended requirements
Number of positions	5
Number of slots	6
Coding	A
LED	yes

## System properties

## Local diagnostics

Monitored function	Supply voltage per module
Optical representation	Green LED

## Electrical properties

Max. operating voltage $U_{\max}$	30 V DC
Local diagnostics	Supply voltage per module Green LED Status display I/O Yellow LED
Nominal voltage $U_N$	24 V DC
Rated current, total	10 A 2x 8 A (For electrical isolation)
Max. current carrying capacity per path	2 A
Current carrying capacity per slot	4 A

## Signaling

Status display present yes

## Dimensions

Dimensional drawing

Width **58 mm**

# SACB-6/12-L-C GG SCO - Distributor box header

1516755

<https://www.phoenixcontact.com/us/products/1516755>



Height	26 mm
Length	126 mm

## Material specifications

Material Threaded sleeve	Die-cast zinc
Material Housing	PBT
Material Molding compound	PUR
Flammability rating according to UL 94	V0
Seal material O-ring	NBR
Contact material	Cu alloy
Contact surface material	gold-plated
Contact carrier material	PA
Material of contact, master cable side	CU alloy
Material of the contact carrier on the master cable side	PA 6.6 V0
Material of contact surface, master cable side	gold-plated

## Cable/line

Connection method	Pluggable screw connection
-------------------	----------------------------

## Environmental and real-life conditions

Ambient conditions	
Degree of protection	IP65
	IP67
	IP69K
Ambient temperature (operation)	-30 °C ... 80 °C

## Standards and regulations

Standard designation	M12 connector
Standards/specifications	IEC 61076-2-101

# SACB-6/12-L-C GG SCO - Distributor box header


1516755

<https://www.phoenixcontact.com/us/products/1516755>




## Drawings

Dimensional drawing



Schematic diagram



M12 slot, socket, 5-pos.


# SACB-6/12-L-C GG SCO - Distributor box header

1516755

<https://www.phoenixcontact.com/us/products/1516755>



Schematic diagram



Potential  $U_{N1}$  and  $U_{N2}$  bridged. Potential assignment:  $U_{N1} = U_{N2} = \text{slots 1,2,3,4,5,6}$ .


# SACB-6/12-L-C GG SCO - Distributor box header



1516755


<https://www.phoenixcontact.com/us/products/1516755>

Schematic diagram



Electrically isolated. Potential assignment: U<sub>N1</sub> = slots 1,3,5 and U<sub>N2</sub> = slots 2,4,6.

Circuit diagram



# SACB-6/12-L-C GG SCO - Distributor box header

1516755

<https://www.phoenixcontact.com/us/products/1516755>



## Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1516755>

cUL Recognized		Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $mm^2$
keine		24 V	3 A	-	-

UL Recognized		Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $mm^2$
keine		24 V	3 A	-	-

EAC					
Approval ID: RU C-DE.AI30.B.01102					

# SACB-6/12-L-C GG SCO - Distributor box header

1516755

<https://www.phoenixcontact.com/us/products/1516755>



## Classifications

### ECLASS

ECLASS-13.0	27440111
ECLASS-15.0	27440111

### ETIM

ETIM 9.0	EC003558
----------	----------

### UNSPSC

UNSPSC 21.0	31251500
-------------	----------

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road

Middletown, PA 17057, United States

(+717) 944-1300

[info@phoenixcon.com](mailto:info@phoenixcon.com)