

SAC-5P- 2,0-900/FSB SCO - Bus system cable

1517916

<https://www.phoenixcontact.com/us/products/1517916>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Bus system cable, INTERBUS (16 Mbps), 5-position, PUR halogen-free, may green RAL 6017, shielded, free cable end, on Socket straight M12 SPEEDCON, coding: B, cable length: 2 m

Commercial data

Item number	1517916
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF04
Product key	AF1CKB
GTIN	4017918968038
Weight per piece (including packing)	168.3 g
Weight per piece (excluding packing)	164.5 g
Customs tariff number	85444290
Country of origin	PL

SAC-5P- 2,0-900/FSB SCO - Bus system cable

1517916

<https://www.phoenixcontact.com/us/products/1517916>



Technical data

Product properties

Product type	Data cable preassembled
Application	Standard
Sensor type	INTERBUS
Number of positions	5
No. of cable outlets	1
Shielded	yes
Coding	B

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Interfaces

Bus system	INTERBUS
Signal type/category	INTERBUS, 16 Mbps

Signaling

Status display	no
Status display present	no

Electrical properties

Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	48 V AC
	60 V DC
Nominal current I_N	4 A
Transmission medium	Copper
Transmission speed	16 Mbps

Material specifications

Flammability rating according to UL 94	V0
Seal material	NBR
Material of grip body	TPU, hardly inflammable, self-extinguishing
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	PA 6.6
Material for screw connection	Zinc die-cast, nickel-plated

Connection data

Connection assignment	
Contact Color (signal designation) Contact (optional)	1 (Socket) YE (DO)
	2 (Socket) GN (DO)

SAC-5P- 2,0-900/FSB SCO - Bus system cable

1517916

<https://www.phoenixcontact.com/us/products/1517916>



3 (Socket) GY (DI)
4 (Socket) PK (DI)
5 (Socket) BN (GND)

Connector

Connection 1	
Type	free cable end

Connection 2	
Type	free cable end

Cable/line

Cable length	2 m
--------------	-----

INTERBUS [900]	Dimensional drawing	
----------------	---------------------	--

Cable weight	70 kg/km
Number of positions	6
Shielded	yes
Cable type	INTERBUS [900]
Conductor structure	3 x 2 x 0.22 mm ²
Signal speed	0.66 c
Conductor structure signal line	32x 0.10 mm
AWG signal line	24
Conductor cross section	3x 2x 0.22 mm ²
External cable diameter	8.00 mm
Outer sheath, material	PUR
External sheath, color	may green RAL 6017
Conductor material	Bare Cu litz wires
Material wire insulation	PE
Single wire, color	green-yellow, white-brown, gray-pink
Twisted pairs	2 cores to the pair
Overall twist	3 pairs to the core
Insulation resistance	≥ 5 GΩ*km
Coupling resistance	< 250.00 mΩ/m (at 30 MHz)
Loop resistance	≤ 159.80 Ω/km
Wave impedance	120 Ω ±20 % (at 64 kHz)

SAC-5P- 2,0-900/FSB SCO - Bus system cable

1517916

<https://www.phoenixcontact.com/us/products/1517916>



Cable capacity	100 $\Omega \pm 15\%$ (with 1 MHz)
Nominal voltage, cable	≤ 60 nF/km (At 800 Hz)
Test voltage Core/Core	250 V (Peak value, not for high-power applications)
Test voltage Core/Shield	1500 V _{rms}
Minimum bending radius, fixed installation	1000.00 V _{rms}
Minimum bending radius, flexible installation	7.5 x D
Smallest bending radius, fixed installation	15 x D
Smallest bending radius, movable installation	60 mm
Dynamic load capacity (bending)	120 mm
Near end crosstalk attenuation (NEXT)	Max. bending cycles: 5000000, Bending radius: 120 mm, Traversing path: 10 m, Traversing rate: 1.6 m/s, Acceleration: 3.2 m/s ²
Shield attenuation	≥ 61 dB (at 772 kHz) ≥ 59 dB (with 1 MHz) ≥ 55 dB (at 2 MHz) ≥ 50 dB (at 4 MHz) ≥ 46 dB (at 8 MHz) ≥ 44 dB (at 10 MHz) ≥ 41 dB (at 16 MHz) ≥ 40 dB (at 20 MHz)
Flame resistance	≤ 15 dB/km (at 256 kHz) ≤ 24 dB/km (at 772 kHz) ≤ 27 dB/km (with 1 MHz) ≤ 52 dB/km (at 4 MHz) ≤ 84 dB/km (at 10 MHz) ≤ 112 dB/km (at 16 MHz) ≤ 119 dB/km (at 20 MHz)
Ambient temperature (operation)	according to VDE 0472, Part 4, test type B according to IEC 60332-1 -40 °C ... 80 °C (cable, fixed installation) -30 °C ... 70 °C (Cable, flexible installation)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
	IP67
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 90 °C (Plug / socket)

SAC-5P- 2,0-900/FSB SCO - Bus system cable


1517916

<https://www.phoenixcontact.com/us/products/1517916>




Drawings

Dimensional drawing



M12 x 1 socket, straight, shielded

Schematic diagram



Pin assignment M12 socket, 5-pos., B-coded, female side


SAC-5P- 2,0-900/FSB SCO - Bus system cable

1517916

<https://www.phoenixcontact.com/us/products/1517916>



Circuit diagram



Contact assignment of the M12 socket

SAC-5P- 2,0-900/FSB SCO - Bus system cable

1517916

<https://www.phoenixcontact.com/us/products/1517916>



Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1517916>



EAC-RoHS

Approval ID: RU D-DE.HB35.B.00387

SAC-5P- 2,0-900/FSB SCO - Bus system cable

1517916

<https://www.phoenixcontact.com/us/products/1517916>



Classifications

ECLASS

ECLASS-13.0	27060307
ECLASS-15.0	27060307

ETIM

ETIM 9.0	EC001855
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

SAC-5P- 2,0-900/FSB SCO - Bus system cable

1517916

<https://www.phoenixcontact.com/us/products/1517916>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.0 Climate Change

CO2e kg	0.881 kg CO2e
---------	---------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road

Middletown, PA 17057, United States

(+717) 944-1300

info@phoenixcon.com