

# SACC-MINFS-5CON-PG13 - Connector



1521397

<https://www.phoenixcontact.com/us/products/1521397>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



## Your advantages

- Safe use in the field, thanks to a high degree of protection
- Screw connection: proven connection technology for a large selection of different conductors

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1521397       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | BF30          |
| Product key                          | AF2FAA        |
| GTIN                                 | 4017918949617 |
| Weight per piece (including packing) | 57.62 g       |
| Weight per piece (excluding packing) | 55.24 g       |
| Customs tariff number                | 85366990      |
| Country of origin                    | DE            |

## Technical data

### Notes

#### Assembly note

**NOTE:** Observe the permissible bending radii when routing cables, since the degree of protection may be at risk if the bending forces are too high. Reduce mechanical loads upstream of the connector, e.g., by using cable ties.

### Mounting

#### Assembly note

The wires can be connected both with ferrules and without ferrules

### Product properties

|                      |                                 |
|----------------------|---------------------------------|
| Product type         | Circular connector (cable-side) |
| Sensor type          | Universal                       |
| Number of positions  | 5                               |
| No. of cable outlets | 1                               |
| Shielded             | no                              |
| Coding               | A                               |
| Cable outlet         | straight                        |
| Pg screw connection  | Pg13,5                          |

#### Insulation characteristics

|                      |     |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution  | 3   |

### Dimensions

#### Dimensional drawing



#### Length

84 mm

#### External dimensions

#### Outside diameter

10 mm ... 12 mm

#### Housing

#### Diameter housing

27 mm

### Material specifications

|                                        |                              |
|----------------------------------------|------------------------------|
| Flammability rating according to UL 94 | HB                           |
| Material of grip body                  | PBT                          |
| Contact material                       | CuZn                         |
| Contact surface material               | Au                           |
| Contact carrier material               | PUR/PA 6.6                   |
| Material for screw connection          | Zinc die-cast, nickel-plated |

# SACC-MINFS-5CON-PG13 - Connector



1521397

<https://www.phoenixcontact.com/us/products/1521397>

## Connection data

### Conductor connection

|                                         |                                                                |
|-----------------------------------------|----------------------------------------------------------------|
| Connection method                       | Screw connection                                               |
| Connection cross section                | 0.34 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> (without ferrule) |
|                                         | 0.34 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> (with ferrule)    |
|                                         | 0.34 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> (solid)           |
| Connection cross section AWG            | 22 ... 16 (without ferrule)                                    |
|                                         | 22 ... 16 (with ferrule)                                       |
| Stripping length of the individual wire | 7 mm                                                           |
| Tightening torque                       | 0.8 Nm (7/8" connectors)                                       |
|                                         | 0.4 Nm (Screw terminal blocks)                                 |
|                                         | 1 Nm ... 1.4 Nm (Pressure screw)                               |

## Electrical properties

|                                |          |
|--------------------------------|----------|
| Rated surge voltage            | 4 kV     |
| Contact resistance             | ≤ 5 mΩ   |
| Insulation resistance          | ≥ 100 MΩ |
| Nominal voltage U <sub>N</sub> | 300 V AC |
|                                | 300 V DC |
| Nominal current I <sub>N</sub> | 9 A      |

## Mechanical properties

### Mechanical data

|                             |       |
|-----------------------------|-------|
| Insertion/withdrawal cycles | ≥ 100 |
|-----------------------------|-------|

## Connector

### Connection 1

|                   |            |
|-------------------|------------|
| Head design       | Socket     |
| Head cable outlet | straight   |
| Head thread type  | 7/8"-16UNF |
| Coding            | A          |

## Cable/line

|                                         |           |
|-----------------------------------------|-----------|
| Signal type/category                    | Universal |
| Stripping length of the individual wire | 7 mm      |

## Environmental and real-life conditions

### Ambient conditions

|                                                                   |                                  |
|-------------------------------------------------------------------|----------------------------------|
| Degree of protection                                              | IP67                             |
| Ambient temperature (operation) (male connector/female connector) | -25 °C ... 85 °C (Plug / socket) |

# SACC-MINFS-5CON-PG13 - Connector


1521397

<https://www.phoenixcontact.com/us/products/1521397>




## Drawings

Dimensional drawing



Socket 7/8"-16UNF, straight, Pg13

Functional drawing




# SACC-MINFS-5CON-PG13 - Connector

1521397

<https://www.phoenixcontact.com/us/products/1521397>



Schematic diagram



Pin assignment, socket, 7/8"-16UNF, 5-pos., view of female side

# SACC-MINFS-5CON-PG13 - Connector



1521397

<https://www.phoenixcontact.com/us/products/1521397>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1521397>

|                                                                                                                                       |                                |                                |                   |                               |
|---------------------------------------------------------------------------------------------------------------------------------------|--------------------------------|--------------------------------|-------------------|-------------------------------|
|  <b>cUL Recognized</b><br>Approval ID: FILE E 221474 |                                |                                |                   |                               |
|                                                                                                                                       | Nominal voltage U <sub>N</sub> | Nominal current I <sub>N</sub> | Cross section AWG | Cross section mm <sup>2</sup> |
| keine                                                                                                                                 |                                |                                |                   |                               |
|                                                                                                                                       | 600 V                          | 9 A                            | -                 | -                             |

|                                                                                                                                      |                                |                                |                   |                               |
|--------------------------------------------------------------------------------------------------------------------------------------|--------------------------------|--------------------------------|-------------------|-------------------------------|
|  <b>UL Recognized</b><br>Approval ID: FILE E 221474 |                                |                                |                   |                               |
|                                                                                                                                      | Nominal voltage U <sub>N</sub> | Nominal current I <sub>N</sub> | Cross section AWG | Cross section mm <sup>2</sup> |
| keine                                                                                                                                |                                |                                |                   |                               |
|                                                                                                                                      | 600 V                          | 9 A                            | -                 | -                             |

|                                                                                                                                     |  |  |  |  |
|-------------------------------------------------------------------------------------------------------------------------------------|--|--|--|--|
|  <b>EAC</b><br>Approval ID: RU C-DE.AI30.B.01102 |  |  |  |  |
|-------------------------------------------------------------------------------------------------------------------------------------|--|--|--|--|

# SACC-MINFS-5CON-PG13 - Connector



1521397

<https://www.phoenixcontact.com/us/products/1521397>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27440116 |
| ECLASS-15.0 | 27440116 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC002635 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

## Environmental product compliance

## EU RoHS

|                                         |      |
|-----------------------------------------|------|
| Fulfills EU RoHS substance requirements | Yes  |
| Exemption                               | 6(c) |

## China RoHS

|                                        |                                                                                                                                                                                                                                   |
|----------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-50                                                                                                                                                                                                                           |
|                                        | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

## EU REACH SVHC

|                                     |                                      |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1)                 |
| SCIP                                | 1f75efab-59d4-4e9a-8c46-de58ddf0d219 |

## EF3.0 Climate Change

|         |               |
|---------|---------------|
| CO2e kg | 1.546 kg CO2e |
|---------|---------------|